


RoHS Compliant



- NOTES:
- MATERIAL:
 - Insulator: High Temperature Thermoplastic, UL94V-0; Color Black.
 - Terminal: Copper Alloy.
 - Shell: Stainless Steel.
 - PLATING:
 - Contact: Plated Ni Overall Contact Au 1u",
 - Shell: Plated Ni Overall, PAD Au 1u"
 - SPECIALITY:
 - Current Rating :0.5mA AC/DC max.
 - Voltage Rating :125V AC/DC
 - Ambient Temperature Range :-20° C~+60° C
 - Storage Temperature Range :-40° C~+70° C
 - Ambient Humidity Range :95% R.H. Max.
 - Contact Resistance:100mΩ max.
 - Insulation Resistance:1000MΩ min./500VDC
 - Mating Cycles:10,000 Insertions
 - Reflow peak temp.: 260° C ±5° C, 3~5 s
 - Mating Cycles:3,000 Insertions Min
 - PLEASE CONTACT LQ SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS & AVAILABILITY

SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	NANO SIM NO PUSH 1.35H 带柱		
		料号(PART NO)	MLD-NANO SIM 6P-H1.35		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	版次(REV): A/O	页次(PAGE): 1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1		模号 (MODEL NO)	图号 (DWG NO)	审核 (CHECKED)	邱敏
图号 (DWG NO)		图号 (DWG NO)		核准 (APPROVED)	陈镇
图号 (DWG NO)		图号 (DWG NO)	图号 (DWG NO)	图号 (DWG NO)	图号 (DWG NO)