






NOTE:


1:SPECIFICATION:


- 1.1 Voltage Rating: 60V AC/DC
- 1.2 Rated current : signal contact 0.3 AMPS/Pin
power contact 12 AMPS Max/(All power Pin)
- 1.3 Temperature Range: -40 °C to +85°C
- 1.4 Contact Resistance:
Signalpin:Initial:50mΩ MAX
AFTER TEST:Δ20mΩ
Power pin:Initial:15mΩ MAX
AFTER TEST:15mΩ MAX
- 1.5 Insulation Resistance
Initial: 500 MΩ Minimum.
After test: 500 MΩ Minimum.
- 1.6 Dielectric Withstanding Voltage
NO EVIDENCE OF BREAKDOWN IN AC 100 V,
1 MINUTE
- 1.7 MATING-UNMATING FORCE:
MATING FORCE: 30N MAX
UNMATING FORCE: 3N MIN
- 1.8 SALT WATER SPRAY: TEMPERATURE 35°C±2°C
DENSITY OF SALT WATER 5±1%
DURATION:48±2 HOUR
- 1.9 Storage Temperature Range -40°C to +85°C
0 to 90 % RH (Relative humidity).

4	POWER CONTACT-B	COPPER ALLY, AuSn ¹ Min on CONTACT AREA, AuSn ¹ Min on SOLDER AREA, Ni 50u"Min ALL OVER				
3	POWER CONTACT-A	COPPER ALLY, AuSn ¹ Min on CONTACT AREA, AuSn ¹ Min on SOLDER AREA, Ni 50u"Min ALL OVER	7	REEL		PLASTIC
2	SIGNAL CONTACT	COPPER ALLY, AuSn ¹ Min on CONTACT AREA, AuSn ¹ Min on SOLDER AREA, Ni 50u"Min ALL OVER	6	COVER TAPE		PLLYESTER
1	HOUSING	LCP , BLACK, UL 94 V-0	5	EMBOSSED CARRIER TAPE	PS	
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS	




深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY :	DATE :	PART NAME:	
X.X ±0.30		陈一鸣	2014-02-23	0.3PH 单槽BTB 母座6+6P	
X.XX ±0.25					
X.XXX ±0.15					
X: ±2° X.X: ±0.5°		CHECKED BY:	DATE :	PART NO.	HYCW58F-BTB2X3-6-05
		马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch]				APPROVED BY:	DATE :
SCALE: 1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1




DIRECTION OF UNREELING



STYLE AND DIMENSION OF REEL

PER REEL 15000 CONNECTORS



TRAILER

TAPING (FREE)

LEADER



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY :	DATE :	PART NAME:	
	陈一鸣	2014-02-23	包装图	
	CHECKED BY:	DATE :	PART NO.	
	马跃	2014-02-23	MOLD NO.	
APPROVED BY: 邱敏	DATE :	DRAW NO:		
	2014-02-23	SHEET NO.	1 OF 1	