



General description

The SD48C-SL is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time , make these parts ideal for ESD protection on designs where board space is at a premium

Features and benefits

- Reverse stand-off voltage: 48V Max
- Low leakage current: nA Level
- Low Clamping Voltage
- Response time is typically < 1 ns
- IEC61000-4-2 Level 4 ESD Protection

Application information

- Cell phones
- Audio equipment
- Portable devices
- Digital cameras
- Power supplies

Ordering information

Device	Package	Packaging	Reel Size
SD48C-SL	SOD323	3000/Tape & Reel	7 Inch

Schematic & Pin configuration

Simplified outline	Graphic symbol

Maximum Ratings ($T_{OP} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power ($t_p = 8/20\text{ }\mu\text{s}$)	P_{PPM}	760	W
Peak Pulse Current ($t_p = 8/20\text{ }\mu\text{s}$)	I_{PPM}	9	A
Maximum lead temperature for soldering during 10s	T_L	260	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	-55 to +150	$^{\circ}\text{C}$
Operating Temperature Range	T_{OP}	-40 to +125	$^{\circ}\text{C}$
Maximum junction temperature	T_j	150	$^{\circ}\text{C}$
ESD voltage IEC 61000-4-2 (air discharge)	V_{ESD}	30	kV
ESD voltage IEC 61000-4-2 (contact discharge)	V_{ESD}	30	kV

Electrical Characteristics ($T_{OP} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Condition
Reverse Working Voltage	V_{RWM}	--	--	48.0	V	
Breakdown Voltage	V_{BR}	52.0	--	65.0	V	$I_T=1\text{mA}$
Leakage Current I_{Leak}	I_R	--	--	100	nA	$V_{RWM}=48\text{V}$
Clamping Voltage	V_C	--	64	72	V	$I_{PP}=3\text{A}, t_p=8/20\mu\text{s}$
Clamping Voltage	V_C	--	80	84	V	$I_{PP}=9\text{A}, t_p=8/20\mu\text{s}$
Junction Capacitance	C_j	--	15	20	pF	$V_R=0\text{V}, f=1\text{MHz}$


Portion Electronics Parameter

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
I_T	Test Current
V_{BR}	VBR Breakdown Voltage @ I_T



Package Outline Dimensions

SOD323



SYMBOL	Dimensions In Millimet	
	MIN	MAX
A	0.700	0.900
A1	0.450	0.600
B	1.600	1.800
B1	2.500	2.750
C	1.200	1.400
D	0.080	0.150
D1	0.250	0.350
E	0.000	0.100
R	0.010	0.060