







PCB.WELDING DRAWING (TOLERANCE:±0.05)



SECTION A-A  
SCALE 1:1



技术指标:

- 1.温度范围: -25°C~85°C.
- 2.额定电压: 250V AC,DC.
- 3.耐压: 1500V AC/minute.
- 4.接触电阻: ≤20mΩ .
- 5.绝缘电阻: ≥1000MΩ.
- 6.额定电流: 5A AC,DC.


| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |

| 型号               | CKT  | A     | B     |
|------------------|------|-------|-------|
| A420E1W2-2W2P12  | 2*1  | 0.00  | 5.40  |
| A420E1W2-2W4P12  | 2*2  | 4.20  | 9.60  |
| A420E1W2-2W6P12  | 2*3  | 8.40  | 13.80 |
| A420E1W2-2W8P12  | 2*4  | 12.60 | 18.00 |
| A420E1W2-2W10P12 | 2*5  | 16.80 | 22.20 |
| A420E1W2-2W12P12 | 2*6  | 21.00 | 26.40 |
| A420E1W2-2W14P12 | 2*7  | 25.20 | 30.60 |
| A420E1W2-2W16P12 | 2*8  | 29.40 | 34.80 |
| A420E1W2-2W18P12 | 2*9  | 33.40 | 39.00 |
| A420E1W2-2W20P12 | 2*10 | 37.80 | 43.20 |
| A420E1W2-2W22P12 | 2*11 | 42.00 | 47.40 |
| A420E1W2-2W24P12 | 2*12 | 46.20 | 51.60 |

| 2  | 端子Contact | 黄铜              | N*1 | 表面镀锡 |
|----|-----------|-----------------|-----|------|
| 1  | 基座Wafer   | PA66<br>UL94V-2 | 1   | 白色   |
| 序号 | 名称        | 材料              | 数量  | 备注   |

| TOLERANCE  |           | <div> 深圳聚兴泰电子科技有限公司<br/>Shenzhen Juxingtai Electronic Technology Co., Ltd</div> |                                                                                                                  |              |              |
|------------|-----------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------|--------------|--------------|
| X.X ±0.20  | X.* ±10°  | PART NO.<br>A420E1W2-2WXP12                                                                                                                                          | TITLE:<br>4.2MM WAFER DIP TYPE                                                                                   |              |              |
| .XX ±0.10  | .X* ± 8°  |                                                                                                                                                                      |                                                                                                                  |              |              |
| .XXX ±0.05 | .XX* ± 5° |                                                                                                                                                                      |                                                                                                                  |              |              |
| UNITS      | mm        | DESIGN: Ethan                                                                                                                                                        | <div></div> MANUFACTURE DWG |              |              |
| MATERILA   | — — —     | CHED: Olvia                                                                                                                                                          |                                                                                                                  |              |              |
| FINISH     | — — —     | APPD: Ava                                                                                                                                                            |                                                                                                                  |              |              |
|            |           |                                                                                                                                                                      | <div></div>                 | SCALE<br>N:A | SHEET<br>1/2 |

| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |



|            |           |                                                                                                                                                                            |  |                                                                                                                                    |     |
|------------|-----------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------|-----|
| TOLERANCE  |           | <div>深圳聚兴泰电子科技有限公司</div> <div>Shenzhen Juxingtai Electronic Technology Co., Ltd</div> |  |                                                                                                                                    |     |
| X.X ±0.20  | X.* ±10°  | PART NO.                                                                                                                                                                   |  | TITLE:                                                                                                                             |     |
| .XX ±0.10  | .X* ± 8°  | A420E1W2-2BXP12                                                                                                                                                            |  | 4.2MM WAFER DIP TYPE                                                                                                               |     |
| .XXX ±0.05 | .XX* ± 5° | DESIGN: Ethan                                                                                                                                                              |  | MANUFACTURE DWG                                                                                                                    |     |
| UNITS      | mm        | CHED: Olvia                                                                                                                                                                |  | <div></div> <div>SCALE</div> <div>SHEET</div> |     |
| MATERILA   | — — —     | APPD: Ava                                                                                                                                                                  |  |                                                                                                                                    |     |
| FINISH     | — — —     |                                                                                                                                                                            |  | N:A                                                                                                                                | 2/2 |