





RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE





SPECIFICATION:

1. Material & Finish: See the list;
2. Mechanical:
 - 2.1. Mating force: 5-20Nf;
 - 2.2. Unmating force: 6-20Nf;
 - 2.3. Durability: 3000 Cycles;
3. Electrical:
 - 3.1. Current Rating: 3A Max.;
 - 3.2. Voltage Rating: 20V Max.;
 - 3.3. Dielectric Withstanding voltage: 100Vac;
 - 3.4. Contact resistance: 40m Ohms Max.;
 - 3.5. Insulation Resistance: 100M Ohms Min.;
4. Environmental:
 - 4.1. Operating temperature: -40° C ~ +85° C;
 - 4.2. Salt Spray Test: 24H Min. (No oxidation or rust);
 - 4.3. Wetting Temperature: 265±5° C, 5±0.5s



A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL	PIN	SIGNAL

NO.	PART NAME	Q'TY	MATERIAL	FINISH
3	Shell	1	SUS201 T=0.30mm	Ni
2	Housing	1	LCP	UL 94 V-0
1	Contact	1	C5191 T=0.20mm	Au



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X.°	±5°
.XX	±0.20	X.X°	±1°
.XXX	±0.10	X.XX°	±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.

TITLE:

HMT-TYPE-C 6P

Type-C 6P 贴片

DESIGN: James

CUSTOMER

SIZE

UNITS

CHED: Talen


SCALE

SHEET

APPD: Sophia



N:A 1/1



RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

- 说明:
- 每卷前后各空 16PCS, 尾部用美纹胶纸封住;
 - 将产品放满盘后, 再卷一圈保护带, 用美纹胶纸将其封住, 并贴上 1Pcs 物料标签;
 - 每 15 卷盘一叠共 15000Pcs 装入 1 个外箱内;
 - 在搬运过程中要轻拿轻放;
 - 在运输中不可堆放过多 (1.8M 最高), 不可重压;
 - 跌落测试条件:
成品箱从 1.2 米高度自由落体 (一角三棱六面):
 - 产品不可跑出下带凹槽;
 - 产品不可有摔伤, 变形;
 - 内包装材料不可严重破损.

NO.	NAME	SPEC	Q' TY
①	TYPE C RECEPTACLE		15000PCS/CARTON
②	CARRIER TAPE	W=16mm, T=0.40mm	1000PCS/PLATE
③	COVER TAPE	W=13.2mm	15PLATES/CARTON
④	REEL PLATE	330*100*16.4mm	15PCS/CARTON
⑤	RoHS LABEL		15PCS/CARTON
⑥	PRODUCT LABER		15PCS/CARTON
⑦	CARTON	340*340*325mm	1PCS/PACKAGE

GENERAL TOLERANCES UNLESS SPECIFIED			HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO.	TITLE:		
.XX ±0.20	X.X° ±1°	HMT-TYPE-C 6P	Type-C 母 插座		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1