








RoHS




- NOTE:1
- 1. ELECTRICAL CHARACTERISTICS:
 - 1.1 CURRENT RATING: 0.5A MAX.
 - 1.2 IMPEDANCE: 500HM NOMINAL.
 - 2. MECHANICAL CHARACTERISTICS:
 - 2.1 OPERATING TEMP. -40°~90°
 - 2.2 VEW R UP TO 3GHz: 1.3MAX.
 - 3GHz TO 6GHz: 1.4MAX.
 - 2.3 DURABILITY: 30CYCLES



- NOTE:2
- 1. HOUSING MATERIAL: LCP, NATURE, UL94V-0.
 - 2. TERMINAL MATERIAL: COPPER ALLOY (C2680),
 - 3. SHELL MATERIAL: COPPER ALLOY (C5191),

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

3	GROUND CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
2	INNER CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
1	HOUSING	1	LCP UL94V-0		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARK

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. HMT-IPEX-K501	TITLE: IPEX 内针		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1