

1.Description

The PC814A is a photoelectric coupler composed of two light-emitting diode and phototransistor. It is packaged in a 4-pin package, two forms (DIP, SMD)


2.Features

- Current transfer ratio:
20~300% ($I_F=5\text{mA}$, $V_{CE}=5\text{V}$)
- High isolation voltage between input and output
($V_{ISO}=5000\text{Vrms}$)
- Collector-emitter breakdown voltage $BV_{CEO} \geq 80\text{V}$
- Meet safety standard approval: EU REACH and RoHS

3.Applications

- Switching power supply, intelligent meter
- Industrial control, measuring instruments
- Office equipment such as copiers
- Household appliances: such as air conditioners, fans, water heaters, etc.

4.Pinning Information



DIP-4



SOP-4



5. Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$)

Parameter		Symbol	Rating	Unit
Input	Forward Current	I_F	± 50	mA
	Power Dissipation	P	70	mW
	PowerdissipationDerating factor (above $T_A=100^{\circ}\text{C}$)	P_{DD}	2.9	mW/ $^{\circ}\text{C}$
	Thermal Resistance Junction-Ambient	R_{thJ-A}	325	$^{\circ}\text{C}/\text{W}$
	Thermal Resistance Junction-Case	R_{thJ-C}	200	$^{\circ}\text{C}/\text{W}$
Output	Collector Power Dissipation	P_C	150	mW
	Collector Current	I_C	50	mA
	Collector-Emitter Voltage	V_{CEO}	80	V
	Emitter - Collector Voltage	V_{ECO}	6	V
Total Power Dissipation		P_{TOT}	200	mW
Isolation Voltage		V_{ISO}	5000	Vrms
Operating Temperature		T_{OPR}	-55 to 110	$^{\circ}\text{C}$
Storage Temperature		T_{STG}	-55 to 125	$^{\circ}\text{C}$
Soldering Temperature		T_{SOL}	260 (10s)	$^{\circ}\text{C}$



6. Electrical Characteristics ($T_A=25^\circ\text{C}$)


Parameter	Symbol	Conditions	Min	Typ	Max	Units
Input						
Forward Voltage	V_F	$I_F=\pm 20\text{mA}$		1.2	1.4	V
Terminal Capacitance	C_t	$V=0, f=1\text{kHz}$		30	250	pF
Output						
Collector Dark Current	I_{CEO}	$V_{CE}=20\text{V}$			100	nA
Collector-Emitter Breakdown Voltage	BV_{CEO}	$I_C=0.1\text{mA}, I_F=0$	80			V
Emitter-Collector Breakdown Voltage	BV_{ECO}	$I_E=0.1\text{mA}, I_F=0$	6			V
Transfer Characteristics						
Current Transfer Ratio	CTR	$I_F=5\text{mA}, V_{CE}=5\text{V}$	20		300	%
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_F=20\text{mA}, I_C=1\text{mA}$		0.1	0.2	V
Isolation Resistance	R_{ISO}	DC500V, 40~60%R.H.	5×10^{10}	1×10^{11}		Ω
Isolation Capacitance	C_f	$V=0, f=1\text{MHz}$		0.6	1	pF
Cut-off Frequency	F_C	$V_{CE}=5\text{V}, I_C=2\text{mA}, R_L=100\Omega, -3\text{dB}$		80		kHz
Switching Characteristics						
Rise Time	T_r	$V_{CE}=2\text{V}, I_C=2\text{mA}$		4	18	μs
Fall Time	T_f	$R_L=100\Omega$		3	18	μs



7.Rank Table of CTR


Type	Classification	Current Transfer Ratio (%) (I_C/I_F)		
		$I_F=\pm 5\text{mA}, V_{CE}=5\text{V}, T_A=25^\circ\text{C}$		
		Min	Typ	Max
PC814	A	50	-	150
	B	100	-	300
	None	20	-	300

8.Switching Time Test Circuit






9.1 Typical Characteristic





9.2 Typical Characteristic





10. Solder Reflow Profile

Soldering Precautions

Whether using a soldering iron or reflow soldering, the soldering temperature should be as close as possible to the conditions shown below.


- When reflow soldering Reflow

soldering should be completed within 10 seconds if reflow

soldering does not exceed 260°C. The soldering temperature profile is based on the surface temperature of the plastisol (see the chart below, based on the surface temperature of the plastisol).

Reflow soldering is limited to one or two passes.

It must be used within 2 weeks after unpacking




- Wave soldering

It is recommended to perform one-time soldering under temperature conditions.


Temperature: 260+0/-5°C Time: 10 sec.

Preheat temperature: 25 to 140°C Preheat time: 30 to 80 seconds.





11.1 SOP-4 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	C	D	D1	E
Min	4.30	3.60	0.15	5.00	6.70	0.30	2.54	1.82
Max	4.50	4.10		5.40	7.30	0.50	TYP	2.02



11.2 DIP-4 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	B	b	c	D	D1	E
Min	6.15	4.33	7.37	0.26	7.85	3.40	1.35	2.54
Max	6.65	4.83	7.87		8.80	3.90	1.55	TYP



12.Ordering Information



yy: Year Code
ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW PC814A-S	814A	SOP-4	2000	Tape and reel
UMW PC814A	814A	DIP-4	5000	Tube and box



13.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.