








RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT (TOP VIEW)

THICKNESS 0.60MM; DEFAULT TOLERANCE: ±0.05



SECTION:A-A

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30 X.* ±5°

.XX ±0.20 X.X* ±1°

.XXX ±0.10 X.XX* ±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.

HMT-TYPE-C-24PIN

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:

USB CF 24PIN SMT

CUSTOMER

SIZE UNITS

A4 MM




SCALE

SHEET

N:A 1/1

RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



	REEL	CARTON
CONNECTOR (PCS)	900	9000

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X.°	±5°
.XX	±0.20	X.X°	±1°
.XXX	±0.10	X.XX°	±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司

HMTCONN Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-TYPE-C-24PIN

TITLE:
USB CF 24PIN SMT

DESIGN: James

CHED: Talen

APPD: Sophia

CUSTOMER

SCALE

N:A

SIZE
A4

UNITS
MM

SHEET
1/1