

1.Description

HCPL-2611 are consists of an infrared emitting diode optically coupled to a high speed integrated photo detector logic gate with a strobable output. It is packaged in a 8-pin DIP package and available in wide-lead spacing and SMD options.



3.Applications

- Ground loop elimination
- LSTTL to TTL, LSTTL or 5 volt CMOS
- Line receiver, data transmission
- Data multiplexing


2.Features

- High speed 10Mbit/s
- Guaranteed performance from -40 to 85°C
- Logic gate output
- High isolation voltage between input and output (Viso=5000 Vrms)
- Pb free and RoHS compliant.

4.Pinning Information



DIP-8



SOP- 8

A 0.1μF bypass capacitor must be connected between pins 8 and 5 ^{*3}



5.Truth Table (Positive Logic)

LED	Enable	Output
ON	H	L
OFF	H	H
ON	L	H
OFF	L	H
ON	NC	L
OFF	NC	H

6.Absolute Maximum Ratings $T_A = 25^{\circ}\text{C}$

Parameter		Symbol	Value	Units
Input	Forward current	I_F	20	mA
	Enable input voltage Not exceed V_{CC} by more than 500mV	V_E	$V_{CC}+0.5$	V
	Reverse voltage	V_R	5	V
	Power dissipation	P_D	45	mW
Output	Power dissipation	P_C	85	mW
	Output current	I_O	50	mA
	Output voltage	V_O	7	V
Supply voltage		V_{CC}	7	V
Isolation voltage ^{*1}		V_{ISO}	5000	V_{rms}
Operating temperature		T_{OPR}	-40 to 85	$^{\circ}\text{C}$
Storage temperature		T_{STG}	-55 to 125	$^{\circ}\text{C}$
Soldering temperature ^{*2}		T_{SOL}	260	$^{\circ}\text{C}$

*1 AC for 1 minute, R.H.=40 ~ 60% R.H. In this test, pins 1,2,3 & 4 are shorted together, and pins 5,6,7 & 8 are shorted together.

*2 For 10 seconds.



7. Electrical Characteristics ($T_A=0$ to 70°C unless specified otherwise)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Input						
Forward voltage	V_F	$I_F=10\text{mA}$		1.4	1.8	V
Reverse voltage	V_R	$I_R=10\mu\text{A}$	5			V
Temperature coefficient of forward voltage	$\Delta V_F/\Delta T_A$	$I_F=10\text{mA}$		-1.8		mV/ $^{\circ}\text{C}$
Input capacitance	C_{IN}	$V_F=0$, $f=1\text{MHz}$		60		pF
Output						
High level supply current	I_{CCH}	$I_F=0\text{mA}$, $V_E=0.5\text{V}$, $V_{CC}=5.5\text{V}$		7	9	mA
Low level supply current	I_{CCL}	$I_F=10\text{mA}$, $V_{CC}=5.5\text{V}$, $V_E=0.5\text{V}$		9	12	mA
High level enable current	I_{EH}	$V_E=2\text{V}$, $V_{CC}=5.5\text{V}$		-0.6	-1.5	mA
Low level enable current	I_{EL}	$V_E=0.5\text{V}$, $V_{CC}=5.5\text{V}$		-0.8	-1.5	mA
High level enable voltage	V_{EH}	$I_F=10\text{mA}$, $V_{CC}=5.5\text{V}$	2			V
Low level enable voltage	V_{EL}	$I_F=10\text{mA}$, $V_{CC}=5.5\text{V}$			0.8	V

8. Transfer Characteristics ($T_A=-40$ to 85°C unless specified otherwise)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
HIGH Level Output Current	I_{OH}	$V_{CC}=5.5\text{V}$, $V_O=5.5\text{V}$ $I_F=250\mu\text{A}$, $V_E=2\text{V}$		2.1	100	μA
LOW Level Output Voltage	V_{OL}	$V_{CC}=5.5\text{V}$, $I_F=5\text{mA}$ $V_E=2\text{V}$, $I_{CL}=13\text{mA}$		0.35	0.6	V
Input Threshold Current	I_{FT}	$V_{CC}=5.5\text{V}$, $V_O=0.6\text{V}$ $V_E=2\text{V}$, $I_{OL}=13\text{mA}$		2.5	5	mA



9. Switching Characteristics

($T_A = -40$ to 85°C , $V_{CC} = 5\text{V}$, $I_F = 7.5\text{mA}$ unless specified otherwise)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Propagation delay time to output High level	T_{PHL}	$C_L = 15\text{pF}$, $R_L = 350\Omega$, $T_A = 25^\circ\text{C}$		35	75	ns
Propagation delay time to output Low level	T_{PLH}	$C_L = 15\text{pF}$, $R_L = 350\Omega$, $T_A = 25^\circ\text{C}$		40	75	ns
Pulse width distortion	$ T_{PHL} - T_{PLH} $	$C_L = 15\text{pF}$, $R_L = 350\Omega$		5	35	ns
Output rise time	t_r	$C_L = 15\text{pF}$, $R_L = 350\Omega$		40		ns
Output fall time	t_f	$C_L = 15\text{pF}$, $R_L = 350\Omega$		10		ns
Enable Propagation Delay Time to Output High Level	t_{ELH}	$I_F = 7.5\text{mA}$, $V_{EH} = 3.5\text{V}$, $C_L = 15\text{pF}$, $R_L = 350\Omega$		15		ns
Enable Propagation Delay Time to Output Low Level	t_{EHL}	$I_F = 7.5\text{mA}$, $V_{EH} = 3.5\text{V}$, $C_L = 15\text{pF}$, $R_L = 350\Omega$		15		ns
Common Mode Transient Immunity at Logic High	$ CM_H $	$I_F = 0\text{mA}$, $V_{OH} = 2\text{V}$, $R_L = 350\Omega$ $T_A = 25^\circ\text{C}$, $V_{CM} = 50\text{Vp-p}$	2000			V/ μS
Common Mode Transient Immunity at Logic Low	$ CM_L $	$I_F = 7.5\text{mA}$, $V_{OL} = 0.8\text{V}$, $R_L = 350\Omega$ $T_A = 25^\circ\text{C}$, $V_{CM} = 50\text{Vp-p}$	2000			V/ μS



10.1 Typical Characteristic




Figure 1: Input Diode Forward Voltage vs. Forward Current




Figure 2: Low Level Output Voltage vs. Ambient Temperature




Figure 3: Low Level Output Current vs. Ambient Temperature




Figure 4: Input Threshold Current vs. Ambient Temperature




Figure 5: Output Voltage vs. Input Forward Current




Figure 6: High Level Output Current vs. Temperature



10.2 Typical Characteristic




Figure 7: Switching Time vs. Forward Current




Figure 8: Switching Time vs. Temperature




Figure 9: Pulse Width Distortion vs. Temperature




Figure 10: Rise and Fall Time vs. Temperature








Figure 11: Enable Propagation Delay vs. Temperature





11. Test circuit



Test circuit and waveforms for t_{PHL} , t_{PLH} , t_r , and t_f




Test circuit and waveform for t_{EHL} and t_{ELH}




Test circuit Common mode Transient Immunity



12. Recommended Drive Circuit For EL for High-CMR



13. Precautions for Use



1. Soldering Condition


1.1 (A) Maximum Body Case Temperature Profile for evaluation of Reflow Profile



Preheat	
Temperature min (T_{smin})	150°C
Temperature max (T_{smax})	200°C
Time (T_{smin} to T_{smax}) (ts)	60-120 seconds
Average ramp-up rate (T_{smax} to T_p)	3°C/second max
Other	
Liquidus Temperature (T_L)	216°C
Time above Liquidus Temperature (t_L)	60-100 sec
Peak Temperature (T_p)	260°C
Time within 5°C of Actual Peak Temperature: $T_p - 5^\circ\text{C}$	30s
Ramp- Down Rate from Peak Temperature	6°C /second max
Time 25°C to peak temperature	8 minutes max
Reflow times	3 times



14.1 DIP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	B1	C	D	D1
Min	6.30	9.46	7.62	0.25	5°	0.40	2.54	4.20
Max	6.90	10.06	TYP.		15°	0.60	TYP.	4.80



14.2 SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	B1	B2	C	D	D1	E
Min	6.30	1.45	9.46	7.62	0.25	0.6	-	2.54	3.20	4.00
Max	6.90		10.06	TYP		-	10.3	TYP	3.80	4.60



15.Ordering Information



yy: Year Code
ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW HCPL-2611-000E	2611	DIP-8	2250	Tube and box
UMW HCPL-2611-500E	2611	SOP-8	1000	Tape and reel



16.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.