




REV.	REVISION DESCRIPTION	DATE	APPD











PCB LAYOUT

NOTES

Available in 02 through 20 Circuits.

Mates with SH-Y/SH-YF Series Housing.

Material : LCP UL94V-0.

Material : Phosphor Bronze.

Finish : Over Ni;Tin-plated.

序号	图号	名称	材料	数量	附件
3	③	基座	LCP	1	UL94V-0
2	②	焊片	磷青铜	2	镀锡
1	①	接触件	磷青铜	N*	镀锡

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	SH-2AB	1.0	4.0	2.6	10	SH-10AB	9.0	12.0	10.6
3	SH-3AB	2.0	5.0	3.6	11	SH-11AB	10.0	13.0	11.6
4	SH-4AB	3.0	6.0	4.6	12	SH-12AB	11.0	14.0	12.6
5	SH-5AB	4.0	7.0	5.6	13	SH-13AB	12.0	15.0	13.6
6	SH-6AB	5.0	8.0	6.6	14	SH-14AB	13.0	16.0	14.6
7	SH-7AB	6.0	9.0	7.6	15	SH-15AB	14.0	17.0	15.6
8	SH-8AB	7.0	10.0	8.6	–	–	–	–	–
9	SH-9AB	8.0	11.0	9.6	20	SH-20AB	19.0	22.0	20.6


GENERAL TOLERANCES (UNLESS SPECIFIED)


.X: ± 0.25	X° : ± 3.0°
.XX: ± 0.15	.X° : ± 2.0°
.XXX: ± 0.01	.XX° : ± 1.0°
FINISH:	
DRAWING NO:	


浙 江 德 利 接 插 件 有 限 公 司
ZHE JIANG DELI CONNECTORS CO .,LTD


PRODUCT NAME: SH-AB		TITLE: 1.0mm Pitch Wire To Board SMT Wafer
DR:Chen Quan Long	DATE:20.12.31	PART NO:
CHKD: Wu Hui	DATE:20.12.31	SCALE: N/A / PAGE: 1/1
APPD:Ren An De	DATE:20.12.31	UNITS: mm / REV.: A


REV.	REVISION DESCRIPTION	DATE	APPD











PCB LAYOUT

NOTES

Available in 02 through 05 Circuits.

Mates with SH-Y/SH-YF Series Housing.

Material : LCP UL94V-0.

Material : Phosphor Bronze.

Finish : Over Ni;Tin-plated.

序号	图号	名称	材料	数量	附件
3	③	基座	LCP	1	UL94V-0
2	②	焊片	磷青铜	2	镀锡
1	①	接触件	磷青铜	N*	镀锡

Circuits	Product name	Dimension mm		
		A	B	C
2	SH-2AB-02	1.0	4.0	2.6
3	SH-3AB-02	2.0	5.0	3.6
4	SH-4AB-02	3.0	6.0	4.6
5	SH-5AB-02	4.0	7.0	5.6

GENERAL TOLERANCES (UNLESS SPECIFIED)

.X: ± 0.25	X° : ± 3.0°
.XX: ± 0.15	.X° : ± 2.0°
.XXX:± 0.01	.XX° :± 1.0°


FINISH:


DRAWING NO:


浙 江 德 利 接 插 件 有 限 公 司
ZHE JIANG DELI CONNECTORS CO .,LTD


PRODUCT NAME: SH-AB-02		TITLE: 1.0mm Pitch Wire To Board SMT Wafer
DR:Chen Quan Long	DATE:20.12.31	PART NO:
CHKD: Wu Hui	DATE:20.12.31	SCALE: N/A / PAGE: 1/1
APPD:Ren An De	DATE:20.12.31	UNITS: mm / REV.: A


REV.	REVISION DESCRIPTION	DATE	APPD











PCB LAYOUT

NOTES

Available in 02 through 20 Circuits.

Mates with SH-Y/SH-YF Series Housing.

Material :LCP UL94V-0.

Material : Phosphor Bronze.

Finish : Over Ni;Tin-plated.

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	SH-2AWB	1.0	4.0	2.6	10	SH-10AWB	9.0	12.0	10.6
3	SH-3AWB	2.0	5.0	3.6	11	SH-11AWB	10.0	13.0	11.6
4	SH-4AWB	3.0	6.0	4.6	12	SH-12AWB	11.0	14.0	12.6
5	SH-5AWB	4.0	7.0	5.6	13	SH-13AWB	12.0	15.0	13.6
6	SH-6AWB	5.0	8.0	6.6	14	SH-14AWB	13.0	16.0	14.6
7	SH-7AWB	6.0	9.0	7.6	15	SH-15AWB	14.0	17.0	15.6
8	SH-8AWB	7.0	10.0	8.6	-	-	-	-	-
9	SH-9AWB	8.0	11.0	9.6	20	SH-20AWB	19.0	22.0	20.6

序号	图号	名称	材料	数量	附件
3	③	基座	LCP	1	UL94V-0
2	②	焊片	磷青铜	2	镀锡
1	①	接触件	磷青铜	N*	镀锡

GENERAL TOLERANCES (UNLESS SPECIFIED)

.X: ± 0.25	X° : ± 3.0°
.XX: ± 0.15	.X° : ± 2.0°
.XXX:± 0.01	.XX° :± 1.0°

FINISH:

DRAWING NO:

浙 江 德 利 接 插 件 有 限 公 司
ZHE JIANG DELI CONNECTORS CO .,LTD

PRODUCT NAME: SH-AWB

TITLE: 1.0mm Pitch Wire To Board SMT Wafer


DR:Chen Quan Long	DATE:20.12.31
CHKD: Wu Hui	DATE:20.12.31
APPD:Ren An De	DATE:20.12.31

PART NO:

SCALE: N/A PAGE: 1/1

UNITS: mm REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD



NOTES


Available in 02 through 05 Circuits.


Mates with SH-Y/SH-YF Series Housing.


Material :LCP UL94V-0.


Material : Phosphor Bronze.

Finish : Over Ni;Tin-plated.









PCB LAYOUT

序号	图号	名称	材料	数量	附件
3	③	基座	LCP	1	UL94V-0
2	②	焊片	磷青铜	2	镀锡
1	①	接触件	磷青铜	N*	镀锡

Circuits	Product name	Dimension mm		
		A	B	C
2	SH-2AWB-02	1.0	4.0	2.6
3	SH-3AWB-02	2.0	5.0	3.6
4	SH-4AWB-02	3.0	6.0	4.6
5	SH-5AWB-02	4.0	7.0	5.6


GENERAL TOLERANCES (UNLESS SPECIFIED)


.X: ± 0.25	X° : ± 3.0°
.XX: ± 0.15	.X° : ± 2.0°
.XXX:± 0.01	.XX° :± 1.0°
FINISH:	
DRAWING NO:	


浙 江 德 利 接 插 件 有 限 公 司
ZHE JIANG DELI CONNECTORS CO .,LTD


PRODUCT NAME: SH-AWB-02		TITLE: 1.0mm Pitch Wire To Board SMT Wafer
DR:Chen Quan Long	DATE:20.12.31	PART NO:
CHKD: Wu Hui	DATE:20.12.31	SCALE: N/A / PAGE: 1/1
APPD:Ren An De	DATE:20.12.31	UNITS: mm / REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD









NOTES

Available in 02 through 20 Circuits.

Match with SH series housing.


Material : PBT UL94V-0.

Accepts SH-T Crimp Terminal.

Circuits	Type	Dimension mm			Circuits	Type	Dimension mm		
		A	B	C			A	B	C
2	SH-2Y	1.0	5.0	2.4	10	SH-10Y	9.0	13.0	10.4
3	SH-3Y	2.0	6.0	3.4	11	SH-11Y	10.0	14.0	11.4
4	SH-4Y	3.0	7.0	4.4	12	SH-12Y	11.0	15.0	12.4
5	SH-5Y	4.0	8.0	5.4	13	SH-13Y	12.0	16.0	13.4
6	SH-6Y	5.0	9.0	6.4	14	SH-14Y	13.0	17.0	14.4
7	SH-7Y	6.0	10.0	7.4	15	SH-15Y	14.0	18.0	15.4
8	SH-8Y	7.0	11.0	8.4	–	–	–	–	–
9	SH-9Y	8.0	12.0	9.4	20	SH-16Y	19.0	23.0	16.4

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SH-Y		TITLE: 1.0 mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE:19/08/01	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A / PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:19/08/01	UNITS: mm / REV.: A
DRAWING NO:				

REV.	REVISION DESCRIPTION	DATE	APPD




NOTES


Available in 02 through 20 Circuits.

Match with SH series housing.

Material : PBT UL94V-0.

Accepts SH-T Crimp Terminal.





Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	SH-2YF	1.0	3.0	2.4	10	SH-10YF	9.0	11.0	10.4
3	SH-3YF	2.0	4.0	3.4	11	SH-11YF	10.0	12.0	11.4
4	SH-4YF	3.0	5.0	4.4	12	SH-12YF	11.0	13.0	12.4
5	SH-5YF	4.0	6.0	5.4	13	SH-13YF	12.0	14.0	13.4
6	SH-6YF	5.0	7.0	6.4	14	SH-14YF	13.0	15.0	14.4
7	SH-7YF	6.0	8.0	7.4	15	SH-15YF	14.0	16.0	15.4
8	SH-8YF	7.0	9.0	8.4	–	–	–	–	–
9	SH-9YF	8.0	10.0	9.4	20	SH-16YF	19.0	21.0	16.4

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SH-YF		TITLE: 1.0 mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE:19/08/01	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A / PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:19/08/01	UNITS: mm / REV.: A
DRAWING NO:				

REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in SH-Y or
SH-YF Series Housing.

Accepts AWG #32～28 Wire Range.
0.032～ 0.08 mm^2 .


Insulation O.D.=0.4～0.8 mm.


Material : Phosphor Bronze .


Finish: Tin plated.

Qty/Reel: 15,000 PCS.


Thickness: 0.12 mm.








SECTION A-A



SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SH-T		TITLE: 1.0mm Pitch Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE:19/08/01	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A	PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:19/08/01	UNITS: mm	REV.: A
DRAWING NO:					