



## Features

- Wide bandgap SiC MOSFET technology
- Low On-Resistance with High Blocking Voltage
- Low Capacitances with High-Speed switching
- Low reverse recovery(Qrr)
- Halogen free, RoHs compliant

## Benefits


- Reduce switching losses
- Increased system Switching Frequency
- Increased power density
- Reduction of heat sink requirements

## Applications


- Switch mode power supplies
- Renewable energy
- On Board Charger
- High Voltage DC/DC Converters



| Ordering Part Number | Package    | Brand      |
|----------------------|------------|------------|
| NTH4L023N065M3S      | TO-247H-4L | HXY MOSFET |



TO-247H-4L



## Maximum Ratings ( $T_c = 25^\circ\text{C}$ unless otherwise specified)

| Symbol        | Parameter                      | Test conditions                                   | Value            | Unit             | Note    |
|---------------|--------------------------------|---------------------------------------------------|------------------|------------------|---------|
| $V_{DSmax}$   | Drain-Source Voltage           | $V_{GS} = 0V, I_D = 100\mu A$                     | 750              | V                |         |
| $V_{GSmax}$   | Gate-Source voltage            | AC ( $f > 1\text{ Hz}$ )                          | -10/+25          | V                |         |
| $V_{GSop}$    | Recommend Gate-Source Voltage  | Static                                            | -4/+15<br>-4/+18 | V                |         |
| $I_D$         | Continuous Drain current       | $V_{GS} = 18V, T_c = 25^\circ\text{C}$            | 108              | A                | Fig. 14 |
|               |                                | $V_{GS} = 18V, T_c = 100^\circ\text{C}$           | 76               |                  |         |
| $I_{D,pulse}$ | Pulsed Drain Current           | Pulse with $t_p$ limited by $T_{jmax}$            | 193              | A                |         |
| $P_D$         | Power Dissipation              | $T_c = 25^\circ\text{C}, T_j = 175^\circ\text{C}$ | 341              | W                | Fig.16  |
| $T_j$         | Operating junction temperature |                                                   | -55~175          | $^\circ\text{C}$ |         |
| $T_{stg}$     | Storage temperature            |                                                   | -55~175          | $^\circ\text{C}$ |         |
|               | TO-247 miunting torque         | M3 Screw                                          | 0.7              | Nm               |         |



### Thermal Characteristics

| Symbol       | Parameter                                   | Value |      |      | Unit | Note    |
|--------------|---------------------------------------------|-------|------|------|------|---------|
|              |                                             | Min.  | Typ. | Max. |      |         |
| $R_{th(jc)}$ | Thermal resistance from Junction to Case    |       | 0.44 |      | K/W  | Fig. 15 |
| $R_{th(ja)}$ | Thermal resistance from Junction to Ambient |       | 40   |      | K/W  |         |

### Electrical Characteristics (T<sub>c</sub> = 25°C unless other wise specified)

#### Static Characteristics

| Symbol        | Parameter                        | Test conditions                                                                              | Value |          |      | Unit       | Note         |
|---------------|----------------------------------|----------------------------------------------------------------------------------------------|-------|----------|------|------------|--------------|
|               |                                  |                                                                                              | Min.  | Typ.     | Max. |            |              |
| $V_{(BR)DSS}$ | Drain-Source Breakdown voltage   | $V_{GS} = 0V, I_D = 100\mu A$                                                                | 750   |          |      | V          |              |
| $V_{GS(th)}$  | Gate Threshold voltage           | $V_{GS} = V_{DS}, I_D = 20mA$                                                                |       | 2.6      |      | V          | Fig. 9       |
|               |                                  | $V_{GS} = V_{DS}, I_D = 20mA, T_j = 175^\circ C$                                             |       | 1.8      |      |            |              |
| $I_{GSS}$     | Gate-Source Leakage current      | $V_{GS} = 18V, V_{DS} = 0V$                                                                  |       |          | 250  | nA         |              |
| $I_{DSS}$     | Zero Gate Voltage Drain Current  | $V_{DS} = 750V, V_{GS} = 0V, T_j = 25^\circ C$                                               |       | 1        | 50   | $\mu A$    |              |
| $R_{DS(on)}$  | Drain-Source On-state Resistance | $V_{GS} = 15V, I_D = 40A$                                                                    |       | 25       |      | m $\Omega$ | Fig. 3, 4, 5 |
|               |                                  | $V_{GS} = 18V, I_D = 40A$                                                                    |       | 20       | 30   |            |              |
|               |                                  | $V_{GS} = 15V, I_D = 40A, T_j = 175^\circ C$<br>$V_{GS} = 18V, I_D = 40A, T_j = 175^\circ C$ |       | 30<br>28 |      |            |              |
| $g_{fs}$      | Transconductance                 | $V_{DS} = 15V, I_D = 40A$                                                                    |       | 25       |      | S          | Fig. 6       |
|               |                                  | $V_{DS} = 15V, I_D = 40A, T_j = 175^\circ C$                                                 |       | 25       |      |            |              |



### Gate Charge Characteristics

| Symbol   | Parameter             | Test conditions                                      | Value |      |      | Unit | Note    |
|----------|-----------------------|------------------------------------------------------|-------|------|------|------|---------|
|          |                       |                                                      | Min.  | Typ. | Max. |      |         |
| $Q_{GS}$ | Gate to Source Charge | $V_{DS} = 400V$<br>$I_D = 40A$<br>$V_{GS} = -4V/18V$ |       | 35   |      | nC   | Fig. 10 |
| $Q_{GD}$ | Gate to Drain Charge  |                                                      |       | 17   |      |      |         |
| $Q_G$    | Total Gate Charge     |                                                      |       | 142  |      |      |         |

### AC Characteristics

| Symbol       | Parameter                    | Test conditions                                                       | Value |      |      | Unit     | Note    |
|--------------|------------------------------|-----------------------------------------------------------------------|-------|------|------|----------|---------|
|              |                              |                                                                       | Min.  | Typ. | Max. |          |         |
| $C_{iss}$    | Input Capacitance            | $V_{GS} = 0V, V_{DS} = 600V$<br>$f = 1\text{ MHz}$<br>$V_{AC} = 25mV$ |       | 2935 |      | pF       | Fig. 13 |
| $C_{oss}$    | Output Capacitance           |                                                                       |       | 221  |      | pF       |         |
| $C_{rss}$    | Reverse Transfer Capacitance |                                                                       |       | 16.6 |      | pF       |         |
| $R_{G(int)}$ | Internal Gate Resistance     | $f = 1\text{ MHz}, V_{AC} = 25mV$                                     |       | 1.2  |      | $\Omega$ |         |



### Reverse Diode Characteristics

| Symbol         | Parameter                        | Test conditions                                                  | Value |      |      | Unit | Note     |
|----------------|----------------------------------|------------------------------------------------------------------|-------|------|------|------|----------|
|                |                                  |                                                                  | Min.  | Typ. | Max. |      |          |
| $V_{SD}$       | Diode Forward Voltage            | $V_{GS} = -4V, I_{SD} = 20A$                                     |       | 3.7  |      | V    | Fig. 7,8 |
|                |                                  | $V_{GS} = -4V, I_{SD} = 20A, T_J = 175^{\circ}C$                 |       | 3.2  |      |      |          |
| $I_S$          | Continuous Diode Forward Current | $V_{GS} = -4V, T_C = 25^{\circ}C$                                |       | 81   |      | A    |          |
| $I_{S, pulse}$ | Diode pulse Current              | $V_{GS} = -4V$ , pulse width $t_p$ limited by $T_{jmax}$         |       | 193  |      | A    |          |
| $t_{rr}$       | Reverse Recovery Time            | $V_{GS} = -4V, I_{SD} = 40A, V_R = 400V$<br>$diff/dt = 3800A/us$ |       | 16   |      | nS   |          |
| $Q_{rr}$       | Reverse Recovery Charge          |                                                                  |       | 184  |      | nC   |          |
| $I_{rm}$       | Peak Reverse Recovery Current    |                                                                  |       | 27   |      | A    |          |

### Switching Characteristics

| Symbol       | Parameter              | Test conditions                                                                          | Value |      |      | Unit    | Note   |
|--------------|------------------------|------------------------------------------------------------------------------------------|-------|------|------|---------|--------|
|              |                        |                                                                                          | Min.  | Typ. | Max. |         |        |
| $t_{d(on)}$  | Turn-On Delay Time     | $V_{DS} = 400V, V_{GS} = -4/+18V$<br>$I_D = 40A, R_{G(ext)} = 5\Omega$<br>$L = 200\mu H$ |       | 3    |      | nS      | Fig.21 |
| $t_r$        | Rise Time              |                                                                                          |       | 18   |      | nS      |        |
| $t_{d(off)}$ | Turn-Off Delay Time    |                                                                                          |       | 24   |      | nS      |        |
| $t_f$        | Fall Time              |                                                                                          |       | 5    |      | nS      |        |
| $E_{on}$     | Turn-On Energy         |                                                                                          |       | 58   |      | $\mu J$ | Fig.19 |
| $E_{off}$    | Turn-Off Energy        |                                                                                          |       | 65   |      | $\mu J$ |        |
| $E_{tot}$    | Total switching energy |                                                                                          |       | 123  |      | $\mu J$ |        |



## Typical Performance




Figure 1. Output characteristics at  $T_j=25^\circ\text{C}$




Figure 2. Output characteristics at  $T_j=175^\circ\text{C}$




Figure 3. Normalized On-Resistance vs. Temperature




Figure 4. On-Resistance vs. Drain current for Various Temperature




Figure 5. On-Resistance vs. Temperature for Various Gate Voltage




Figure 6. Transfer Characteristics for Various Junction Temperatures




Figure 7. Body Diode Characteristics at  $T_j=25$ °C




Figure 8. Body Diode Characteristics at  $T_j=175$ °C




Figure 9. Threshold Voltage vs. Temperature




Figure 10 Gate Charge Characteristics




Figure 11. 3rd Quadrant Characteristic at  $T_J=25\text{ °C}$




Figure 12. 3rd Quadrant Characteristic at  $T_J=175\text{ °C}$




Figure 13. Capacitances vs. Drain-Source Voltage (0 – 600V)




Figure 14. Continuous Drain Current Derating vs Case Temperature




Figure 15. Transient Thermal Impedance (Junction – Case)




Figure 16. Maximum Power Dissipation Derating vs. Case Temperature






Figure 17. Output Capacitor Stored Energy




Figure 18. Safe Operating Area




Figure 19. Clamped Inductive Switching Energy vs. Drain Current( $V_{DD} = 400V$ )




Figure 20. Clamped Inductive Switching Energy vs.  $R_{G(ext)}$






Figure 21. Switching Times vs.  $R_{G(\text{ext})}$



## Package Dimensions

Package TO-247H-4L



SECTION "F-F", "G-G" AND "H-H"  
SCALE: NONE




NOTE ;

1. ALL METAL SURFACES: TIN PLATED, EXCEPT AREA OF CUT
2. DIMENSIONING & TOLERANCEING CONFIRM TO  
ASME Y14.5M-1994.
3. ALL DIMENSIONS ARE IN MILLIMETERS.  
ANGLES ARE IN DEGREES.
4. 'N' IS THE NUMBER OF TERMINAL POSITIONS

| SYM | MILLIMETERS |       |
|-----|-------------|-------|
|     | MIN         | MAX   |
| A   | 4.83        | 5.21  |
| A1  | 2.29        | 2.54  |
| A2  | 1.91        | 2.16  |
| b`  | 1.07        | 1.28  |
| b   | 1.07        | 1.33  |
| b1  | 2.39        | 2.94  |
| b2  | 2.39        | 2.84  |
| b3  | 1.07        | 1.60  |
| b4  | 1.07        | 1.50  |
| b5  | 2.39        | 2.69  |
| b6  | 2.39        | 2.64  |
| b7  | 1.30        | 1.70  |
| c`  | 0.55        | 0.65  |
| c   | 0.55        | 0.68  |
| D   | 23.30       | 23.60 |
| D1  | 16.25       | 17.65 |
| D2  | 0.95        | 1.25  |
| E   | 15.75       | 16.13 |

| SYM | MILLIMETERS |       |
|-----|-------------|-------|
|     | MIN         | MAX   |
| E1  | 13.10       | 14.15 |
| E2  | 3.68        | 5.10  |
| E3  | 1.00        | 1.90  |
| E4  | 12.38       | 13.43 |
| e   | 2.54 BSC    |       |
| e1  | 5.08 BSC    |       |
| N*  | 4           |       |
| L   | 17.31       | 17.82 |
| L1  | 3.97        | 4.37  |
| L2  | 2.35        | 2.65  |
| Ø P | 3.51        | 3.65  |
| Q   | 5.49        | 6.00  |
| S   | 6.04        | 6.30  |
| T   | 17.5° REF.  |       |
| W   | 3.5° REF.   |       |
| X   | 4° REF.     |       |





### **Attention**

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.