

RoHS		2	3	4	5	6	7	8	9																																																																																
								<table border="1"><thead><tr><th>序号 (NO.)</th><th>品名 (Name)</th><th>材质 (Material)</th></tr></thead><tbody><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(Ø=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></tbody></table>		序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(Ø=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																				
序号 (NO.)	品名 (Name)	材质 (Material)																																																																																							
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(Ø=5.2)	LCP UL94V-0 本色 Natural																																																																																							
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																							
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																							
								技术指标(Technical Index): - 温度范围(Temperature range): -40°C~+ 105 ° C. - 额定电压(Rated voltage): 200V, AC. - 额定电流(Rated Current):2A AC/DC - 接触电阻(Contact resistance): ≤20mΩ - 绝缘电阻(Insulation resistance): ≥1000MΩ. - 产品料号(Product material No.):																																																																																	
								<table border="1"><thead><tr><th>CKT</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr></thead><tbody><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></tbody></table>		CKT	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00
CKT	DIM A	DIM B	DIM C																																																																																						
2	2.00	4.90	8.00																																																																																						
3	4.00	6.90	10.00																																																																																						
4	6.00	8.90	12.00																																																																																						
5	8.00	10.90	14.00																																																																																						
6	10.00	12.90	16.00																																																																																						
7	12.00	14.90	18.00																																																																																						
8	14.00	16.90	20.00																																																																																						
9	16.00	18.90	22.00																																																																																						
10	18.00	20.90	24.00																																																																																						
11	20.00	22.90	26.00																																																																																						
12	22.00	24.90	28.00																																																																																						
13	24.00	26.90	30.00																																																																																						
14	26.00	28.90	32.00																																																																																						
15	28.00	30.90	34.00																																																																																						
16	30.00	32.90	36.00																																																																																						
17	32.00	34.90	38.00																																																																																						
18	34.00	36.90	40.00																																																																																						
19	36.00	38.90	42.00																																																																																						
20	38.00	40.90	44.00																																																																																						
		2 PIN 结构样式 (Structural style) 3 PIN 结构样式 (Structural style)																																																																																							
				OPERATION		DRAW		SCALE FIT																																																																																	
				X.X ±0.30		CHECK		UNIT mm																																																																																	
				X.XX ±0.20				SIZE A4																																																																																	
				X.XXX ±0.10				SHEET 1/1																																																																																	
				Angle ±3°		APPROVE		TITLE:																																																																																	
				DIM TOL				PART NO. 1130300242																																																																																	
								HY-AWR																																																																																	

[illegible][illegible]

- | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-------------|--|--|-------|--|-------|------|-------|-----------|--|-------------|--------------|------------------|----------------|---|---------------------------|---------|--|--|------|--|--|------|------|-------|------|-------|-------|-------|---|-------|-------|-------|----|------------|-------------|-------|---|-------|-------|-------|------|-------|----------|------------|-----|-------|--------------------------|-------|--------|-------|-------|---------|-------|-------|--------|---------|----|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|
| | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| G | RoHS | | | | | | | | <table><tr><td>序号
(NO.)</td><td>品名
(Name)</td><td>材质
(Material)</td></tr><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯
2.00 Pitch R/A Wire To Board Housing(H=5.2)</td><td>LCP UL94V-0
本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子
2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡
Copper Alloy/
Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片
2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡
Copper Alloy/
Tin Plating</td></tr></table> | 序号
(NO.) | 品名
(Name) | 材质
(Material) | ① | 2.00 F型卧式2代WTB胶芯
2.00 Pitch R/A Wire To Board Housing(H=5.2) | LCP UL94V-0
本色 Natural | ② | 2.00 F型卧式2代WTB端子
2.00 Pitch R/A Wire To Board Terminal(H=5.2) | 铜合金/表面镀锡
Copper Alloy/
Tin Plating | ③ | 2.00 F型卧式WTB焊片
2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6) | 铜合金/表面镀锡
Copper Alloy/
Tin Plating | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 序号
(NO.) | 品名
(Name) | 材质
(Material) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ① | 2.00 F型卧式2代WTB胶芯
2.00 Pitch R/A Wire To Board Housing(H=5.2) | LCP UL94V-0
本色 Natural | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ② | 2.00 F型卧式2代WTB端子
2.00 Pitch R/A Wire To Board Terminal(H=5.2) | 铜合金/表面镀锡
Copper Alloy/
Tin Plating | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ③ | 2.00 F型卧式WTB焊片
2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6) | 铜合金/表面镀锡
Copper Alloy/
Tin Plating | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| F | <p>0.5±0.03(SQ) 2.00±0.15(PITCH)</p> <p>DIM A ±0.2
DIM B ±0.15
DIM C ±0.2</p> <p>2 PIN 结构样式
(Structural style)</p> <p>3 PIN 结构样式
(Structural style)</p> <p>适用线路板(PCB LAYOUT)</p> | | | 技术指标(Technical Index):
1. 温度范围(Temperature range): -40° C~+ 105° C.
2. 额定电压(Rated voltage): 200V, AC.
3. 额定电流(Rated Current): 2A AC/DC
4. 接触电阻(Contact resistance): ≤20mΩ
5. 绝缘电阻(Insulation resistance): ≥1000MΩ.
6. 产品料号(Product material No.): | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| E | | | | <table><tr><td>CKT</td><td>DIM A</td><td>DIM B</td><td>DIM C</td></tr><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></table> | | | | | CKT | DIM A | DIM B | DIM C | 2 | 2.00 | 4.90 | 8.00 | 3 | 4.00 | 6.90 | 10.00 | 4 | 6.00 | 8.90 | 12.00 | 5 | 8.00 | 10.90 | 14.00 | 6 | 10.00 | 12.90 | 16.00 | 7 | 12.00 | 14.90 | 18.00 | 8 | 14.00 | 16.90 | 20.00 | 9 | 16.00 | 18.90 | 22.00 | 10 | 18.00 | 20.90 | 24.00 | 11 | 20.00 | 22.90 | 26.00 | 12 | 22.00 | 24.90 | 28.00 | 13 | 24.00 | 26.90 | 30.00 | 14 | 26.00 | 28.90 | 32.00 | 15 | 28.00 | 30.90 | 34.00 | 16 | 30.00 | 32.90 | 36.00 | 17 | 32.00 | 34.90 | 38.00 | 18 | 34.00 | 36.90 | 40.00 | 19 | 36.00 | 38.90 | 42.00 | 20 | 38.00 | 40.90 | 44.00 |
| CKT | | | | | | | | | DIM A | DIM B | DIM C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 2.00 | 4.90 | 8.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 4.00 | 6.90 | 10.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 6.00 | 8.90 | 12.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 8.00 | 10.90 | 14.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 10.00 | 12.90 | 16.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 12.00 | 14.90 | 18.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 14.00 | 16.90 | 20.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 16.00 | 18.90 | 22.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 18.00 | 20.90 | 24.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 11 | 20.00 | 22.90 | 26.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 12 | 22.00 | 24.90 | 28.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 13 | 24.00 | 26.90 | 30.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 14 | 26.00 | 28.90 | 32.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 15 | 28.00 | 30.90 | 34.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 16 | 30.00 | 32.90 | 36.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 17 | 32.00 | 34.90 | 38.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 18 | 34.00 | 36.90 | 40.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 19 | 36.00 | 38.90 | 42.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 20 | 38.00 | 40.90 | 44.00 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| D | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| B | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| A | <table><tr><td></td><td></td><td></td><td></td><td colspan="2">OPERATION</td><td rowspan="4">DRAW</td><td rowspan="4">SCALE</td><td rowspan="4">FIT</td><td colspan="2" rowspan="4">深圳市连盛精密连接器有限公司</td></tr><tr><td></td><td></td><td></td><td></td><td>X.X</td><td>±0.30</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XX</td><td>±0.20</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XXX</td><td>±0.10</td></tr><tr><td>A0</td><td>2012.04.18</td><td colspan="2">NEW DRAWING</td><td></td><td>Angle</td><td>±3'</td><td rowspan="2">CHECK</td><td rowspan="2">SIZE</td><td rowspan="2">A4</td><td rowspan="2">PART NO.</td><td rowspan="2">1130300242</td></tr><tr><td>REV</td><td>DATE</td><td colspan="2">MODIFICATION DESCRIPTION</td><td>CHANGE</td><td>DIM</td><td>TOL</td><td rowspan="2">APPROVE</td><td rowspan="2">SHEET</td><td rowspan="2">1/1</td><td rowspan="2">TITLE:</td><td rowspan="2">HY-NAWR</td></tr><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td></tr></table> | | | | | | | OPERATION | | DRAW | SCALE | FIT | 深圳市连盛精密连接器有限公司 | | | | | | X.X | ±0.30 | | | | | X.XX | ±0.20 | | | | | X.XXX | ±0.10 | A0 | 2012.04.18 | NEW DRAWING | | | Angle | ±3' | CHECK | SIZE | A4 | PART NO. | 1130300242 | REV | DATE | MODIFICATION DESCRIPTION | | CHANGE | DIM | TOL | APPROVE | SHEET | 1/1 | TITLE: | HY-NAWR | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | | | | | | | | | | | | | | | | | | | | | | | |
| | | | | OPERATION | | DRAW | SCALE | FIT | 深圳市连盛精密连接器有限公司 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | | X.X | ±0.30 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | | X.XX | ±0.20 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | | X.XXX | ±0.10 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| A0 | 2012.04.18 | NEW DRAWING | | | Angle | ±3' | CHECK | SIZE | A4 | PART NO. | 1130300242 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| REV | DATE | MODIFICATION DESCRIPTION | | CHANGE | DIM | TOL | | | | | | APPROVE | SHEET | 1/1 | TITLE: | HY-NAWR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

[illegible][illegible]