

Part No	CKT	A	B
XH2.54-2PZZ-MR	2	2.5	7.5
XH2.54-3PZZ-MR	3	5.0	10.0
XH2.54-4PZZ-MR	4	7.5	12.5
XH2.54-5PZZ-MR	5	10.0	15.0
XH2.54-6PZZ-MR	6	12.5	17.5
XH2.54-7PZZ-MR	7	15.0	20.0
XH2.54-8PZZ-MR	8	17.5	22.5
XH2.54-9PZZ-MR	9	20.0	25.0
XH2.54-10PZZ-MR	10	22.5	27.5
XH2.54-11PZZ-MR	11	25.0	30.0
XH2.54-12PZZ-MR	12	27.5	32.5
XH2.54-13PZZ-MR	13	30.0	35.0
XH2.54-14PZZ-MR	14	32.5	37.5
XH2.54-15PZZ-MR	15	35.0	40.0
XH2.54-16PZZ-MR	16	37.5	42.5


常规2 Pin样式

SECTION A-A



技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V,AC.
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



序号	品名	材质
①	XH2.5直针WTB胶芯	LCP UL94V-0 米色 白色
②	XH2.5直针WTB端子	铜合金/表面镀锡
③	XH2.5立式吸盖	LCP UL94V-0 米色



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: XH2.5直针WTB	
DECIMALS:	ANGLES:	PAR	XH2.54-NPZZ-MR
X.: ± 0.50	$\pm 1^{\circ}$	DWN	Lucas
X.X: ± 0.20		CHKD	Ethan
X.XX: ± 0.10		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32



CKT (2.5mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)
2	24	500	10	5000
3				
4				
5				
6	32	500	8	4000
7	44	500	6	3000
8				
9				
10				
11				
12	56	500	5	2500
13				
14				
15				
16				

CKT (2.5mm pitch)	B0	W	F	S
2	7.80	24	11.50±0.10	
3	10.30			
4	12.80			
5	15.30	32	14.20±0.10	28.40
6	17.80			
7	20.30			
8	22.80	44	20.20±0.10	40.40
9	25.30			
10	27.80			
11	30.30			
12	32.80	56	26.2±0.10	52.40
13	35.30			
14	37.80			
15	40.30			
16	42.80			

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: XH2.5直针WTB 载带包装规格		
			PAR	XH2.54-NPZZ-MR	
DWN	Lucas				
CHKD	Ethan				
APVD	Jacob				
X.X:±0.50 ±1°				SCALE:1:1	UNIT:MM
X.X:±0.20					
X.XX:±0.10					
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A