

STGWA15H120DF2-VB Datasheet

1200V Trench and Fieldstop IGBT



RoHS
COMPLIANT
HALOGEN
FREE

PRODUCT SUMMARY		
V_{CE} (V)	1200	
I_C (A)	50 ($T_C=25^\circ\text{C}$)	25 ($T_C=100^\circ\text{C}$)
$V_{CE(sat)}$ (V)	1.7	
I_{CM} (A)	75	

FEATURES

- Very Low V_{CEsat}
- Low turn-off losses
- High speed switching
- Maximum junction temperature 175°C
- Ultra low gate charge (Q_g)
- Avalanche energy rated (UIS)

APPLICATIONS

- Telecommunications
 - Server and telecom power supplies
- Lighting
 - High-intensity discharge (HID)
 - Fluorescent ballast lighting
- Consumer and computing
 - ATX power supplies
- Industrial
 - Welding
 - Battery chargers
- Renewable energy
 - Solar (PV inverters)
- Switch mode power supplies (SMPS)


Package pin definition

- Pin1 G - Gate
- Pin2 C & backside - Collector
- Pin3 E - Emitter

TO-247



Top View



ABSOLUTE MAXIMUM RATINGS (T _C = 25 °C, unless otherwise noted)					
PARAMETER			SYMBOL	LIMIT	UNIT
Collector-Emitter Voltage			V _{CE}	1200	V
Gate-Emitter Voltage			V _{GE}	±30	
Continuous Collector Current (T _J = 150 °C)	V _{GE} at 15 V	T _C = 25 °C	I _C	50	A
		T _C = 100 °C		25	
Pulsed Collector Current ^a			I _{CM}	75	
Diode Forward Current ^b			I _F	25	A
Maximum Power Dissipation		T _C = 25 °C	P _D	300	W
		T _C = 100 °C		150	W
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Short Circuit Withstand Time ^{TC=150°C}	V _{GE} = 15V, V _{CE} ≤ 400V		t _{sc}	3	μs
Short Circuit Withstand Time ^{TC=100°C}	V _{GE} = 15V, V _{CE} ≤330V			5	
Soldering Recommendations (Peak Temperature) ^c		for 10 s		260	°C

Notes

- Repetitive rating; pulse width limited by maximum junction temperature.
- Current limited by maximum junction temperature.
- 1.6 mm from case.

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Maximum Junction-to-Ambient	R_{thJA}	-	40	°C/W
Maximum Junction-to-Case	R_{thJC}	-	0.5	

SPECIFICATIONS ($T_J = 25\text{ °C}$, unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static						
Collector-Emitter Breakdown Voltage	BV_{CE}	$V_{GE} = 0\text{ V}, I_C = 250\text{ }\mu\text{A}$ $V_{GE} = 0\text{ V}, I_C = 1\text{ mA}$	1200 1200	- -	- -	V
Gate-Source Threshold Voltage (N)	$V_{GE(th)}$	$V_{CE} = V_{GE}, I_D = 250\text{ }\mu\text{A}$	4	5	6	V
Zero Gate Voltage Collector Current	I_{CES}	$V_{CE} = 1200\text{ V}, V_{GE} = 0\text{ V}, T_J = 25\text{ °C}$	-	1	20	μA
		$V_{CE} = 1200\text{ V}, V_{GE} = 0\text{ V}, T_J = 150\text{ °C}$	-	1000	-	μA
Gate-Emitter Leakage Current	I_{GES}	$V_{CE} = 0\text{ V}, V_{GS} = \pm 20\text{ V}$	-	-	100	nA
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$V_{GE} = 15\text{ V}, I_C = 25\text{ A}$	-	1.7	2.1	V
Forward Transconductance	g_{fs}	$V_{CE} = 20\text{ V}, I_C = 25\text{ A}$	-	40	-	S
Dynamic						
Input Capacitance	C_{ies}	$V_{GE} = 0\text{ V}, V_{CE} = 25\text{ V},$ $f = 500\text{ KHz}$	-	2900	-	pF
Output Capacitance	C_{oes}		-	210	-	
Reverse Transfer Capacitance	C_{res}		-	52	-	
Turn-on Energy	E_{on}	$V_{CE} = 400\text{ V}, V_{GE} = 0/15\text{ V},$ $I_C = 25\text{ A}, R_g = 10\Omega$	-	0.6	-	nJ
Turn-off Energy	E_{off}		-	0.3	-	
Total Gate Charge	Q_g	$V_{GE} = 15\text{ V}, I_C = 25\text{ A}, V_{CE} = 400\text{ V}$	-	150	-	nC
Gate-Emitter Charge	Q_{ge}		-	14	-	
Gate to Collector Charge	Q_{gc}		-	30	-	
Turn-On Delay Time	$t_{d(on)}$	$V_{CE} = 400\text{ V}, V_{GE} = 0/15\text{ V},$ $I_C = 25\text{ A}, R_g = 10\Omega$	-	55	-	ns
Rise Time	t_r		-	41	-	
Turn-Off Delay Time	$t_{d(off)}$		-	164	-	
Fall Time	t_f		-	27	-	
Internal emitter inductance measured 5 mm	L_E		-	13	-	nH
Diode Characteristics						
Diode Forward Current	I_F	IGBT symbol showing the integral reverse junction diode	-	-	25	A
Pulsed Diode Forward Current	I_{FM}		-	-	75	
Diode Forward Voltage	V_F	$I_F = 20\text{ A}$	-	1.65	2.0	V
Reverse Recovery Time	t_{rr}	$T_J = 25\text{ °C}, I_F = 20\text{ A},$ $di/dt = 200\text{ A}/\mu\text{s}, V_R = 400\text{ V}$	-	73	-	ns
Reverse Recovery Charge	Q_{rr}		-	0.38	-	μC
Reverse Recovery Current	I_{RRM}		-	10	-	A




Figure 1. Forward bias safe operating area




Figure 2. Power dissipation as a function of case temperature




Figure 3. Collector current as a function of case temperature




Figure 4. Typical output characteristic




Figure 5. Typical output characteristic




Figure 6. Typical transfer characteristic




Figure 7. Typical collector-emitter saturation voltage as a function of junction temperature




Figure 8. Typical switching times as a function of collector current




Figure 9. Typical switching times as a function of gate resistor




Figure 10. Typical switching times as a function of junction temperature




Figure 11. Gate-emitter threshold voltage as a function of junction temperature




Figure 12. Typical switching energy losses as a function of collector current




Figure 13. Typical switching energy losses as a function of gate resistor




Figure 14. Typical switching energy losses as a function of junction temperature




Figure 15. Typical switching energy losses as a function of collector emitter voltage




Figure 16. Typical turn off switching energy loss for soft switching




Figure 17. Typical gate charge




Figure 18. Typical capacitance as a function of collector-emitter voltage




Figure 19. IGBT transient thermal resistance




Figure 20. Diode transient thermal impedance as a function of pulse width




Figure 21. Typical diode forward current as a function of forward voltage





Figure 22. Typical diode forward voltage as a function of junction temperature

Package: TO-247



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	4.850	5.150	0.191	0.200
A1	2.200	2.600	0.087	0.102
b	1.000	1.400	0.039	0.055
b1	2.800	3.200	0.110	0.126
b2	1.800	2.200	0.071	0.087
c	0.500	0.700	0.020	0.028
c1	1.900	2.100	0.075	0.083
D	15.450	15.750	0.608	0.620
E1	3.500 REF		0.138 REF	
E2	3.600 REF		0.142 REF	
L	40.900	41.300	1.610	1.626
L1	24.800	25.100	0.976	0.988
L2	20.300	20.600	0.799	0.811
ϕ	7.100	7.300	0.280	0.287
e	5.450 TYP		0.215 TYP	
H	5.980 REF		0.235 REF	
h	0.000	0.300	0.000	0.012

Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.