








LOCK CONFIGURATION(锁扣位置)



技术指标(Technical Index):




1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
2. 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。
(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
3. 温度范围(Temperature range): -25°C~+85°C.
4. 额定电流 Rated Current: 1A AC/DC
5. 额定电压(Rated voltage): 125V, AC/DC(=等效).
6. 接触电阻(Contact resistance): ≤0.02Ω.
7. 绝缘电阻(Insulation resistance): ≥100MΩ

Part No	CKT	A	B	C
MX1.25-2PZZ-MR	2	1.25	3.20	4.30
MX1.25-3PZZ-MR	3	2.50	4.45	5.55
MX1.25-4PZZ-MR	4	3.75	5.70	6.80
MX1.25-5PZZ-MR	5	5.00	6.95	8.05
MX1.25-6PZZ-MR	6	6.25	8.20	9.30
MX1.25-7PZZ-MR	7	7.50	9.45	10.55
MX1.25-8PZZ-MR	8	8.75	10.70	11.80
MX1.25-9PZZ-MR	9	10.00	11.95	13.05
MX1.25-10PZZ-MR	10	11.25	13.20	14.30
MX1.25-11PZZ-MR	11	12.50	14.45	15.55
MX1.25-12PZZ-MR	12	13.75	15.70	16.80
MX1.25-13PZZ-MR	13	15.00	16.95	18.05
MX1.25-14PZZ-MR	14	16.25	18.20	19.30
MX1.25-15PZZ-MR	15	17.50	19.45	20.55
MX1.25-16PZZ-MR	16	18.75	20.70	21.80
MX1.25-17PZZ-MR	17	20.00	21.95	23.05
MX1.25-18PZZ-MR	18	21.25	23.20	24.30
MX1.25-19PZZ-MR	19	22.50	24.45	25.55
MX1.25-20PZZ-MR	20	23.75	25.70	26.80


序号	品名	材质
①	A型立式DIP型WTB胶芯 1.25 Pitch S/T Wire To Board Housing DIP(H=4.7)	LCP UL94V-0 本色 Natural
②	A型立式DIP型WTB端子 1.25 Pitch S/T Wire To Board Terminal DIP(H=4.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	A型立式DIP型WTB吸盖 1.25 Pitch S/T Wire To Board Cap	LCP UL94V-0 本色
MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 1.25 Pitch A型直针WTB
DECIMALS:	ANGLES:	PAR MX1.25-NPZZ-MR
X.:±0.50	±1°	DWN Lucas
X.X:±0.20		CHKD Ethan
X.XX:±0.10		APVD Jacob
CUSTOMER COPY		SCALE:1:1 UNIT:MM
		SIZE:A4 SHEET:1F1 REV:A

NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弧形MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS.
(载带材料:透明 PS.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 7.68 METERS. (每卷包装长度: 7.68米.)
- 7.COMPONENT LOAD PER REEL: 900 PCS. (每卷包装数量: 900只, 前后各空包30只.)
8. 纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
9. 纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



CKT (1.25mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	900	14	12600
3				
4				
5				
6				
7	24	900	10	9000
8				
9				
10				
11				
12	32	900	8	7200
13				
14				
15				
16				
17	44	900	6	5400
18				
19				
20				



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32

CKT (1.25mm pitch)	B0	W	F	S
2	4.60	16	7.50	
3	5.85			
4	7.10			
5	8.35			
6	9.60			
7	10.85	24	11.50	
8	12.10			
9	13.35			
10	14.60			
11	15.85			
12	17.10	32	14.2±0.10	28.45
13	18.35			
14	19.60			
15	20.85			
16	22.10			
17	23.35	44	20.2±0.15	40.45
18	25.85			
19	28.35			
20	30.85			

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 1.25-A型直针WTB载带包装
DECIMALS:	ANGLES:		PAR MX1.25-NPZZ-MR
X.:±0.50	±1°		DWN Lucas
X.X:±0.25			CHKD Ethan
X.XX:±0.15			APVD Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A