









P.C.B Layout

NOTES:

1. Material:
Insulation:LCP,UL94V-0(White)
Pin:Phosphor bronze/Gold Plated
Tab:Phosphor bronze/Tin-Plated
2. Current Rating: 1.5A AC,DC
3. Voltage Rating: 100V AC,DC
4. Temperature Rang: -25°C~+85°C
5. Contact Resistance: 20mΩ Max
6. Insulation Resistance: 500MΩ Min
- 7 Withstanding Voltage: 250V AC/minute




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

—TOLERANCES—
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE: 0.8MM间距灯条板
产品名称: 对板双面接连接器

X.X ±0.30 X.X* ±3°

APPD:
核准: 谢亮

PART NO:
产品编号: D0801RS-2xNP

X.XX ±0.20 X.XX* ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.15 X.XXX* ±1°

DRAW:
绘图: 黄艳兰

1:1 mm A001