





REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	/

DESIGN
/



面板开孔尺寸



PART NO.:

PCB板开孔尺寸
A-A(比例: 1: 1)

- EC-GX12-P04-C A V
- ① Model(型号): EC
- ② Series(系列): GX12
- ③ Needle core configuration(针芯配置): 4Pin
- ④ Outer casing(外壳): 锌合金镀镍/Zinc alloy nickel plated
- ⑤ Insulator(绝缘体): 橡胶黑木/Rubber Ebony
- ⑥ Needle core(针芯): 母焊接针/Mother welding needle

Specifications:

规格:
Number of insertions and removals: 1000
插拔次数: 1000
Temperature: -55° ~ +70°
温度: -55° ~ +70°
Protection level: IP50
防护级别: IP50
Salt spray: 5% NaCl for 25 hours / 25 hours in 5% NaCl mist
盐雾: 5% NaCl for 25 hours/5%NaCl雾气中25小时
Rated Voltage: 400V
额定电压: 400V
Rated current: 5A
额定电流: 5A
Pin material: gold-plated copper alloy
插针材料: 铜合金镀金
Insulation resistance: >100MΩ
绝缘电阻: >100MΩ

AUGLAR	±5°	XKB 星野 Connection				XKB INDUSTRIAL PRECISION CO., LIMITED					
X.	±0.40										
X.x	±0.30										
X.xx	±0.20										
X.xxx	±0.15										
UNSPECIFIED TOLERANCES											
		DESIGN		阿控		VIEW: 		MODEL TYPE: EC.GX12.P04.CAV			
		CHECKED				UNIT: mm/in		PART NO.: /			
		APPROVED				SIZE: A4		DWG NO.:			
								SCALE			
								PAGE			
								REVISION			