



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold (Au)**
Wire Contact Termination Area Plating Material: **Tin**
Contact Retention Within Housing: **With**
Contact Size: **Size 16**

Features

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Size	Size 16
Contact Base Material	Brass
Contact Current Rating (Max)	13 A
Mating Pin Diameter	1.57 mm[.062 in]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material Finish	Bright
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.76 µm[30 µin]



Termination Features

Termination Method to Wire & Cable	Solder Tab
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 206060-1 CPC PLUG ASSEMBLY SIZE 11-4	 TE Part # 208488-3 CMC PLUG ASSEMBLY,SZ 22	 TE Part # 211766-1 CPC PLUG ASSEMBLY SIZE 17-9	 TE Part # 788153-2 SLD CPC PLUG ASSY,11-4,REV SEX
 TE Part # 208470-3 CMC PLUG ASSEMBLY,SZ 28	 TE Part # 208714-2 CMC PLUG ASSEMBLY,SZ 14-7	 TE Part # 206554-1 CPC PLUG ASSEMBLY SIZE 17-16	 TE Part # 206305-1 CPC PLUG ASSEMBLY SIZE 23-37
 TE Part # 213852-1 CPC PLUG ASSEMBLY SIZE 23-19	 TE Part # 208720-1 PLUG ASSY,SZ 14,CMC	 TE Part # 202236-7 III+PIN,SOLTAB,30AU>10,LP,SN	 TE Part # 1977887-1 PLUG.ASSY,23-37STD SEX THRD AD, UV RESIS
 TE Part # 305183 EXTRACT TOOL TYPE 2 20-16	 TE Part # 211772-1 CPC PLUG ASSEMBLY SIZE 23-19	 TE Part # 1977884-1 SLD CPC PLUG ASSY,13-9,STD SEX, UV RESIS	 TE Part # 208457-3 CMC PLUG ASSEMBLY,SZ 28-24



TE Part # 208488-1
CMC PLUG ASSEMBLY, SZ 22

TE Part # 213851-1
CPC PLUG ASSEMBLY SIZE 23-24

TE Part # 208714-1
CMC PLUG ASSEMBLY, SZ 14-7

TE Part # 796288-1
PLUG.ASSY, 23-37 STD SEX THRD AD

Also in the Series

AMP Type III+

Connector Contacts(260)

Insertion & Extraction Tools(4)

Power Contacts(260)

Also in the Series

Circular Plastic Connectors Series 1

Circular Power Connectors(211)

Connector Contacts(260)

Power Contacts(260)

Customers Also Bought

TE Part #170038-2
187 FASTON, REC., 20-16 AWG, TPBR

TE Part #1-171822-0
EIS REC. HSG 10P-NATURAL

TE Part #176273-1
AMP UNIVERSAL POWR PLUG 4P

TE Part #CAT-D9934-A83A
Receptacle and Tab Housing: 5.08 or 10.16 mm pitch, 250-600V



Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_202237-7_T.2d_dxf.zip

English

Customer View Model

ENG_CVM_202237-7_T.3d_igs.zip

English

Customer View Model

ENG_CVM_202237-7_T.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_202237-7_W.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_202237-7_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_202237-7_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Signal Contacts

English

Product Specifications

Application Specification

English

