




PCB LAYOUT



修订	标记	修改摘要	签名	日期

SPECIFICATIONS

Rated(额定参数): 300V,15A

Dielectric strength(抗电强度): AC2000V/1 Minute

Insulation Resistance(绝缘电阻):1000MΩ Min


Contact Resistance(接触电阻):20mΩ Max

Temp. range(操作温度): -40℃~+105℃

MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)

Contact(端子): Brass, Tin plating(黄铜镀锡)



PART NO.	Dimensions (mm)		PART NO.	Dimensions (mm)		PART NO.	Dimensions (mm)	
	A	B		A	B		A	B
2P	5.08	12.16	10P	45.72	52.80	18P	86.36	93.44
3P	10.16	17.24	11P	50.80	57.88	19P	91.44	98.52
4P	15.24	22.32	12P	55.88	62.96	20P	96.52	103.60
5P	20.32	27.40	13P	60.96	68.04	21P	101.60	108.68
6P	25.40	32.48	14P	66.04	73.12	22P	106.68	113.76
7P	30.48	37.56	15P	71.12	78.20	23P	111.76	118.84
8P	35.56	42.64	16P	76.20	83.28	24P	116.84	123.92
9P	40.64	47.72	17P	81.28	88.36			




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: 插拔式接线端子

X.X ±0.30 X.X* ±3°

APPD:
核准: 谢亮

PART NO:
产品编号: HDGC2EDGVC-5.08-NP

X.XX ±0.20 X.XX* ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.15 X.XXX* ±1°

DRAW:
绘图: 黄艳兰

1:1 mm A001