





REVISONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	/



PART NO.:

EC-GX12-P07-C A V

① Model(型号): EC

② Series(系列): GX12

③ Needle core configuration(针芯配置):6Pin

④ Outer casing(外壳): 锌合金镀镍/Zinc alloy nickel plated

⑤ Insulator(绝缘体): 橡胶黑木/Rubber Ebony

⑥ Needle core(针芯): 母焊接针/Mother welding needle

PCB板开孔尺寸

A-A(比例: 1: 1)

Specifications:

规格:

Number of insertions and removals: 1000

插拔次数: 1000

Temperature: -55° ~ +70°

温度: -55° ~+70°

Protection level: IP50

防护级别: IP50

Salt spray: 5% NaCl for 25 hours / 25 hours in 5% NaCl mist

盐雾: 5% NaCl for 25 hours/5%NaCl雾气中25小时

Rated Voltage: 400V

额定电压: 400V

Rated current: 5A


额定电流: 5A

Pin material: gold-plated copper alloy

插针材料: 铜合金镀金

Insulation resistance: >100MΩ

绝缘电阻: >100MΩ

AUGLAR	±5°					DESIGN	阿控	VIEW:	MODEL TYPE:
X.	±0.40					CHECKED		UNIT: mm/in	EC:GX12.P07.CAV
X.xx	±0.30								PART NO.:
X.xxx	±0.20					APPROVED		SIZE: A4	DWG NO.:
UNSPECIFIED TOLERANCES		KKB INDUSTRIAL PRECISION CO., LIMITED				SCALE		PAGE	REVISION
						N/A		1/1	A0

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

KKB INDUSTRIAL PRECISION CO., LIMITED

SCALE N/A

PAGE 1/1

REVISION A0