


FEATURES


- High current gain
- Excellent h_{FE} linearity
- Low noise between 30Hz and 15kHz
- For AF input stages and driver applications



SOT-23

APPLICATIONS

- General purpose switching and amplification



ORDERING INFORMATION


Type No.	Marking	Package Code
BC847,215-JSM	1G	SOT-23

MAXIMUM RATING @ $T_a=25^{\circ}\text{C}$ unless otherwise specified

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	50	V
V_{CEO}	Collector-Emitter Voltage	45	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current -Continuous	0.1	A
P_C	Collector Dissipation	250	mW
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	500	$^{\circ}\text{C/W}$
T_J, T_{STG}	Junction and Storage Temperature	-55 to +150	$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified


Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=10\mu A, I_E=0$	50			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=10mA, I_B=0$	45			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=10\mu A, I_C=0$	6			V
Collector-base cut-off current	I_{CBO}	$V_{CB}=30V, I_E=0$ $V_{CB}=30V, I_E=0, T_j=150^\circ C$			15 5	nA uA
Emitter-base cut-off current	I_{EBO}	$V_{EB}=5V, I_C=0$			100	nA
Collector-emitter cut-off current	I_{CEO}	$V_{CE}=30V, I_B=0$			1	mA
DC current gain	h_{FE}	$V_{CE}=5V, I_C=10\mu A$		480		
DC current gain	h_{FE}	$V_{CE}=5V, I_C=2mA$	420		800	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=10mA, I_B=0.5mA$ $I_C=100mA, I_B=5mA$		0.09 0.2	0.25 0.6	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C=10mA, I_B=0.5mA$ $I_C=100mA, I_B=5mA$		0.7 0.9	0.9 1.1	V
Base-emitter voltage	$V_{BE(on)}$	$I_C=2mA, V_{CE}=5V$ $I_C=10mA, V_{CE}=5V$	0.58	0.66	0.7 0.77	V
Collector capacitance	C_C	$V_{CB}=10V, I_E=I_C=0,$ $f=1MHz$		2.5		pF
Transition frequency	f_T	$V_{CE}=5V, I_C=10mA$ $f=100MHz$	100			MHz

TYPICAL CHARACTERISTICS @ $T_a=25^\circ\text{C}$ unless otherwise specified


BC846A; $V_{CE} = 5\text{ V}$.

- (1) $T_{amb} = 150^\circ\text{C}$.
 (2) $T_{amb} = 25^\circ\text{C}$.
 (3) $T_{amb} = -55^\circ\text{C}$.


Fig.1 DC current gain as a function of collector current; typical values.



BC846A; $V_{CE} = 5\text{ V}$.

- (1) $T_{amb} = -55^\circ\text{C}$.
 (2) $T_{amb} = 25^\circ\text{C}$.
 (3) $T_{amb} = 150^\circ\text{C}$.


Fig.2 Base-emitter voltage as a function of collector current; typical values.



BC846A; $I_C/I_B = 20$.

- (1) $T_{amb} = 150^\circ\text{C}$.
 (2) $T_{amb} = 25^\circ\text{C}$.
 (3) $T_{amb} = -55^\circ\text{C}$.


Fig.3 Collector-emitter saturation voltage as a function of collector current; typical values.



BC846A; $I_C/I_B = 10$.

- (1) $T_{amb} = -55^\circ\text{C}$.
 (2) $T_{amb} = 25^\circ\text{C}$.
 (3) $T_{amb} = 150^\circ\text{C}$.

Fig.4 Base-emitter saturation voltage as a function of collector current; typical values.




BC847B; $V_{CE} = 5\text{ V}$.

(1) $T_{amb} = 150^\circ\text{C}$.

(2) $T_{amb} = 25^\circ\text{C}$.

(3) $T_{amb} = -55^\circ\text{C}$.

Fig.5 DC current gain as a function of collector current; typical values.




BC847B; $V_{CE} = 5\text{ V}$.

(1) $T_{amb} = -55^\circ\text{C}$.

(2) $T_{amb} = 25^\circ\text{C}$.

(3) $T_{amb} = 150^\circ\text{C}$.

Fig.6 Base-emitter voltage as a function of collector current; typical values.




BC847B; $I_C/I_B = 20$.

(1) $T_{amb} = 150^\circ\text{C}$.

(2) $T_{amb} = 25^\circ\text{C}$.

(3) $T_{amb} = -55^\circ\text{C}$.

Fig.7 Collector-emitter saturation voltage as a function of collector current; typical values.




BC847B; $I_C/I_B = 10$.

(1) $T_{amb} = -55^\circ\text{C}$.

(2) $T_{amb} = 25^\circ\text{C}$.

(3) $T_{amb} = 150^\circ\text{C}$.


Fig.8 Base-emitter saturation voltage as a function of collector current; typical values.



BC847C; $V_{CE} = 5\text{ V}$.

- (1) $T_{amb} = 150\text{ }^{\circ}\text{C}$.
- (2) $T_{amb} = 25\text{ }^{\circ}\text{C}$.
- (3) $T_{amb} = -55\text{ }^{\circ}\text{C}$.


Fig.9 DC current gain as a function of collector current; typical values.



BC847C; $V_{CE} = 5\text{ V}$.

- (1) $T_{amb} = -55\text{ }^{\circ}\text{C}$.
- (2) $T_{amb} = 25\text{ }^{\circ}\text{C}$.
- (3) $T_{amb} = 150\text{ }^{\circ}\text{C}$.


Fig.10 Base-emitter voltage as a function of collector current; typical values.



BC847C; $I_C/I_B = 20$.

- (1) $T_{amb} = 150\text{ }^{\circ}\text{C}$.
- (2) $T_{amb} = 25\text{ }^{\circ}\text{C}$.
- (3) $T_{amb} = -55\text{ }^{\circ}\text{C}$.

Fig.11 Collector-emitter saturation voltage as a function of collector current; typical values.



BC847C; $I_C/I_B = 10$.


- (1) $T_{amb} = -55\text{ }^{\circ}\text{C}$.
- (2) $T_{amb} = 25\text{ }^{\circ}\text{C}$.
- (3) $T_{amb} = 150\text{ }^{\circ}\text{C}$.

Fig.12 Base-emitter saturation voltage as a function of collector current; typical values.

PACKAGE OUTLINE


Plastic surface mounted package

SOT-23



SOT-23		
Dim	Min	Max
A	2.70	3.10
B	1.10	1.50
C	0.90	1.10
D	0.30	0.50
E	0.35	0.48
G	1.80	2.00
H	0.02	0.10
J	0.05	0.15
K	2.20	2.60
All Dimensions in mm		

SOLDERING FOOTPRINT



Unit: mm

PACKAGE INFORMATION

Device	Package	Shipping
BC847,215-JSM	SOT-23	3000 pcs / Tape & Reel

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2024

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com