

Customer : _____
(客 戶)

Part No. : _____
(貴公司料號)

SPECIFICATION FOR APPROVAL

承 認 書

Description : ALUMINUM ELECTROLYTIC CAPACITORS
(零 件 名 稱)

Lelon Series : LSM Series
(立 隆 系 列)

Lelon Part No.: LSM151M2G--A2525
(立 隆 料 號)

LELON ELECTRONICS CORP.
立 隆 電 子 工 業 股 份 有 限 公 司

Headquarters

147, Sec. 1, Guoguang Rd., Dali District, Taichung, Taiwan
TEL: +886-4-2418-1856 FAX: +886-4-2418-1906

Manufacturing Sites

Lelon Electronics Corp.
147, Sec. 1, Guoguang Rd., Dali District, Taichung, Taiwan
TEL: +886-4-2418-1856 FAX: +886-4-2418-1906

Lelon Electronics (Huizhou) Co., Ltd.
Taiyang Industrial Zone, Baihua Town, Huidong County, Huizhou City,
Guangdong, China
TEL: +86-752-8768222 FAX: +86-752-8768199

Lelon Electronics (Suzhou) Co., Ltd.
1220, Zhongshan North Rd., Songling Town, Wujiang City, Jiangsu, China
TEL: +86-512-63457588 FAX: +86-512-63457791

Approval Signatures
貴公司承認印

Approval 核 淮	Check 確 認	Design 作 成
		

Please Return One Copy with Your Approval
承 認 後 請 寄 回 本 圖 一 份

Part Numbering System

Product Code Guide – Snap-in Type

LSM Series	150μF	±20%	400V	2-pin Terminals	Terminal Length 4.0 mm	25 φ × 25L	Pb-free Terminal + PET Sleeve	Supplement code
LSM	151	M	2G	=	A	2525		
① Series	Capacitance	Capacitance Tolerance	Rated Voltage	Terminal Type	Terminal Length	Case Size	Terminal and Sleeve Type	Supplement Code

① Series:

Series is represented by a three-letter code. When the series name only has two letters, use a hyphen, “-”, to fill the third blank.

② Capacitance:

Capacitance in μF is represented by a three-digit code. The first two digits are significant and the third digit indicates the number of zeros following the significant figure.

Example:	Capacitance	47	100	150	1,000	1,500	6,800	10,000	12,000
	Part number	470	101	151	102	152	682	103	123

③ Tolerance:

K = -10% ~ +10%	M = -20% ~ +20%	V = -10% ~ +20%
-----------------	-----------------	-----------------

④ Rated voltage:

Rated voltage in volts (V) is represented by a two-digit code

Rated Volt. (V)	16	25	35	50	63	80	100		
Code	1C	1E	1V	1H	1J	1K	2A		
Rated Volt. (V)	160	180	200	250	350	315	400	420	450
Code	2C	2S	2D	2E	2V	2F	2G	2P	2W

⑤ Terminal type:

Terminal type (pins)	2 (Standard)	3	4	5	Vibration-resistant	Horizontal Mounting
Terminal code	--	L3	L4	L5	T2	H2 G2

⑥ Terminal length:

Terminal length (mm)	4.0	6.3
Terminal code	A	-

⑦ Case Size:

The first two digits indicate case diameter in mm. The last two digits indicate case length in mm.

φ D×L	20×15	20×20	20×25	20×30	20×35	20×40	20×45	20×50	22×15	22×20	22×25	22×30
Code	2015	2020	2025	2030	2035	2040	2045	2050	2215	2220	2225	2230
φ D×L	22×35	22×40	22×45	22×50	22×55	22×60	25×15	25×20	25×25	25×30	25×35	25×40
Code	2235	2240	2245	2250	2255	2260	2515	2520	2525	2530	2535	2540
φ D×L	25×45	25×50	25×55	25×60	30×15	30×20	30×25	30×30	30×35	30×40	30×45	30×50
Code	2545	2550	2555	2560	3015	3020	3025	3030	3035	3040	3045	3050
φ D×L	30×55	30×60	30×65	35×15	35×20	35×25	35×30	35×35	35×40	35×45	35×50	35×60
Code	3055	3060	3065	3515	3520	3525	3530	3535	3540	3545	3550	3560
φ D×L	35×70	35×80	35×90	35×100	40×25	40×30	40×35	40×40	40×45	40×50	40×55	40×60
Code	3570	3580	3590	35A0	4025	4030	4035	4040	4045	4050	4055	4060
φ D×L	40×70	40×80	40×90	40×100	45×70	45×80	45×90					
Code	4070	4080	4090	40A0	4570	4580	4590					

Note: When a case size is required and not shown in the table, please contact with us for further discussion.

⑧ Terminal and Sleeve Type:

None = Pb free terminal + PET sleeve (Standard design)	M = Pb free terminal + PET sleeve + No bottom insulation + Rilled
R = Pb free terminal + PET sleeve + Rilled	C = Pb free terminal + Nano carbon coating insulation
N = Pb free terminal + PET sleeve + No bottom insulation	K / L = Automotive control code


* When a supplement code following a blank digit code of terminal and sleeve type (standard design), use a hyphen, “-”, to fill the blank digit. When the bottom insulation plate is not required or a rilled construction is necessary, please consult Lelon.

⑨ Supplement code (Optional):

For special control purposes

CUSTOMER :
CUSTOMER P/N :

PRODUCT DIMENSIONS




Items	Performance																				
Rated Voltage V_R	400 V																				
Capacitance C_R	150 μ F (120 Hz, 20°C)																				
Category Temperature Range	-25°C ~ +105°C																				
Capacitance Tolerance	-20 % ~ +20 % (120 Hz, 20°C)																				
Surge Voltage V_s	440 V _{DC}																				
Leakage Current (20°C)	$I_{LEAK} \leq 0.73$ mA After 5 minutes																				
Tan δ	≤ 0.15 (120 Hz, 20°C)																				
Ripple Current ($I_{AC, R}$ / rms)	0.77 A (120 Hz, 105°C)																				
Low Temperature Characteristics at 120 Hz	<table border="1"> <tr> <td rowspan="2">Impedance ratio</td> <td>$Z_{(-25^\circ\text{C})}/Z_{(+20^\circ\text{C})}$</td> <td>8</td> </tr> <tr> <td>$Z_{(-40^\circ\text{C})}/Z_{(+20^\circ\text{C})}$</td> <td>-</td> </tr> </table>						Impedance ratio	$Z_{(-25^\circ\text{C})}/Z_{(+20^\circ\text{C})}$	8	$Z_{(-40^\circ\text{C})}/Z_{(+20^\circ\text{C})}$	-										
Impedance ratio	$Z_{(-25^\circ\text{C})}/Z_{(+20^\circ\text{C})}$	8																			
	$Z_{(-40^\circ\text{C})}/Z_{(+20^\circ\text{C})}$	-																			
Ripple Current(A) and Frequency Multipliers	<table border="1"> <tr> <td>Frequency (Hz)</td> <td>50 / 60</td> <td>100 / 120</td> <td>300</td> <td>1k</td> <td>10k up</td> </tr> <tr> <td>Multiplier</td> <td>0.8</td> <td>1.0</td> <td>1.1</td> <td>1.3</td> <td>1.4</td> </tr> </table>						Frequency (Hz)	50 / 60	100 / 120	300	1k	10k up	Multiplier	0.8	1.0	1.1	1.3	1.4			
Frequency (Hz)	50 / 60	100 / 120	300	1k	10k up																
Multiplier	0.8	1.0	1.1	1.3	1.4																
Endurance and Shelf Life Test	<table border="1"> <tr> <th>Items</th> <th>Endurance</th> <th>Shelf Life Test</th> </tr> <tr> <td>Test Time</td> <td>3000 Hrs at 105°C; $V_R, I_{AC, R}$</td> <td>1000 Hrs at 105°C</td> </tr> <tr> <td>Cap. Change</td> <td>Within ± 20 % of initial value</td> <td>Within ± 20 % of initial value</td> </tr> <tr> <td>Tan δ</td> <td>Less than 200% of specified value</td> <td>Less than 150% of specified value</td> </tr> <tr> <td>Leakage Current</td> <td>Within specified value</td> <td>Within specified value</td> </tr> </table> <p>Shelf Life Test: The rated voltage shall be applied to the capacitors before the measurements (Refer to JIS C 5101-4 4.1)</p>						Items	Endurance	Shelf Life Test	Test Time	3000 Hrs at 105°C; $V_R, I_{AC, R}$	1000 Hrs at 105°C	Cap. Change	Within ± 20 % of initial value	Within ± 20 % of initial value	Tan δ	Less than 200% of specified value	Less than 150% of specified value	Leakage Current	Within specified value	Within specified value
Items	Endurance	Shelf Life Test																			
Test Time	3000 Hrs at 105°C; $V_R, I_{AC, R}$	1000 Hrs at 105°C																			
Cap. Change	Within ± 20 % of initial value	Within ± 20 % of initial value																			
Tan δ	Less than 200% of specified value	Less than 150% of specified value																			
Leakage Current	Within specified value	Within specified value																			
Solder Heat-resistance	During dip of wave soldering , temperature at the capacitors terminals should be less than $260 \pm 5^\circ\text{C}$, 10 ± 1 seconds.																				
Standards	JIS C 5101-4, IEC 60384-4																				
Remarks	RoHS Compliance ,Halogen-free																				

* Please refer to " Precautions and Guidelines for Aluminum Electrolytic Capacitors " section in Lelon's catalog for further details

Publication Date	April 20, 2023	Approval Signatures: Please return one copy with your approval	Approved	Checked	Designed
Revision Date					
Version No.	1				

Diagram of Dimensions:

Unit: mm



Marking:

Each capacitor shall be marked with the following information.


(Front)

Manufacturer's name: trade mark ← **Lelon**
 Capacitance ← 150 μ F
 Rated voltage ← 400 V
 Polarity of the terminals ←



(Back)

LSM
105°C (M)
A301



Printing:

Marking color: White


Sleeve color: Black ----- LSM Series

Sleeve material: PET

Packaging Specification:

Snap-in type in packaging

1-1 Inner Box:




Unit: mm			
ϕD	L	W	H
20	311	195	31 ~ 115
22			
25			
30			
35			
40	245 ~ 265	267 ~ 310	35 ~ 105
45			

Packaging Quantity:

ϕD \ L	15	20	25	30	35	40	45	50	55	60
20	110	110	110	110	110	110	100	100	---	---
22	90	90	90	90	90	90	80	80	80	80
25	65	65	65	65	65	65	65	65	65	65
30	50	50	50	50	50	50	45	45	45	45
35	40	40	40	40	40	40	40	40	40	40
40	---	---	30	30-	30	30	30	30	30	30

ϕD \ L	65	70	75	80	85	90	95	100
35	40	40	40	40	40	40	40	40
40	30	30	30	30	30	30	20	20
45	---	25	25	25	25	25	---	---


1-2 Outer Box:



Unit: mm			
ϕD	L	W	H
20	412	336	277 ~ 335
22			
25			
30			
35			
40	260 ~ 330	282 ~ 560	210 ~ 290

Packaging Specification:


Packaging Quantity:



		Unit: pcs								
		L	15	20 ~ 25	30	35 ~ 40	45 ~ 50	55 ~ 60	65~80	85 ~ 100
ϕD	L	Boxes	16	12	10	8	8	8	---	---
	Quantity	1,760	1,320	1,100	880	800	800	---	---	
22	L	Boxes	16	12	10	8	8	8	6	---
	Quantity	1,440	1,080	900	720	640	640	480	---	
25	L	Boxes	16	12	10	8	8	8	6	---
	Quantity	1,040	780	650	520	520	520	390	---	
30	L	Boxes	16	12	10	8	8	8	6	---
	Quantity	800	600	500	400	360	360	270	---	
35	L	Boxes	16	12	10	8	8	8	6	4
	Quantity	640	480	400	320	320	320	240	160	
		L	20 ~ 30	35 ~ 50	55 ~ 70	75 ~ 90	95~100			
ϕD	L	Boxes	5	4	3	2	4			
	Quantity	150	120	90	60	80				
45	L	Boxes	---	---	3	2	4			
	Quantity	---	---	75	50	80				

Note: The quantities are principle. Some difference may be provided.

3. Label:



Endurance characteristic:

No.	Item	Conditions	Specification	
1	Rotational Temperature Test	<p>Capacitor is placed in an oven whose temperatures follow specific regulation to change. The specific regulation is "+25°C (3 min.) → -40 / -25°C (30 min.) → +25°C (3 min.) → +105°C (30 min.) → +25°C (3 min.)", and it is called a cycle. The test totals 10 cycles, and then the capacitor shall be subjected to standard atmospheric conditions for 4 hours, after which measurements shall be made.</p> <p>1. -40°C for 16 ~ 100V 2. -25°C for 160 ~ 500V</p>	Capacitance change	Within ± 10% of initial value.
			Tan δ	Within specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged
2	High Temperature Endurance Life Test	<p>1. Capacitors shall be placed in oven with application of ripple current and rated voltage for 3,000 +72 / -0 hours at 105°C.</p> <p>2. The capacitor should be used within specified permissible ripple current in each standard products table (the sum of DC voltage and AC peak voltage shall be equal to the rated DC working voltage).</p> <p>3. The specified maximum permissible ripple current is defined at 105°C and 120 Hz (unless otherwise specified).</p> <p>4. Then the capacitor shall be subjected to standard atmospheric conditions for 4 hours, After which measurements shall be made.</p>	Capacitance change	Within ± 20% of initial value.
			Tan δ	Less than 200% of specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged
3	High Temperature Unload Life Test	<p>After 1,000 +48 / -0 hours test at 105°C without rated voltage. And then the capacitor shall be subjected to standard atmospheric conditions for 4 hours, after which measurements shall be made. The rated voltage shall be applied to the capacitors before the measurements (Refer to JIS C 5101-4 4.1)</p>	Capacitance change	Within ± 20% of initial value.
			Tan δ	Less than 150% of specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged
4	Humidity Test	<p>Capacitors shall be exposed for 1,000 +48 / -0 hours in an atmosphere of 90 ~ 95% R. H. at 60 ± 3°C. And then the capacitor shall be subjected to standard atmospheric conditions for 4 hours, after which measurements shall be made.</p>	Capacitance change	Within ± 10% of initial value.
			Tan δ	Less than 120% of specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged
5	Low Temperature Test	<p>Capacitors are placed at -40 / -25 ± 3°C for 96 ± 4 hours. And then the capacitor shall be subjected to standard atmospheric conditions for 4 hours, after which measurements shall be made.</p> <p>1. -40°C for 16 ~ 100V 2. -25°C for 160 ~ 500V</p>	Capacitance change	Within ± 10% of initial value.
			Tan δ	Within specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged
6	Vibration Test	<p>1. Fix it at the point 4 mm or less from body. For ones of 12.5 mm or more in diameter or 25 mm or more length, use separate fixture.</p> <p>2. Direction and during of vibration: 3 orthogonal directions mutually each for 2 hours (total of 6 hours).</p> <p>3. Frequency: 10 to 55 Hz reciprocation for 1 minute.</p> <p>4. Total amplitude : 1.5 mm</p>	Capacitance change	Within ± 10% of initial value.
			Tan δ	Within specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged
7	Solder Heat-Resistance Test	<p>The section of lead below 4 mm from the body of capacitor must be immersed in 260 ± 5°C liquid tin 10 ±1 seconds, than, after removing the following specifications shall be satisfied when capacitor terminal is restored to 20°C over 4 hours.</p>	Capacitance change	Within ± 10% of initial value.
			Tan δ	Within specified value
			Leakage Current	Within specified value
			Physical	No broken and undamaged

No.	Item	Conditions	Specification																																								
8	Surge Voltage Test	The capacitor shall be subjected to 1,000 cycles at 15 ~ 35°C. Protective series resistor a 1KΩ each consisting of a charge period of 30 ± 5 seconds, followed by discharge period of approximately 5.5 minutes.	Capacitance change	Within 20% of initial value.																																							
			Tan δ	Less than 175% of specified value																																							
			Leakage Current	Within specified value																																							
			Physical	No broken and undamaged																																							
		Applying voltage:																																									
		<table border="1"> <thead> <tr> <th>Rated Voltage (V)</th><th>16</th><th>25</th><th>35</th><th>50</th><th>63</th><th>80</th><th>100</th></tr> </thead> <tbody> <tr> <td>Surge Voltage (V)</td><td>18.4</td><td>28.8</td><td>40.3</td><td>57.5</td><td>72.5</td><td>92</td><td>115</td></tr> <tr> <th>Rated Voltage (V)</th><th>160</th><th>200</th><th>250</th><th>350</th><th>400</th><th>420</th><th>450</th></tr> <tr> <td>Surge Voltage (V)</td><td>184</td><td>230</td><td>288</td><td>385</td><td>440</td><td>462</td><td>495</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>550</td></tr> </tbody> </table>	Rated Voltage (V)	16	25	35	50	63	80	100	Surge Voltage (V)	18.4	28.8	40.3	57.5	72.5	92	115	Rated Voltage (V)	160	200	250	350	400	420	450	Surge Voltage (V)	184	230	288	385	440	462	495								550	
Rated Voltage (V)	16	25	35	50	63	80	100																																				
Surge Voltage (V)	18.4	28.8	40.3	57.5	72.5	92	115																																				
Rated Voltage (V)	160	200	250	350	400	420	450																																				
Surge Voltage (V)	184	230	288	385	440	462	495																																				
							550																																				
9	Venting Test	<p>1. Applicable to the capacitors with case diameter is 6.3 mm and larger.</p> <p>2. Test condition:</p> <p>(1) AC test The capacitor shall be connected across an applying 50 or 60 Hz AC which is 0.7 times of rated voltage or 250Vrms AC whichever is the lower.</p> <p>(2) DC test: Applying inverse DC rated voltage with current to the capacitor. Where case diameter: $\phi D \leq 22.4$ mm: 1 A DC max. $\phi D > 22.4$ mm: 10 A DC max.</p> <p>Note:</p> <p>(1) When the pressure relief vent operated, the capacitor shall avoid any danger of fire or explosion of capacitor element (terminal and metal foil etc.) or cover.</p> <p>(2) When the pressure relief device does not open with the voltage applied over 30 minutes, the test is considered to be passed.</p>																																									
10	Mechanical Characteristics Test	<p>1. The test is about lead tabs strength.</p> <p>2. Test Function:</p> <p>2.1 Applying tensile force on termination in the weakest direction gradually, after reached to the specified tensile force, keep it for 30 ± 5 sec.</p> <p>2.2 Applying tensile force in the opposite direction with the same way.</p> <p>2.3 Carry out this operation once.</p> <table border="1"> <thead> <tr> <th>Min. sectional area (mm²)</th><th>Tensile Force (kgf)</th></tr> </thead> <tbody> <tr> <td>Over 0.5 to 1 include</td><td>1</td></tr> <tr> <td>Over 1</td><td>2.5</td></tr> </tbody> </table>	Min. sectional area (mm ²)	Tensile Force (kgf)	Over 0.5 to 1 include	1	Over 1	2.5																																			
Min. sectional area (mm ²)	Tensile Force (kgf)																																										
Over 0.5 to 1 include	1																																										
Over 1	2.5																																										
11	Solder ability Test	After the lead wire fully immersed in the solder for 2 ± 0.5 secs at a temperature of 245 ± 5°C, the solder coating must be more than 95%.																																									
12	Standards	Satisfies Characteristic JIS C 5101-4																																									

Precautions and Guidelines for Aluminum Electrolytic Capacitors

1. Guidelines for Circuit Design (General / Application guidelines for using electrolytic capacitors)

Selecting of a right capacitor is a key to a good circuit design.

(1) Polarity

Most of the aluminum electrolytic capacitors are polarized. Therefore, they must be installed with the correct polarity. Usage in the reverse polarity results into a short-circuit condition that may damage or even explode the capacitor. In addition, it may influence circuit functionality. A bi-polar electrolytic capacitor should be installed when polarity across a capacitor is unstable / reversible. It should be, however, noted that usage of both polar and bi-polar capacitors are limited to DC applications. They must NOT be used for AC application.

(2) Operating Voltage

Applied DC voltage must not exceed rated voltage of the capacitor. Applying higher voltage than its rated voltage across a capacitor terminals cause overheating due to higher leakage currents and capacitor dielectric/insulation deterioration that will ultimately affect a capacitor's performance. The device, however, is capable of working under short-time transient voltages such as DC transients and peak AC ripples. Reverse voltages higher than 1 Volt within a specified temperature limit or AC voltages are not permissible. Overall, using capacitors at recommended operating voltages can prolong its lifespan. Note that the result of DC voltage overlapped with peak ripple voltage should not exceed rated voltage.

(3) Ripple Current

One of the key functions of any capacitor is removal of the ripple current i.e. the RMS value of AC flowing through a capacitor. But, a ripple current higher than rated ripple current will drop resultant capacitance, cause undue internal heating and thus reduces life span of the capacitor. In extreme cases, internal high temperature will cause the pressure relief vent to operate while destroying the device. Overall, it is important to note that an electrolytic capacitor must be used within a permissible range of ripple current. Indicators like temperature coefficient of allowable ripple current are generally used to determine life expectancy of the capacitor, but to avoid related complex calculations and for the sake of simplicity, we haven't provided temperature coefficient in the catalogue. But it offers key indicators like maximum operating temperature for calculation of life expectancy at a given temperature.

(4) Operating Temperature

Capacitors should be used within a permissible range of operating temperatures. Using capacitor at a higher temperature than maximum rated temperature will considerably shorten its life. In the worst-case scenario, high temperature can cause pressure relief vent to operate and the device will get destroyed. Using capacitors at an ambient room temperature assure their longer life.

(5) Leakage Current

Leakage current flows through a capacitor when DC voltage is applied across it. Leakage current varies with changes in ambient temperature and applied DC voltage level and its time of application. Overvoltage situation, presence of moisture, and thermal stresses, especially occurring during the soldering process can enhance leakage current. Initial leakage current is usually higher and does not decrease until voltage is applied for a certain period of time. It is recommended to keep initial leakage current within specified levels.

(6) Charge and Discharge

Regular electrolytic capacitors are not suitable for rapid charging/discharging circuits. Such usage may either cause reduction in overall capacitance or damage due to overheating. Lelon provides special assistance for selecting appropriate capacitors for rapid charging/discharging circuits.

(7) Surge Voltage

The Surge voltage rating is referred as the maximum DC overvoltage that may be applied to an electrolytic capacitor for a short time interval of 30 seconds at infrequent time intervals not exceeding 5.5minutes with a limiting resistance of $1k\Omega$. Unless otherwise described on the catalogue or product specifications, please do not apply a voltage exceeding the capacitor's voltage rating. The rated surge voltages corresponding to rated voltages of electrolytic capacitors are presented as follows:

Rated Voltage(V)	4	6.3	10	16	25	35	50
Surge Voltage(V)	4.6	7.3	11.5	18.4	28.8	40.3	57.5
Rated Voltage(V)	63	80	100	160	180	200	250
Surge Voltage(V)	72.5	92	115	184	207	230	288
Rated Voltage(V)	315	350	400	420	450	500	525
Surge Voltage(V)	347	385	440	462	495	550	578

(8) Condition of Use

The capacitors shall NOT be exposed to:

- (a) Fluids including water, saltwater spray, oil, fumes, highly humid or condensed climates, etc.
- (b) Ambient conditions containing hazardous gases/fumes like hydrogen sulfide, sulfuric acid, nitrous acid, chlorine or bromine gas, ammonia, etc.
- (c) Exposed to ozone, ultraviolet rays and radiation.
- (d) Severe vibrations or physical shocks that exceeds the specifications mentioned in this catalogue.

(9) Circuit Design Consideration

- (a) Please ensure whether application, operating and mounting conditions satisfy the conditions specified in the catalog before installation of a capacitor. Please consult Lelon, if any of the conditions are beyond the conditions specified in the catalog.
- (b) Heat-generating components or heat sinks should not be placed closer to Aluminum electrolytic capacitors on the PCB to avoid their premature failure. A cooling system is recommended to improve their reliable working.
- (c) Electrical characteristics and performance of aluminum electrolytic capacitors are affected by variation of applied voltage, ripple current, ripple frequency and operating temperature. Therefore, these parameters shall not exceed specified values in the catalog.
- (d) Aluminum capacitors may be connected in the parallel fashion for increasing total capacitance and/or for achieving higher ripple current capability. But, such design may cause unequal current flow through each of the capacitors due to differences in their impedances.
- (e) When two or more capacitors are connected in series, voltage across each capacitor may differ and fall below the applied voltage. A resistor should be placed across each capacitor so as to match applied voltage with voltage across a capacitor.
- (f) Please consult Lelon while selecting a capacitor for high-frequency switching circuit or a circuit that undergoes rapid charging/discharging
- (g) Standard outer sleeve of the capacitor is not a perfect electrical insulator therefore is unsuitable for the applications that requires perfect electrical insulation. Please consult Lelon, if your application requires perfect electrical insulation.
- (h) Tilting or twisting capacitor body is not recommended once it is soldered to the PCB.

2. Caution for Assembling Capacitors

(1) Mounting


- (a) Aluminum electrolytic capacitors are not recommended to reuse in other circuits once they are mounted and powered in a circuit.

- (b) Aluminum electrolytic capacitors may hold static charge between its anode and cathode, which is recommended to be discharged through a $1\text{k}\Omega$ resistor before re-use.
- (c) A long storage of capacitors may result into its insulation deterioration. This can lead to a high leakage current when voltage is applied that may damage the capacitor. Capacitors following a long storage period must undergo voltage treatment/re-forming.
- Capacitors are charged by applying rated DC voltage through a resistor of $1\text{k}\Omega$ in series at least for an hour. It is recommended to increase applied voltage gradually using a voltage regulator unit once capacitors are assembled on the board. The charging should be followed by discharging through a $1\text{k}\Omega$ resistor.
- (d) Please check capacitor rated voltage before mounting.
- (e) Please check capacitor polarity before mounting.
- (f) Please don't drop capacitor on the floor / hard object.
- (g) Please don't deform the capacitor during installation.
- (h) Please confirm whether the lead spacing of the capacitors match with its pad spacing / footprint on PCB prior to installation.
- (i) Please avoid excessive mechanical shocks to capacitor during the auto-insertion process, inspection or centering operations.
- (j) Please don't place any wiring or circuit over the capacitor's pressure relief vent. The pressure relief vent may fail to open if adequate clearance space is not provided. Following table shows minimum clearance space required for different case diameters.


Case Diameter	$\phi 6.3 \sim \phi 16$	$\phi 18 \sim \phi 35$	$\phi 40$ or above
Clearance (min)	2 mm	3 mm	5 mm

(2) Soldering


- (a) Please confirm that soldering conditions, especially temperature and contact time are within our specifications. Dip or flow preheat temperature is 150°C with 120 seconds (max.), the soldering temperature should be limited at $260 \pm 5^\circ\text{C}$ for 10 ± 1 sec while manual soldering using soldering iron should be limited at $350 \pm 5^\circ\text{C}$ for 3 +1/-0 seconds. Please do not dip capacitor body into molten solder. A capacitor's life will be negatively affected if these conditions are violated.
- (b) Storage of capacitors in high humidity conditions is likely to affect the solder-ability of lead wires and terminals.



(a)



(b)



3. Maintenance Inspection

Periodical inspection of aluminum capacitors is absolutely necessary, especially when they are used with industrial equipment. The following items should be checked:

- (1) Appearance: Bloated, vent operated, leaked, etc.
- (2) Electrical characteristic: Capacitance, $\text{Tan } \delta$, leakage current, and other specified items listed in specification.

Lelon recommend replacing the capacitors if any of the abovementioned items fail to meet specifications.

- (c) **Reflow soldering should ONLY be used for SMD type capacitors.** The temperature and duration shall not exceed the specified temperature and duration in the specification. If the temperature or duration is higher than the value specified, please consult Lelon before usage.
- (d) Standard aluminum electrolytic capacitors are not designed to withstand multiple reflow processes. Please consult Lelon if repeated reflowing is unavoidable.
- (e) Incorrect mounting on PCB with improper external strength applied on its lead wires or capacitor body after soldering may damage a capacitor's internal structure, cause short circuit, or lead to high leakage current issues. Do not bend or twist the capacitor body after soldering. Referring to the drawings below only case (i) is recommended.
 - (i) Correct soldering
 - (ii) Hole-to-hole spacing on PCB differs from the lead space of lead wires.
 - (iii) Lead wires are bent after soldering.
 - (iv) Capacitor body doesn't stand vertical on PCB after soldering.

(3) Cleaning Circuit Boards after Soldering

- (a) Following chemicals are not recommended for cleaning: Solvent containing halogen ions, Alkaline solvent, Xylene, Acetone, Terpene, petro-based solvent.
- (b) Recommended cleaning conditions: Fatty-alcohol - Pine Alpha ST-100S, Clean Through-750H and IPA (isopropyl alcohol) are examples of the most acceptable cleaning agents. Temperature of the cleaning agent must not exceed 60°C . Flux content in the cleaning agents should be limited to 2 Wt. %. Overall length of cleaning process (e.g., immersion, ultrasonic or other) shall be within 5 minutes (5 ~ 7mm height within 3 minutes). CFC substitute cleaning agents such as AK225AES can also be used for cleaning. In this case, its temperature shall not exceed 40°C and cleaning process (e.g., immersion, ultrasonic or other) shall be completed within 2 ~ 3 minutes. After cleaning capacitors should be dried with hot air for at least 10 minutes along with the PCB. Temperature of hot air shall not exceed maximum category temperature of the capacitor. Insufficient drying may cause appearance defects, sleeve shrinkage, and bottom-plate bulging. However, usage of this CFC substitute must completely regulated for protection of environment.

4. Storage

- (1) The most suitable conditions for aluminum capacitor storage are $5^\circ\text{C} \sim 35^\circ\text{C}$ and indoor relative humidity less than 75%. High temperature and/or humidity storage is detrimental to the capacitors.
- (2) Capacitors shall not be stored in wet or damp atmospheres containing water, brine, fumes or oil.
- (3) Capacitors storage area shall neither be exposed to hazardous gases such as hydrogen sulfide, sulfuric acid, nitrous acid, chlorine, ammonium, etc. nor to acidic or alkaline solutions.
- (4) Capacitors shall not be exposed to ozone, ultraviolet rays or radiation.

5. Estimation of life time

$$L_r = L_0 \times 2^{\frac{T_{0\max} - T_{r\max}}{10}}$$

L_r : Estimated lifetime (hours)

L_0 : Base lifetime specified at maximum operating temperature with applied the DC voltage and the ripple current (hours)

$T_{0\max}$: The core temperature that rated ripple current applied at maximum operating temperature.

$T_{r\max}$: The core temperature that applied actual ripple current at ambient temperature.

6. Disposal

Please consult with a local industrial waste disposal specialist when disposing of aluminum electrolytic capacitors

7. Environmental Consideration

Lelon already have received IECQ QC 080000 certificate. Cadmium (Cd), Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr⁺⁶), PBB, PBDE, DEHP, BBP, DBP and DIBP have never been using in capacitor. If you need "Halogen-free" products, please consult with us.

8. AEC-Q200 Compliance

Automotive Electronics Counsel (AEC) has established various electronic component qualification/reliability standards in order to serve automotive electronics industry. AEC-Q200 standard is dedicated for passive components like capacitors, inductors, etc. and is widely adopted domestically as well as internationally.

Lelon offers compliant product designs and support services to satisfy customers' product requirements, including the AEC-Q200 required criteria of the reliability tests. Lelon's capacitors are professionally designed to outperform all requirements of AEC-Q200.

For further details, please refer to

IEC 60384-4- Fixed capacitors for use in electronic equipment – Part 4: Sectional specification – Aluminum electrolytic capacitors with solid (MnO₂) and non-solid electrolyte (Established in January 1995, Revised in March 2007), and

JEITA RCR-2367D- Safety application guide for fixed aluminum electrolytic capacitors for use in electronic equipment (Established in March 1995, Revised in October 2017)