



D ON		E NAME			
ECN NO.		NAME		DATE	
Part No	CKT	A	B	C	D
WF-PA2.0-2PE1	2	2.00	4.55	7.95	6.10
WF-PA2.0-3PE1	3	4.00	6.55	9.95	8.10
WF-PA2.0-4PE1	4	6.00	8.55	11.95	10.10
WF-PA2.0-5PE1	5	8.00	10.55	13.95	12.10
WF-PA2.0-6PE1	6	10.00	12.55	15.95	14.10
WF-PA2.0-7PE1	7	12.00	14.55	17.95	16.10
WF-PA2.0-8PE1	8	14.00	16.55	19.95	18.10
WF-PA2.0-9PE1	9	16.00	18.55	21.95	20.10
WF-PA2.0-10PE1	10	18.00	20.55	23.95	22.10
WF-PA2.0-11PE1	11	20.00	22.55	25.95	24.10
WF-PA2.0-12PE1	12	22.00	24.55	27.95	26.10
WF-PA2.0-13PE1	13	24.00	26.55	29.95	28.10
WF-PA2.0-14PE1	14	26.00	28.55	31.95	30.10
WF-PA2.0-15PE1	15	28.00	30.55	33.95	32.10
WF-PA2.0-16PE1	16	30.00	32.55	35.95	34.10

序号	品名	材质
1	2.0 R型卧式WTB胶芯 2.0 Pitch R/A Wire To Board Housing(H=5.7)	PA6T UL94V-0 米黄色 LCP UL94V-0 本色
2	2.0 R型立式WTB端子 2.0 Pitch S/T Wire To Board Terminal(H=8.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
3	2.0 R型卧式WTB焊片 2.0 Pitch R/A Wire To Board Fitting Nail(H=5.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
4	2.0 R型立式WTB吸盖 2.0 Pitch S/T Wire To Board Cover(H=8.7)	LCP UL94V-0 黑色/本色

技术指标(Technical Index):

- 1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.工作温度(Temperature range):-25°C~+85°C.
- 3.额定电压(Rated voltage):250V, AC/DC.
- 4.额定电流:3.0A,AC/DC.
- 5.接触电阻(Contact resistance):≤20mΩ.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.
- 7.耐电压(Withstanding Voltage):800V AC/minute.

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					 	
DIM. x. x.x x.xx GENERAL ANGLE: x: GENERAL	TOL. ±0.50 ±0.20 ±0.10 ±1°	TITLE: 2.00Pitch R型立式WTB						
		DWG. NO.: WF-PA2.0-XPE1			CHECKED: MAX			
		PART NO.: WF-PA2.0-XPE1			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	