








F		F		F	
修订	标记	修改摘要	签名	日期	
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE	
AO		NEW DWG	黄艳兰		





P.C.B Layout



B-B



A-A



Poles	Dimension(mm)			
	A	B	C	D
3	3.00	6.60	5.50	7.02
4	4.50	8.10	7.00	8.52
5	6.00	9.60	8.50	10.02
6	7.50	11.10	10.00	11.52
7	9.00	12.60	11.50	13.02
8	10.50	14.10	13.00	14.52
9	12.00	15.60	14.50	16.02

NOTES:

- Material:
Insulation: LCP,UL94V-0(Natural)
Pin:Phosphor Bronze/See Code/Nickel 50u" min. Over All.
Pin:Brass/Tin 80u" min. /Nickel 50u" min. Over All.
- Current Rating: 1.5A AC,DC
- Voltage Rating: 150V AC,DC
- Temperature Rang: -40°C~+125°C
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 100MΩ Min
- Withstanding Voltage: 1000V AC/minute



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: 1.5MM间距灯条板对板连接器	
X.X ±0.30	X.X* ±3°	APPD: 核准: 谢亮	PART NO: 产品编号: D1504RSG1-xP
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.15	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
			1:1
			mm
			A001