

编号

2X01

Technical drawing of a mechanical part, likely a bracket or support, showing dimensions in millimeters (mm). The drawing includes a side view and a top view.

Dimensions:

- Overall height: 14.30 ± 0.25
- Height of the lower section: 7.70 ± 0.20
- Width of the lower section: 8.50 ± 0.20
- Width of the upper section: 5.40 ± 0.20

The drawing shows a base with a central rectangular cutout. The top view shows a rectangular plate with a central rectangular cutout, and a side view shows a vertical plate with a central rectangular cutout. The dimensions are indicated by dimension lines and arrows.

- 1.Current Rating:5A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25°C~+85°C
- 4.Contact Resistance:20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material:Wafer PA66 Black
PIN Brass Tin-plated

