






PIN	尺寸 (mm)		
	A	B	C
02	2.50	7.40	6.50
03	5.00	9.90	9.00
04	7.50	12.40	11.50
05	10.00	14.90	14.00
06	12.50	17.40	16.50
07	15.00	19.90	19.00
08	17.50	22.40	21.50
09	20.00	24.90	24.00
10	22.50	27.40	26.50



- 1.Current Rating:3A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25℃~+85℃
- 4.Contact Resistance:20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material:Wafer PA66
PIN Brass Tin-plated



1	基座	PA66	本色	
序 号	品 名	材 质	电镀/颜色	备 注

品 名 TITLE	胶壳
料 号 PART NO	HC-JK-5264-8Y

GENERAL TOLERANCES (UNLESS SPECIFIED)		比例 SCALE	1:1			
X.±0.25	X.±2°	单位 UNIT	MM	制图 DRAW	AhYe	
±0.25	±1°	张数 PART NO	1 OF 1	审核 CHECKED	夏操云	
.XX±0.15	.XX°±0.5°	版本 REV	A	批准 APPROVE	赵亮亮	
.XXX±0.10	.XXX°±0.5°					