





SECTION A-A



2 PIN 3 PIN


LOCK CONFIGURATION(锁扣位置)






Part No	CKT	A	B	C
ZX-MX1.25-2PWZ-BD	2	1.25	3.20	4.30
ZX-MX1.25-3PWZ-BD	3	2.50	4.45	5.55
ZX-MX1.25-4PWZ-BD	4	3.75	5.70	6.80
ZX-MX1.25-5PWZ-BD	5	5.00	6.95	8.05
ZX-MX1.25-6PWZ-BD	6	6.25	8.20	9.30
ZX-MX1.25-7PWZ-BD	7	7.50	9.45	10.55
ZX-MX1.25-8PWZ-BD	8	8.75	10.70	11.80
ZX-MX1.25-9PWZ-BD	9	10.00	11.95	13.05
ZX-MX1.25-10PWZ-BD	10	11.25	13.20	14.30
ZX-MX1.25-11PWZ-BD	11	12.50	14.45	15.55
ZX-MX1.25-12PWZ-BD	12	13.75	15.70	16.80
ZX-MX1.25-13PWZ-BD	13	15.00	16.95	18.05
ZX-MX1.25-14PWZ-BD	14	16.25	18.20	19.30
ZX-MX1.25-15PWZ-BD	15	17.50	19.45	20.55
ZX-MX1.25-16PWZ-BD	16	18.75	20.70	21.80
ZX-MX1.25-17PWZ-BD	17	20.00	21.95	23.05
ZX-MX1.25-18PWZ-BD	18	21.25	23.20	24.30
ZX-MX1.25-19PWZ-BD	19	22.50	24.45	25.55
ZX-MX1.25-20PWZ-BD	20	23.75	25.70	26.80

技术指标(Technical Index):




1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
2. 锁扣窗口: 2~3PIN为1个, >4PIN为2个。
(Lock Configuration: 2 to 3Pin is 1, >4Pin is 2)
3. 温度范围(Temperature range): -25°C~+85°C.
4. 额定电压(Rated voltage): 125V, AC/DC (=等效).
5. 接触电阻(Contact resistance): $\leq 0.02\Omega$.
6. 绝缘电阻(Insulation resistance): $\geq 100M\Omega$.




制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-MX1.25-NPWZ-BD	版本 REV.	A
			X.:±0.50	±1°	审核 CHECK	LEO			品名 TITLE	1.25 Pitch A型弯针WTB	页次 SHEET	1/1
			X.X:±0.20		核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			X.XX:±0.10		单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			



- NOTE(注):
- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
 - 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弧形MAX:1/100mm.)
 - 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)
 - 4.MATERIAL: CLEAR ANTISTATIC PS.
(载带材料:透明 PS.)
 - 5.THICKNESS: $0.40 \pm 0.05\text{mm}$. (载带厚度: $0.40 \pm 0.05\text{mm}$.)
 - 6.PACKING LENGTH PER REEL: 10.56 METERS. (每卷包装长度: 10.56米.)
 - 7.COMPONENT LOAD PER REEL: 850 PCS. (每卷包装数量: 850片, 前后各空包15片.)
 - 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
 - 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



纸箱型号	小型	中型	标准型
Carton Type	Small Size	Medium	Standard
高度			
Hight (CM)	7.5	15	32



CKT (1.25mm pitch)	B0	W	F	S
2	4.60	16	7.50	
3	5.85			
4	7.10			
5	8.35			
6	9.60			
7	10.85	24	11.50	
8	12.10			
9	13.35			
10	14.60			
11	15.85			
12	17.10			
13	18.35	32	14.2±0.10	28.45
14	19.60			
15	20.85			
16	22.10			
17	23.35			
18	25.85	44	20.2±0.15	40.45
19	28.35			
20	30.85			

CKT (1.25mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	850	14	11900
3				
4				
5				
6				
7	24	850	10	8500
8				
9				
10				
11				
12				
13	32	850	8	6800
14				
15				
16				
17				
18	44	850	6	5100
19				
20				

制图	变更内容	日期	GENERAL TOLERANCE	制图	ROSE	料号	ZX-MX1.25-NPWZ-BD	版本	A
DRAWN	DESCRIPTION	DATE	X.:±0.50	±1°	DRAWING	PART NO.		REV.	
			X.X:±0.25		审核	品名	1.25-A型弯针WTB载带包装	页次	1/1
			X.XX:±0.15		批准	客户料号		SHEET	
					APPROVAL	CUTM.NO.			
					单位	MM			
					比例	SCALE	1:1		



兆星精密电子(深圳)有限公司
ShenZhen ZhaoXing Precision electronics Co., Ltd.