



DUAL TRANSISTOR (NPN+PNP)

FEATURES

- Complementary Pair
- One 4401-Type NPN
One 4403-Type PNP
- Epitaxial Planar Die Construction
- Ideal for Low Power Amplification and Switching



SOT-363



MARKING: K13

Maximum Ratings, NPN 4401 Section (Ta = 25°C unless otherwise specified)

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	60	V
V_{CEO}	Collector-Emitter Voltage	40	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current -Continuous	0.6	A
P_C	Collector Power Dissipation	0.2	W
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient	625	°C/W
T_J, T_{stg}	Operation Junction and Storage Temperature Range	-55 ~ +150	°C

NPN 4401 ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = 100 \mu A, I_E = 0$	60		V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = 1 mA, I_B = 0$	40		V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E = 100 \mu A, I_C = 0$	6		V
Collector cut-off current	I_{CBO}	$V_{CB} = 50 V, I_E = 0$		0.1	μA
Collector cut-off current	I_{CEO}	$V_{CE} = 35 V, I_B = 0$		0.5	μA
Emitter cut-off current	I_{EBO}	$V_{EB} = 5 V, I_C = 0$		0.1	μA
DC current gain	$h_{FE(1)}$	$V_{CE} = 1 V, I_C = 0.1 mA$	20		
	$h_{FE(2)}$	$V_{CE} = 1 V, I_C = 1 mA$	40		
	$h_{FE(3)}$	$V_{CE} = 1 V, I_C = 10 mA$	80		
	$h_{FE(4)}$	$V_{CE} = 1 V, I_C = 150 mA$	100	300	
	$h_{FE(5)}$	$V_{CE} = 2 V, I_C = 500 mA$	40		
Collector-emitter saturation voltage	$V_{CE(sat)1}$	$I_C = 150 mA, I_B = 15 mA$		0.4	V
	$V_{CE(sat)2}$	$I_C = 500 mA, I_B = 50 mA$		0.75	V
Base-emitter saturation voltage	$V_{BE(sat)1}$	$I_C = 150 mA, I_B = 15 mA$	0.75	0.95	V
	$V_{BE(sat)2}$	$I_C = 500 mA, I_B = 50 mA$		1.2	V
Transition frequency	f_T	$V_{CE} = 10 V, I_C = 20 mA, f = 100 MHz$	250		MHz
Output Capacitance	C_{ob}	$V_{CB} = 5 V, I_E = 0, f = 1 MHz$		6.5	pF
Delay time	t_d	$V_{CC} = 30 V, V_{BE} = 2.0 V, I_C = 150 mA, I_{B1} = 15 mA$		15	nS
Rise time	t_r			20	nS
Storage time	t_s	$V_{CC} = 30 V, I_C = 150 mA, I_{B1} = -I_{B2} = 15 mA$		225	nS
Fall time	t_f			30	nS

Maximum Ratings, PNP 4403 Section (Ta = 25°C unless otherwise specified)







Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	-40	V
V_{CEO}	Collector-Emitter Voltage	-40	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current -Continuous	-0.6	A
P_C	Collector Power Dissipation	0.2	W
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient	625	°C/W
T_J, T_{stg}	Operation Junction and Storage Temperature Range	-55 ~ +150	°C

PNP 4403 ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise specified)







Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = -100\mu A, I_E = 0$	-40			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = -1mA, I_B = 0$	-40			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E = -100\mu A, I_C = 0$	-5			V
Collector cut-off current	I_{CBO}	$V_{CB} = -50V, I_E = 0$			-0.1	μA
Collector cut-off current	I_{CEO}	$V_{CE} = -35V, I_B = 0$			-0.5	μA
Emitter cut-off current	I_{EBO}	$V_{EB} = -5V, I_C = 0$			-0.1	μA
DC current gain	$h_{FE(1)}$	$V_{CE} = -1V, I_C = -0.1mA$	30			
	$h_{FE(2)}$	$V_{CE} = -1V, I_C = -1mA$	60			
	$h_{FE(3)}$	$V_{CE} = -1V, I_C = -10mA$	100			
	$h_{FE(4)}$	$V_{CE} = -2V, I_C = -150mA$	100		300	
	$h_{FE(5)}$	$V_{CE} = -2V, I_C = -500mA$	20			
Collector-emitter saturation voltage	$V_{CE(sat)1}$	$I_C = -150mA, I_B = -15mA$			-0.4	V
	$V_{CE(sat)2}$	$I_C = -500mA, I_B = -50mA$			-0.75	V
Base-emitter saturation voltage	$V_{BE(sat)1}$	$I_C = -150mA, I_B = -15mA$	-0.75		-0.95	V
	$V_{BE(sat)2}$	$I_C = -500mA, I_B = -50mA$			-1.3	V
Transition frequency	f_T	$V_{CE} = -10V, I_C = -20mA$ $f = 100MHz$	200			MHz
Output Capacitance	C_{ob}	$V_{CB} = -10V, I_E = 0$ $f = 1MHz$			8.5	pF
Delay time	t_d	$V_{CC} = -30V, V_{BE} = -2V$ $I_C = -150mA, I_{B1} = -15mA$			15	nS
Rise time	t_r				20	nS
Storage time	t_s	$V_{CC} = -30V, I_C = -150mA$ $I_{B1} = -I_{B2} = -15mA$			225	nS
Fall time	t_f				30	nS

Typical Characteristics

NPN Transistor




PNP Transistor



Plastic surface mounted package

SOT-363



SOLDERING FOOTPRINT

