



Description

The IP4220CZ6,125-JSM is an ultra low capacitance TVS array, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive high-speed data lines.

The IP4220CZ6,125-JSM has an ultra-low capacitance with a typical value at 0.6 pF, and complies with the IEC 61000-4-2 (ESD) standard with $\pm 15\text{kV}$ air and $\pm 8\text{kV}$ contact discharge. It is assembled into a 6-pin lead-free SOT23-6 package. The combination of small size, ultra low capacitance, and high ESD surge capability make it ideal for use in applications such as multimedia, and other high speed ports.



SOT23-6



Circuit Diagram

Features

- ◆ Ultra low capacitance: 0.6pF typical (I/O-GND)
- ◆ Ultra low leakage: nA level
- ◆ Low operating voltage: 5.0V
- ◆ Up to 4 data lines and one power line protects
- ◆ Low clamping voltage
- ◆ Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 - Air : $\pm 20\text{kV}$; discharge: $\pm 15\text{kV}$
 - IEC61000-4-5 (Lightning) 4.5A (8/20 μs)
- ◆ SOT23-6 Package
- ◆ RoHS Compliant

Applications

- ◆ Monitors and flat panel displays
- ◆ Set-top box and Digital TV
- ◆ Video graphics cards
- ◆ Digital Video Interface (DVI)
- ◆ Notebook Computers
- ◆ PCI Express and Serial SATA Ports


Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs , I/O-GND)	Ppk	60	W
Peak Pulse Power (8/20 μs , Vcc-GND)	Ppk	300	W
Peak Pulse Current (8/20 μs , I/O-GND)	IPP	4.5	A
Peak Pulse Current (8/20 μs , Vcc-GND)	IPP	17	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD,VDD VESD,I/O	$\pm 20\pm 15$	kV
Operating Temperature Range	TJ	-55 to +125	$^{\circ}\text{C}$
Storage Temperature Range	Tstg	-55 to +150	$^{\circ}\text{C}$


Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	VRWM	Pin 5 to GND, I/O-GND			5.0	V
Breakdown Voltage	VBR	IT= 1mA(Pin 5 to GND, I/O_GND)	6.0	7.5	8.5	V
Reverse Leakage Current	IR	VRWM= 5.0V			0.5	μA
Forward Breakdown Voltage	VF	IF = 15mA, GND to Pin 5/I/O		0.8	1.0	V
Clamping Voltage	VC	IPP = 4.5A (8 x 20 μs pulse, I/O to GND)		14.0	15.0	V
Clamping Voltage	VC	IPP = 17A (8 x 20 μs pulse, Pin 5 to GND)		16.0	18.0	V
Junction Capacitance	CJ	Vpin5= 5V, I/O=0V, f = 1MHz, I/O-GND		0.6	0.7	pF
Junction Capacitance	CJ	Vpin5= 5V, I/O=0V, f = 1MHz, I/O-I/O pins		0.3	0.4	pF


Typical Performance Characteristics ($T_A=25^\circ\text{C}$ unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Clamping Voltage vs. Peak Pulse Current




Peak Pulse Power vs. Pulse Time



IEC61000-4-2 Pulse Waveform




Power Derating Curve




8 X 20us Pulse Waveform

SOT23-6 Package Outline Drawing



SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.90		1.45	0.035		0.057
A1	0.00		0.15	0.000		0.006
A2	0.90	1.15	1.30	0.035	0.045	0.051
b	0.25		0.50	0.010		0.020
c	0.08		0.22	0.003		0.009
D	2.80	2.90	3.10	0.110	0.114	0.122
E1	1.50	1.60	1.75	0.060	0.063	0.069
E	2.80 BSC			0.110 BSC		
e	0.95 BSC			0.037 BSC		
e1	1.90 BSC			0.075 BSC		
N	6			6		
aaa	0.10			0.004		
ccc	0.20			0.008		

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
C	2.50	0.098
G	1.40	0.055
P	0.95	0.037
X	0.60	0.024
Y	1.10	0.043
Z	3.60	0.141

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2024

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com