









技术指标(Technical Index):

- 1.工作温度(Temperature range):-40°C~125°C.
- 2.额定电压(Rated voltage):200V DC/AC(rms).
- 3.额定电流(Rated current):2.0A.
- 4.接触电阻(Contact resistance):≤25mΩ.
- 5.耐压值(Withstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.








SECTION A-A




Part No	CKT	A	B
BX-PH2.0-2PWZ-BD	2	2.0	6.0
BX-PH2.0-3PWZ-BD	3	4.0	8.0
BX-PH2.0-4PWZ-BD	4	6.0	10.0
BX-PH2.0-5PWZ-BD	5	8.0	12.0
BX-PH2.0-6PWZ-BD	6	10.0	14.0
BX-PH2.0-7PWZ-BD	7	12.0	16.0
BX-PH2.0-8PWZ-BD	8	14.0	18.0
BX-PH2.0-9PWZ-BD	9	16.0	20.0
BX-PH2.0-10PWZ-BD	10	18.0	22.0
BX-PH2.0-11PWZ-BD	11	20.0	24.0
BX-PH2.0-12PWZ-BD	12	22.0	26.0
BX-PH2.0-13PWZ-BD	13	24.0	28.0
BX-PH2.0-14PWZ-BD	14	26.0	30.0
BX-PH2.0-15PWZ-BD	15	28.0	32.0
BX-PH2.0-16PWZ-BD	16	30.0	34.0
BX-PH2.0-17PWZ-BD	17	32.0	36.0
BX-PH2.0-18PWZ-BD	18	34.0	38.0
BX-PH2.0-19PWZ-BD	19	36.0	40.0
BX-PH2.0-20PWZ-BD	20	38.0	42.0

序号	品名	材质
①	PH2.0弯针WTB胶芯	LCP UL94V-0 本色
②	PH2.0弯针WTB端子	铜合金/表面镀锡

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX—PH2.0—NPWZ—BD		版本 REV.	A	
			X.±0.50	±1°										
			.X±0.20											
			.XX±0.10											
					审核 CHECK	EVA			品名 TITLE	PH2.0弯针WTB		页次 SHEET	1/1	
					核准 APPROVAL	JADE			客户料号 CUTM.NO.					
					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)					



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32



CKT (2.0mm pitch)	B0	W	F	S
2	6.30	16	7.50	
3	8.30			
4	10.30			
5	12.30			
6	14.30			
7	16.30			
8	18.30	32	14.20±0.10	28.40
9	20.30			
10	22.30			
11	24.30			
12	26.30	44	20.20±0.10	40.40
13	28.30			
14	30.30			
15	32.30			
16	34.30			
17	36.30			
18	38.30	56	26.20±0.10	52.40
19	40.30			
20	42.30			

NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弧形MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.
(载带材料: 透明抗静电 PS, 冷封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 7.68 METERS. (每卷包装长度: 7.68米.)
- 7.COMPONENT LOAD PER REEL: 600 PCS. (每卷包装数量: 600只, 前后各空20只.)
- 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
- 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.

CKT (2.0mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	600	14	8400
3				
4				
5	24	600	10	6000
6				
7				
8	32	600	8	4800
9				
10				
11				
12	44	600	6	3600
13				
14				
15				
16				
17	56	600	5	3000
18				
19				
20				

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA
			X.±0.50	审核 CHECK	EVA
			.X±0.20	批准 APPROVAL	JADE
			.XX±0.10	单位 UNITS	MM
				比例 SCALE	1:1

料号 PART NO.	BX-PH2.0-NPWZ-BD	版本 REV.	A
品名 TITLE	PH2.0弯针WTB	页次 SHEET	1/1
客户料号 CUTM.NO.			

Bossie (博锡)