










SECTION A-A



技术指标(Technical Index):





- 1.温度范围(Temperature range):-25°C~+85°C.
- 2.额定电压(Rated voltage):200V,AC.
- 3.额定电流(Rated current):2.0A AC,DC.
- 4.接触电阻(Contact resistance):≤25mΩ.
- 5.耐压值(Withstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.

Part No	CKT	A	B
ZX-HY2.0-2PZZ-BD	2	2.0	6.0
ZX-HY2.0-3PZZ-BD	3	4.0	8.0
ZX-HY2.0-4PZZ-BD	4	6.0	10.0
ZX-HY2.0-5PZZ-BD	5	8.0	12.0
ZX-HY2.0-6PZZ-BD	6	10.0	14.0
ZX-HY2.0-7PZZ-BD	7	12.0	16.0
ZX-HY2.0-8PZZ-BD	8	14.0	18.0
ZX-HY2.0-9PZZ-BD	9	16.0	20.0
ZX-HY2.0-10PZZ-BD	10	18.0	22.0
ZX-HY2.0-11PZZ-BD	11	20.0	24.0
ZX-HY2.0-12PZZ-BD	12	22.0	26.0
ZX-HY2.0-13PZZ-BD	13	24.0	28.0
ZX-HY2.0-14PZZ-BD	14	26.0	30.0
ZX-HY2.0-15PZZ-BD	15	28.0	32.0
ZX-HY2.0-16PZZ-BD	16	30.0	34.0
ZX-HY2.0-17PZZ-BD	17	32.0	36.0
ZX-HY2.0-18PZZ-BD	18	34.0	38.0
ZX-HY2.0-19PZZ-BD	19	36.0	40.0
ZX-HY2.0-20PZZ-BD	20	38.0	42.0



序号	品名	材质
①	HY2.0直针WTB胶芯	LCP UL94V-0 本色
②	HY2.0直针WTB端子	铜合金/表面镀锡
③	2.00 F型立式2代WTB吸盖	LCP UL94V-0 本色

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-HY2.0-NPZZ-BD	版本 REV.	A
			X.:±0.50	±1°					品名 TITLE	HY2.0直针WTB	页次 SHEET	1/1
			X.X:±0.20						客户料号 CUTM.NO.			
			X.XX:±0.10						核准 APPROVAL	JOHN		
					单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			



NOTE(注):

1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.

(10片孔距累积公差 $\pm 0.2\text{mm}$.)

2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.

(载带拱/弧形MAX:1/100mm.)

3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.

(所有的尺寸要满足协会EIA-481规范.)

4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.

(载带材料: 透明防静电 PS, 冷封.)




5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)

6.PACKING LENGTH PER REEL: 5.28 METERS. (每卷包装长度: 5.28米.)

7.COMPONENT LOAD PER REEL: 400 PCS. (每卷包装数量: 400片.)

8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保丽龙填充.

9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



纸箱型号	小型	中型	标准型
Carton Type	Small Size	Medium	Standard
高度	7.5	15	32
Hight (CM)			

CKT	B0	W	F	S
(2.0mm pitch)				
2	6.30	24	11.50	
3	8.30			
4	10.30			
5	12.30			
6	14.30	32	14.20±0.10	28.4
7	16.30			
8	18.30			
9	20.30			
10	22.30	44	20.20±0.10	40.40
11	24.30			
12	26.30			
13	28.30			
14	30.30	56	26.2±0.10	52.40
15	32.30			
16	34.30			
17	36.30			
18	38.30			
19	40.30			
20	42.30			

CKT	W	PCS/REEL	REEL/CARTON	SUM(PCS)
(2.0mm pitch)				
2	24	400	14	5600
3		400	10	4000
4		400	8	3200
5		400	6	2400
6	32	400	8	3200
7		400	6	2400
8		400	5	2000
9		400	4	1600
10	44	400	6	2400
11		400	5	2000
12		400	4	1600
13		400	3	1200
14	56	400	5	2000
15		400	4	1600
16		400	3	1200
17		400	2	800
18		400	1	400
19		400	1	400
20		400	1	400

制图	变更内容	日期	GENERAL TOLERANCE	制图
DRAWN	DESCRIPTION	DATE	X.:±0.50 ±1°	DRAWING
			X.X:±0.25	审核
			X.XX:±0.15	CHECK
				批准
				APPROVAL
				单位
				UNITS

料号	ZX-HY2.0-NPZZ-BD	版本	A
PART NO.		REV.	
品名	HY2.0直针WTB载带包装	页次	1/1
TITLE		SHEET	
客户料号			
CUTM.NO.			



兆星精密电子(深圳)有限公司
ShenZhen ZhaoXing Precision electronics Co., Ltd.