





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

SPECIFICATIONS


- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Phosphoric bronze Tin-plated
- 8.Applicable Wire Sizes: AWG#22~28#



SEC:A-A



SEC:B-B



1	端子	铜	镀锡	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	端子
料号 PART NO	HC-DZ-5264

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



X±0.25 X±2°

单 位
UNIT

MM

制 图
DRAW

AhYe

.X±0.25 .X°±1°

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

.XX±0.15 .XX°±0.5°

版 本
REV

A

批 准
APPROVE

赵亮亮

