

CMP220N04B/CMB220N04B/CMI220N04B/CMF220N04B

40V, 2.6mΩ typ., 220A N-Channel MOSFET

General Description

The 220N04B uses advanced trench technology to provide excellent $R_{DS(on)}$. This is suitable device for high current switching applications.

Product Summary

BVDSS	$R_{DS(on)}$ max.	ID
40V	3mΩ	220A


Applications

- Switching applications
- Motor Drive Applications

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant

TO-220/263/262/220F Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	220/263/262	220F	Units
V_{DS}	Drain-Source Voltage	40		V
V_{GS}	Gate-Source Voltage	±20		V
$I_D@T_C=25^{\circ}C$	Continuous Drain Current	220	220*	A
$I_D@T_C=100^{\circ}C$	Continuous Drain Current	154	154*	A
I_{DM}	Pulsed Drain Current	880	880*	A
EAS	Single Pulse Avalanche Energy (Note 1)	2664		mJ
$P_D@T_C=25^{\circ}C$	Total Power Dissipation	200	45	W
T_{STG}	Storage Temperature Range	-55 to 150		°C
T_J	Operating Junction Temperature Range	-55 to 150		°C

* Drain current limited by maximum junction temperature.

Thermal Data

Symbol	Parameter	220/263/262	220F	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient Max.	62	62	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-case Max.	0.63	2.78	°C/W

Electrical Characteristics (T_J=25°C , unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =250μA	40	---	---	V
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V , I _D =30A	---	2.6	3	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250μA	3	---	5	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =32V , V _{GS} =0V	---	---	1	μA
I _{GSS}	Gate-Source Leakage Current	V _{GS} = ±20V , V _{DS} =0V	---	---	±100	nA
g _{fs}	Forward Transconductance	V _{DS} =10V , I _D =30A	---	38	---	S
R _g	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz	---	4.7	---	Ω
Q _g	Total Gate Charge	V _{DD} =32V , I _D =80A V _{GS} =0 to 10V	---	108	---	nC
Q _{gs}	Gate-Source Charge		---	31	---	
Q _{gd}	Gate-Drain Charge		---	44	---	
T _{d(on)}	Turn-On Delay Time	V _{DD} =20V , V _{GS} =10V R _G =4.7Ω , I _D =60A	---	35	---	ns
T _r	Rise Time		---	220	---	
T _{d(off)}	Turn-Off Delay Time		---	80	---	
T _f	Fall Time		---	50	---	
C _{iss}	Input Capacitance	V _{DS} =25V , V _{GS} =0V , f=1MHz	---	5300	---	pF
C _{oss}	Output Capacitance		---	1300	---	
C _{rss}	Reverse Transfer Capacitance		---	500	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Diode continuous forward current	V _G =V _D =0V , Force Current	---	---	220	A
I _{S,pulse}	Diode pulse current		---	---	880	A
V _{SD}	Diode Forward Voltage	V _{GS} =0V , I _F =30A , T _J =25 °C	---	0.81	1.2	V

Note :







1.The EAS data shows Max. rating .The test condition is V_{DS}=40V , V_{GS}=10V , L=1mH , I_{AS}=73A.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.


Typical Characteristics




Package Dimension

TO-220

Unit :mm



DIM	MILLIMETERS
A	10.0±0.3
A1	8.64±0.2
A2	1.15±0.1
A3	5.0±0.2
B	15.8±0.4
B1	13.2±0.3
C	4.56±0.1
C1	1.3±0.2
D	0.8±0.2
E	3.6±0.2
F	2.95±0.3
G	6.5±0.3
H	0.5±0.1
K	3.1±0.2
L	13.2±0.4
M	1.25±0.1
N	2.54±0.1
P	2.4±0.3
Q	9.0±0.3
T	W:0.35
DIA	⊙1.5 (deep 0.2)


Package Dimension
TO-263
Unit :mm


DIM	MILLIMETERS
A	9.8 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	15.5 ± 0.3
h	1.54 ± 0.2
h1	10.5 ± 0.2
h2	9.2 ± 0.1
h3	1.54 ± 0.2
h4	2.7 ± 0.2
L	2.4 ± 0.2
1	1.3 ± 0.1
11	0.8 ± 0.1
12	1.3 ± 0.1
13	0.5 ± 0.1
N	2.54 ± 0.1
R	$0.5R \pm 0.05$

Package Dimension

TO-262

Unit :mm




DIM	MILLIMETERS
A	9.98 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	23.9 ± 0.3
h	3.1 ± 0.2
h1	9.16 ± 0.2
h2	13.2 ± 0.2
L	0.5 ± 0.1
11	1.3 ± 0.1
12	0.8 ± 0.1
N	2.45 ± 0.1

Package Dimension

TO-220F

Unit :mm



DIM	MILLIMETERS
A	10.16±0.3
A1	7.00±0.1
A2	3.3±0.2
A3	9.5±0.2
B1	15.87±0.3
B2	4.7±0.2
B3	6.68±0.4
C	3.3±0.2
C1	12.57±0.3
C2	10.02±0.5
D	2.54±0.05
D1	1.28±0.2
D2	0.8±0.1
K	3.1±0.3
E1	2.54±0.1
E3	0.5±0.1
E4	2.76±0.2
DIA	⌀1.5 (deep 0.2)