


Features

- For AF driver and output stages
- High collector current
- Low collector-emitter saturation voltage



SOT-223


Absolute Maximum Ratings $T_a = 25^\circ\text{C}$

Parameter	Symbol	Rating	Unit
collector-base voltage	V_{CB0}	100	V
collector-emitter voltage	V_{CE0}	80	V
emitter-base voltage	V_{EB0}	5	V
collector current (DC)	I_C	1	A
peak collector current ($t_p < 5\text{ms}$)	I_{CM}	1.5	A
power dissipation	P_D	1.5	W
thermal resistance from junction to ambient	$R_{\theta JA}$	94	$^\circ\text{C/W}$
junction temperature	T_j	150	$^\circ\text{C}$
storage temperature	T_{stg}	-65 to +150	$^\circ\text{C}$


Electrical Characteristics $T_a = 25^\circ\text{C}$

Parameter	Symbol	Testconditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = 0.1\text{mA}, I_E = 0$	100			
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = 10\text{mA}, I_B = 0$	80			
Base-emitter breakdown voltage	$V_{(BR)EBO}$	$I_C = 10\mu\text{A}, I_E = 0$	5			
Collector cut-off current	I_{CBO}	$I_E = 0\text{A}; V_{CB} = 30\text{V}$			100	nA
Emitter cut-off current	I_{EBO}	$I_C = 0\text{A}; V_{EB} = 5\text{V}$			100	nA
DC current gain	h_{FE}	$I_C = 5\text{mA}; V_{CE} = 2\text{V}$	25			
		$I_C = 150\text{mA}; V_{CE} = 2\text{V}$	100		250	
		$I_C = 500\text{mA}; V_{CE} = 2\text{V}$	25			
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = 500\text{mA}; I_B = 50\text{mA}$			0.5	V
Transition frequency	f_T	$I_C = 10\text{mA}; V_{CE} = 5\text{V}; f = 100\text{MHz}$		130		MHz


Typical Characteristics




Total power dissipation $P_{tot} = f(T_S)$




Transition frequency $f_T = f(I_C)$




DC current gain $h_{FE} = f(I_C)$




Collector cutoff current $I_{CBO} = f(T_A)$



Base-emitter saturation voltage




Collector-emitter saturation voltage



Permissible pulse load

Package Information

SOT-223



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.520	1.800	0.060	0.071
A1	0.000	0.100	0.000	0.004
A2	1.500	1.700	0.059	0.067
b	0.660	0.820	0.026	0.032
c	0.250	0.350	0.010	0.014
D	6.200	6.400	0.244	0.252
D1	2.900	3.100	0.114	0.122
E	3.300	3.700	0.130	0.146
E1	6.830	7.070	0.269	0.278
e	2.300(BSC)		0.091(BSC)	
e1	4.500	4.700	0.177	0.185
L	0.900	1.150	0.035	0.045
θ	0°	10°	0°	10°

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2024

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com