



深圳市佑驰电子有限公司

Specification for Approval

产品名称： 电感
规格型号： HCZC2915L-220M
产品编号：
日 期： 2021-7-14

- 1、本承诺书的内容更改需经过双方确认，任一方单独的修改均视为无效。
- 2、本承诺书在送达客户后，请给予承认并即签回，如无签回下订单的，我司有权以此承认书标准生产，并表示购买方默认许可。


	审核	制作

批准	审核	检验




Explanation of part numbers:

HCZC 2915 L - 220 M
 | | | | |
 Series Codes Size Codes DCR Type Inductance Codes Tolerance

Schematic:




Product dimensions:(mm)



A	27.9Max.	a	16.6Ref.
B	27.9Max.	b	4.8Ref.
B2	19.7Max.	c	6.35Ref.
C	15.5Max.	d	5.28Ref.
D	3.8Ref.	e	5.4Ref.
E	3.8Ref.	f	5.6Ref.
F	6.6±0.5		
G	6.2Ref.		

PCB Layout:




Electrical characteristics:


Item P/N	Inductance	Heat Rating DC Current(I _{dc})	Saturation DC Current(I _{sat})	DCR	
	100KHz,0.1V				
	(μH)			(mΩ)	
	±20%			Typ.	Max.
HCZC2915L-220M	22.0	30.0	6.8	1.5	1.65

- All test data is referenced to 25°C ambient.
- I_{rms}:DC current(A) that will cause an approximate ΔT of 40°C.
- I_{sat}:DC current(A) that will cause L_o to drop approximate 30%.
- Operating temperature range: -40°C to 125°C .
- Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provision all affect the part temperature. Part temperature should be verified in the end application.

Typical Inductance vs. Current:



Typical Temperature Rise vs. Current:




A	B	C	D	E
260°C	230°C	8-10Sec	150°C	60~240Sec

TEST	Specification & Requirement	Method Used
Solderability	The surface of terminal/pin tested shall be covered with new solder by 95%	Solder heat proof.
		Preheating:180±10°C 90 seconds
		Soldering:255±5°C for 3±1 sec
Shock	Inductance change within ±5% Without mechanical damage	Drop down with 981m/s2 (100G) shock
		Attitude upon a rubber block method shock testing machinem, 3 tests.
Vibration	Inductance change within ±5% Without mechanical damage	Vibration frequency:10Hz to 55Hz to 10Hz, 60 seconds cycle
		Vibration time: 2 hours

TEST	Specification & Requirement	Method Used
Thermal Shock	Inductance change within $\pm 5\%$ Without mechanical damage	-25°C, (30 mins) -> room temp. (5 mins) -> 125°C, (30 mins) -> room temp. (5 mins) 100 cycles
Heat Resistance	Inductance change within $\pm 5\%$ Without mechanical damage	Apply IDC current @ 85°C ambient Duration: 1000 hrs
Humidity Resistance	Inductance change within $\pm 5\%$ Without mechanical damage	Apply IDC current @ 60°C ambient Humidity: 90~95% Duration: 1000 hrs
Low Temp. Storing	Inductance change within $\pm 5\%$ Without mechanical damage	Storing Temp. -25 $\pm$ 2°C for total 1,000+4/-0 hours
High Temp. Storing	Inductance change within $\pm 5\%$ Without mechanical damage	Storing Temp. 125 $\pm$ 2°C for total 1,000+4/-0 hours

Packing information:



Unit:(mm)

A	B	C	L	W	H	Plastic Plate (pcs/PET Box)	N layers (per box)	Outer Box (pcs/ Box)
322	202	24	340	215	220	35	8	280