








RoHS
Compliant

ZONE	E C N . N O .	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2023.06.19




NOTES:

1. MECHANICAL PERFORMANCE,
 - 1-1. INSERTION FORCE: 5N-20N.
 - 1-2. REMOVAL FORCE: 5N-20N.
 - 1-3. DURABILITY: 10000 CYCLES.
2. ELECTRICAL PERFORMANCE,
 - 2-1. CURRENT RATING: 5.0A
 - 2-2. LLC: VBUS & GND PINS AND OTHER PINS: 40mΩ/PIN MAX. SHIELD: 50mΩ/MAX.
 - 2-3. INSULATION RESISTANCE: 100MΩ MIN
 - 2-4. DIELECTRIC WITHSTAND VOLTAGE, AC 100V FOR 1 MINUTE.
3. ENVIRONMENTAL PERFORMANCE,
 - OPERATING TEMPERATURE: -25℃+85℃.



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$



ZB58002-24FBAP-A*

- 1: Au G/F
- 2: Au 1u"
- 3: Au 3u"
- 4: Au 15u"
- 5: Au 30u"

PIN ASSIGNMENTS:

PIN ASSIGNMENTS:																	
PIN No.	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12	⑥	EMI PLATE	1 PCS	SUS304 1/4H T=0.10	_____
SIGNAL NAME	GND	TX1+	TX1-	Vbus	CC1	D+	D-	SBU1	Vbus	RX2-	RX2+	GND	⑤	MID PLATE	1 PCS	SUS 301 3/4H T=0.12	_____
													④	SHELL	1 PCS	SUS 304-1/2H T=0.3	30u" Min. NI OVER ALL
PIN No.	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1	③	TERMINAL 2(12Pin)	1SET	C7025 TMO3 T=0.12	Under Plating: Ni 30u" Contact Plating: Au(See No)
													②	TERMINAL 1(12Pin)	1SET	C7025 TMO3 T=0.12	Soldering Plating: Au(G/F)
SIGNAL NAME	GND	RX1+	RX1-	Vbus	SUB2	D-	D+	CC2	Vbus	TX2-	TX2+	GND	①	HOUSING	1 PCS	HIGH TEMP.THERMOPLASTIC UL94V-0	BLACK
													NO.	PART NAME	QTY.	MATERIAL	REMARK




LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2023.06.19	SCALE	1:1
CHECK:	李宏鑫	DATE:	2023.06.19	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2023.06.19	DWG. NO.	
DRAWING NO.	ZB58002-24FBAP-A*			SHEET	1/2

PART NAME	Type C 24P 双排沉板1.5T SMT母座 斜口	TOLERANCE UNLESS OTHERWISE SPECIFIED:	0.0±0.3 0.00±0.2 0.000±0.1	0°±2° 0.0°±1° 0.0°±0.5°	UNIT: mm	
PART NO.	ZB58002-24PBAP-A*					


RoHS
Compliant

ZONE	EC N. NO.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2023.06.19




① 产品入载带示意图

纸箱规格
L340mm*W340mm*330mm




⑤ 外箱封箱示意图




④ 产品入外箱示意图

② 卷盘贴标签示意图



③ 10盘产品叠层示意图



NOTE:

- QUANTITY/REEL: 1000 PCS
数量/卷: 1000 PCS
QUANTITY/INNER CARTON: 1000 X 10 = 10000 PCS
数量/箱: 1000 X 10 = 10000 PCS
- FREE 15 CAVE IN THE FRONT CARRIER ADN FREE
15 CAVE IN THE END CARRIER.
包装带内圈空15格, 外圈空15格.

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2023.06.19	SCALE	1:1
CHECK:	李宏鑫	DATE:	2023.06.19	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2023.06.19	DWG. NO.	
DRAWING NO.	ZB58001/ZB58002/ZB58003			SHEET	2/2

PART NAME	Type C 24P 双排沉板1.5 包装规范	TOLERANCE UNLESS	0.0±0.3	0.°±2°	UNIT: mm	
PART NO.	ZB58001/ZB58002/ZB58003	OTHERWISE SPECIFIED:	0.00±0.2	0.0°±1°		
			0.000±0.1	0.00°±0.5°		