




RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
WF-HA2.54-2PZZ	2	2.50	7.50
WF-HA2.54-3PZZ	3	5.00	10.00
WF-HA2.54-4PZZ	4	7.50	12.50
WF-HA2.54-5PZZ	5	10.00	15.00
WF-HA2.54-6PZZ	6	12.50	17.50
.....			
WF-HA2.54-20PZZ	20	47.50	52.50

- 技术要求:
1. 塑件材料:PA66(UL-94V-0)
 2. 接触件:黄铜镀锡
 3. 接触电阻: $\leq 10m\Omega$
 4. 绝缘电阻: $\geq 100M\Omega$
 5. 额定电压:250V AC DC
 6. 额定电流:2.0A AC DC
 7. 耐压:能承受1000V AC/Minute
 8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
 9. 可焊性试验:浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求.

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u"MIN, 再镀 锡 80u"MIN	GENERAL TOLERANCES UNLESS SPECIFIED	深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
1	基座 Wafer	PA66 (UL94V-0)	1	白色	X.X ±0.30 X.° ±5°	PART NO.	TITLE:		
序号	名称	材料	数量	备注	.XX ±0.20 X.X° ±1°	WF-HA2.54-NPZZ	HA2.54MM 带扣 直针		
					.XXX ±0.10 X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
					MANUFACTURE DWG	CHED: Talen		A4	MM
						APPD: Sophia		SCALE	SHEET
								N:A	1/1