





RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.11.21



Recommended P.C.B
Layout(±0.05)

Technical Data

Material:

Contact Material:Copper Alloy

Contact Plating: Au or Sn Over Ni

Insulator Material:PPS UL94V-0

Electrical:

Rating current:1Amps/contact max

Rating voltage:60V AC/DC

Contact resistance:≤20MΩ/contact

Insulation resistance:≥1000MΩ

withstanding Voltage:500V AC/minute

Mechanical:

Operating temperatures:--40℃ to +105℃

Soldering temperature:+255℃ MAX(PPS)

Ordering Code:

MF127V-11-XX-H41-0640
1 2

1.序列号

2.Pin位数: 02-50P

X.±0.50	X.°±	PART NO: MF127V-11-XX-H41-0640		XFCN 兴飞连接器	
.X±0.25	.X°±	TITLE: 1.27mm Machined Pin Header		0769-82001899	
.XX±0.15	.XX°±			www.xfconn.com	
.XXX±0.10	.XXX°±			DWG NO: /	
UNITS:	mm	APPD	Chen ZhiQiang		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		CHKD	Liu Wei	VIEW	
		DRAW	Chen HongJiang	SCALE	SHEET
		DATE	2025.11.21	NONE	1/1
					REV
					A1