




标 记
MARK

ECN编号/变更内容
ECN NO/DEFINITION

修 改
REVISE





日 期
DATE

核 准
APPROVE




3D VIEW

- NOTES:
- 1.MATERIAL:
 - 1.1 HOUSING: LCP ,COLOR IS BLACK;
 - 1.2. CONTACT: PHOSPHOR COPPER ;
 - 2.FINISH: GOLD PLATED G/Fu”;
 - 4.ELECTRICAL:
 - 4.1 VOLTAGE RATING: 125 VAC RMS;
 - 4.2 CURRENT RATING: 1.5 AMP;
 - 4.3 CONTACT RESISTANCE: 35MILLIOHMS MAX.;
 - 4.4 WITHSTAND VOLTAGE: 500 VAC RMS 50(60)Hz,1MIN.;
 - 4.5 INSULATION RESISTANCE: 500MEGOHMS MIN @500V DC.;
 - 5.MECHANICAL:
 - 5. 1MATING/UNMATING FORCE: 22N MAX.;
 - 5. 2RETENTION STRENGTH: 50N MIN.;
 - 5. 3OPERATING LIFE: 750 CYCLES MIN.;
 - 6.ENVIRONMENTAL:
 - 6.1 STORAGE TEMPERATURE RANGE: -40℃~+85℃;
 - 6.2 OPERATION TEMPERATURE RANGE: -25℃~+70℃;
 - 7.SALT SPRAY TEST: 8H(EXCLUDING RIVETED BENDS)



PCB 参考图



3	外壳	不锈钢	镀镍	
2	接触	铜	镀金G/F	
1	基座	LCP	黑色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	网口
料 号 PART NO	HC-WK88-C42-DK

UNLESS OTHERWISE,
GENERAL TOLERANCE:

X. xxx ±0.10
X. xx ±0.20
X. x ±0.30

ANGULAR:
X. xx° ±1°
X. x' ±3°
X. x'' ±5°

比 列
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

AhYe

审 核
CHECKED

夏操云

批 准
APPROVE

赵亮亮