




- Note:
1. Material:
 - 1.1 Housing: thermoplastic high temp.UL94V-0; Color: natural.
 - 1.2 Latch: thermoplastic high temp.UL94V-0; Color: black.
 - 1.3 Terminal: copper alloy.
 - 1.4 Fitting Nail: copper alloy.
 - 1.5 Cover: Stainless steel.
 2. Finish:
 - 2.1 Terminal:
 - Underplating: Au/matt Tin overall.
 - 2.2 Fitting Nail:
 - Underplating: matt Tin overall.
 3. Product must comply HF RoHS specification.
 4. Product No:

AFC11-S**
CKTS
SOLDERING TYPE
I:Normal
J:Reverse
PLATING
1:Gold flash 1u"
2:Gold flash 2u"
3:Gold flash 3u"
B:Bright-Tin 90-120u"
C:Matt-Tin 90-120u"

REMARKS
HF:Halogen free

PACKING
A:Tape&Reel
C:Tube
H:Tape&Reel With Cover
J:Tube With Cover

CKTS	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
4	1.50	2.60	6.50	7.60		
5	2.00	3.10	7.00	8.10		
6	2.50	3.60	7.50	8.60		
7	3.00	4.10	8.00	9.10		
8	3.50	4.60	8.50	9.60		
9	4.00	5.10	9.00	10.10		
10	4.50	5.60	9.50	10.60		
11	5.00	6.10	10.00	11.10		
12	5.50	6.60	10.50	11.60		
13	6.00	7.10	11.00	12.10		
14	6.50	7.60	11.50	12.60		
15	7.00	8.10	12.00	13.10		
16	7.50	8.60	12.50	13.60		
17	8.00	9.10	13.00	14.10		
18	8.50	9.60	13.50	14.60		
19	9.00	10.10	14.00	15.10	4.40	5.65
20	9.50	10.60	14.50	15.60		
21	10.00	11.10	15.00	16.10		
22	10.50	11.60	15.50	16.60		
23	11.00	12.10	16.00	17.10		
24	11.50	12.60	16.50	17.60		
25	12.00	13.10	17.00	18.10		
26	12.50	13.60	17.50	18.60		
27	13.00	14.10	18.00	19.10		
28	13.50	14.60	18.50	19.60		
29	14.00	15.10	19.00	20.10		
30	14.50	15.60	19.50	20.60		
31	15.00	16.10	20.00	21.10		
32	15.50	16.60	20.50	21.60		
33	16.00	17.10	21.00	22.10		
34	16.50	17.60	21.50	22.60		
35	17.00	18.10	22.00	23.10		
36	17.50	18.60	22.50	23.60		
37	18.00	19.10	23.00	24.10		
38	18.50	19.60	23.50	24.60		
39	19.00	20.10	24.00	25.10		
40	19.50	20.60	24.50	25.60		
41	20.00	21.10	25.00	26.10		
42	20.50	21.60	25.50	26.60		
43	21.00	22.10	26.00	27.10		
44	21.50	22.60	26.50	27.60		
45	22.00	23.10	27.00	28.10		
46	22.50	23.60	27.50	28.60		
47	23.00	24.10	28.00	29.10		
48	23.50	24.60	28.50	29.60		
49	24.00	25.10	29.00	30.10		
50	24.50	25.60	29.50	30.60		
51	25.00	26.10	30.00	31.10		
52	25.50	26.60	30.50	31.60		
53	26.00	27.10	31.00	32.10		
54	26.50	27.60	31.50	32.60		
55	27.00	28.10	32.00	33.10		
56	27.50	28.60	32.50	33.60		
57	28.00	29.10	33.00	34.10		
58	28.50	29.60	33.50	34.60		
59	29.00	30.10	34.00	35.10		
60	29.50	30.60	34.50	35.60		

CUSTOMER DRAWING

Tolerance Unspecified
(未注公差)

0.0 ±0.15 0° ±5°

0.00 ±0.10 0° 0 ±3°

0.000 ±0.05 0° 00 ±1°

Size(图幅):

Unit(单位):

Scale(比例):

Project View
(投影视图)

Page(页数):

Rev(版本):

LXW

连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

Product Name(产品名称):

0.5Pitch H=4.4&4.95 FPC ZIF S/A Normal Type3 SMT CONN

Product No(产品料号):

AFC11-S**I***

Designer(设计):

Checked(审核):

Approved(核准):

初版发行

2011/09/16

Allan

Change Description

Date

Revisor

变更内容

日期

制/修订人

Project View
(投影视图)

Page(页数):

Rev(版本):

Product Name(产品名称):

0.5Pitch H=4.4&4.95 FPC ZIF S/A Normal Type3 SMT CONN



Product No(产品料号):

AFC11-S**I***

Designer(设计):



Checked(审核):

Approved(核准):



NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
5. THICKNESS: 0.50 ± 0.05 mm.
6. PACKING LENGTH PER 13" REEL:12.60METERS.
7. COMPONENT LOAD PER 13" REEL:1000PCS
8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~100gf).



SECTION B-B
SCALE 1:1

1.0	初版发行	2011/06/02	Allan
Rev	Change Description	Date	Revisor
版本	变更内容	日期	制/修订人

CLASSIFICATION DIMENSION (尺寸类别):	
FA1 (首次检验): ④ To ④	
■ MARK IS MAJOR DIM (重点尺寸标示)	
⊙ MARK IS CRITICAL DIM (Cpk&Cp标示)	
Tolerance Unspecified (未注公差)	Size (图幅): A4
0.0 ±0.10 0° ±3°	Unit (单位): MM
0.00 ±0.05 0° ±2°	Scale (比例): 1:1
0.000 ±0.02 0° ±1°	Page (页数): 1 OF 1
Project View (投影视角)	Rev (版本): 1.0

连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
Product Name (产品名称):	
0.5Pitch H=4.35/4.9 FPC 拉拔立式SMT型3代. 载带	
Product No (产品料号):	
EB-360XXX470-00	
Drawing No (图面编号):	Date (日期):
DNE00025-1	2011/06/02
Designer (设计):	Checked (审核):
Allan 06/02'11	Approved (核准):

CKTS	80±0.10	K0±0.10	W	W1	F	S0±0.10
4	6.80	4.70	16+0.3/-0	16.4	7.5±0.10	单边孔
5	7.30					
6	7.80					
7	8.30					
8	8.80					
9	9.30					
10	9.80					
11	10.30					
12	10.80					
13	11.30					
14	11.80					
15	12.30					
16	12.80					
17	13.30					
18	13.80					
19	14.30					
20	14.80					
21	15.30					
22	15.80					
23	16.30					
24	16.80					
25	17.30					
26	17.80					
27	18.30					
28	18.80					
29	19.30					
30	19.80					
31	20.30					
32	20.80					
33	21.30					
34	21.80					
35	22.30					
36	22.80					
37	23.30					
38	23.80					
39	24.30					
40	24.80					
41	25.30					
42	25.80					
43	26.30					
44	26.80					
45	27.30					
46	27.80					
47	28.30					
48	28.80					
49	29.30					
50	29.80					
51	30.30					
52	30.80					
53	31.30					
54	31.80					
55	32.30					
56	32.80					
57	33.30					
58	33.80					
59	34.30					
60	34.80					
		5.25	44±0.30	44.4	20.2±0.15	40.4
		56±0.30	56.4	26.2±0.15	52.4	