




VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table					
PART NO	PIN	A	B	C	D
WF-MX1.25-2PWZ	2	1.25	4.40	3.20	
WF-MX1.25-3PWZ	3	2.50	5.65	4.45	
WF-MX1.25-4PWZ	4	3.75	6.90	5.70	
WF-MX1.25-5PWZ	5	5.00	8.15	6.95	3.75
WF-MX1.25-6PWZ	6	6.25	9.40	8.20	5.00
.....					
WF-MX1.25-16PWZ	16	18.75	21.90	20.70	17.50

NOTES:

- 1. BASE: PA66
- 2. PIN: Brass
- 3. Solder Tab: Brass

SPECIFICATIONS:

- 1. Spacing: 1.25
- 2. Voltage Rating : 125V AC DC
- 3. Current Rating: 1A AC DC
- 4. Insulation Resistance: 100MΩ Min
- 5. Contact Resistance: 20mΩ Max
- 6. Withstanding voltage: 500V AC 1/Minute
- 7. Temperatuer Range: -25℃ ~+ 85℃

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. WF-MX1.25-NPWZ	TITLE: WAFER 1.25 弯针		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1