




技术要求:


1. 塑件材料:PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受1000V AC/Minute
8. 工作温度: $-25^{\circ} \sim +85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

PIN number variable size comparison table

PART NO	PIN	A	W	C
WF-ZH1. 5-2PZZ	2	1. 50	3. 60	4. 50
WF-ZH1. 5-3PZZ	3	3. 00	5. 10	6. 00
WF-ZH1. 5-4PZZ	4	4. 50	6. 60	7. 50
WF-ZH1. 5-5PZZ	5	6. 00	8. 10	9. 00
WF-ZH1. 5-6PZZ	6	7. 50	9. 60	10. 50
.....				
WF-ZH1. 5-16PZZ	16	22. 50	24. 60	25. 50

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

2	端子 Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍30u"MIN, 再镀锡80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	WF-ZH1.5-NPZZ	ZH1.5MM 直针
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE SHEET
			N:A 1/1