


DESCRIPTION

The WTM07N65VD/F is a high voltage power MOSFET combines advanced planar MOSFET designed to have better characteristics, such as fast switching time, low gate charge, low on-state resistance and high rugged avalanche characteristics. This power MOSFET is usually used in high speed switching applications of switching power supplies and adapters.



FEATURES


- * $R_{DS(ON)} \leq 1.52\Omega$ @ $V_{GS}=10V$, $I_D=3A$
- * Fast switching capability
- * Avalanche energy tested
- * Improved dv/dt capability, high ruggedness

MARKING



WPM: LOGO
07N65VD =Device Code (TO-252)
07N65VF =Device Code (TO-220F)
XXX YYWW =Date Code

SYMBOL



ABSOLUTE MAXIMUM RATINGS($T_A=25^\circ C$, unless otherwise specified.)

SYMBOL	PARAMETER		VALUE	UNIT
V_{DS}	Drain-Source Voltage		650	V
V_{GS}	Gate Source Voltage		± 30	V
I_D	Continuous Drain Current		7	A
I_{DM}	Drain Current Pulsed (Note 2)		14	A
E_{AS}	Avalanche Energy, Single Pulsed (Note 3)		150	mJ
dv/dt	Peak Diode Recovery dv/dt (Note 4)		3.2	V/ns
P_D	Power Dissipation	TO-220F	30	W
		TO-252	50	
T_J	Junction Temperature		150	$^\circ C$
T_{STG}	Storage Temperature		-55 to 150	$^\circ C$

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating: Pulse width limited by maximum junction temperature.

3. $L = 19.5mH$, $I_{AS} = 4A$, $V_{DD} = 50V$, $R_G = 25\Omega$, Starting $T_J = 25^\circ C$

4. $I_{SD} \leq 7.0A$, $di/dt \leq 200A/\mu s$, $V_{DD} \leq BV_{DS}$, Starting $T_J = 25^\circ C$

THERMAL DATA

PARAMETER		SYMBOL	RATINGS	UNIT
Junction to Ambient	TO-220F	θ_{JA}	62.5	°C/W
	TO-252		100	
Junction to Case	TO-220F	θ_{JC}	3.4	°C/W
	TO-252 (Note)		2.5	



Note: Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.

ELECTRICAL CHARACTERISTICS ($T_A=25^{\circ}\text{C}$, unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =250μA	650			V
Drain-Source Leakage Current	I _{DSS}	V _{DS} =650V, V _{GS} =0V			1	μA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±30V, V _{DS} =0V			±100	nA
ON CHARACTERISTICS						
Static Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =3.0A		1.25	1.52	Ω
Gate Threshold Voltage	V _{GS(TH)}	V _{GS} =V _{DS} , I _D =250μA	2.0		4.0	V
DYNAMIC CHARACTERISTICS						
Input Capacitance	C _{ISS}	V _{DS} =25V, V _{GS} =0V, f=1.0MHz		750		pF
Output Capacitance	C _{OSS}			65		
Reverse Transfer Capacitance	C _{RSS}			5		
SWITCHING PARAMETERS						
Total gate charge(Note 1)	Q _g	V _{DS} =520V, V _{GS} =10V I _D =7A, I _{GM} =1mA (Note 1, 2)		25		nC
Gate-source charge	Q _{gs}			6.5		
Gate-drain charge	Q _{gd}			5.5		
Turn-On Delay Time(Note 1)	t _{D(on)}	V _{DD} =100V, V _{GS} =10V I _D =7A, R _G =25Ω (Note 1, 2)		10		nS
Turn-On Rise time	t _r			19		
Turn-Off Delay Time	t _{D(off)}			68		
Turn-Off Fall time	t _f			32		
DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
Maximum Continuous Drain-Source Diode Forward Current	I _S				7	A
Maximum Pulsed Drain-Source Diode Forward Current	I _{SM}				14	A
Drain-Source Diode Forward Voltage	V _{SD}	V _{GS} = 0 V, I _{SD} =7A			1.4	V
Reverse Recovery Time	t _{rr}	V _{GS} = 0 V, I _{SD} =7A,		325		ns
Reverse Recovery Charge	Q _{rr}	di/dt = 100 A/μs		7.5		μC

Note:


1. Pulse test: pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$;
2. Essentially independent of operating temperature.




TEST CIRCUITS AND WAVEFORMS(Con.t)




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Charge
Gate Charge Waveform









Unclamped Inductive Switching Test Circuit









Unclamped Inductive Switching Waveforms


TYPICAL CHARACTERISTICS(1)



TYPICAL CHARACTERISTICS(Con.t)



TO- 220F PACKAGE OUTLINE DIMENSIONS




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max	Min	Max
A	4.300	4.750	0.169	0.185
A1	1.830 REF		0.072 REF	
A2	2.300	2.850	0.090	0.112
A3	2.500	2.900	0.098	0.114
b	0.400	0.420	0.016	0.016
b1	1.220	1.280	0.048	0.050
C	0.690	0.720	0.027	0.028
c	0.490	0.510	0.019	0.020
D	9.960	10.200	0.392	0.400
E	15.000	15.950	0.588	0.625
e	2.574 TYP		0.101TYP	
F	3.470 REF		0.136 REF	
y	3.200 REF		0.125 REF	
h	0.000	0.300	0.000	0.012
L	28.780	28.900	1.128	1.133
L1	2.990	3.100	0.117	0.122

TO - 220F PACKING INFORMATION



50PCS




20 Tube



Outer Box



5 Inner
Box




Inner Box

Package version	Tube dimensions LxWxH (mm)	Per Tube (pcs)	Tube per box	Inner box dimensions LxWxH (mm)	PCS/ Inner box	Outer box dimensions LxWxH(mm)	PCS/ Outer box
TO-220F	530*32*7	50	20	580*155*50	1000	602*277*188	5000

TO - 252 PACKAGE OUTLINE DIMENSIONS



TO - 252 PACKING INFORMATION



Outer box

Inner box

Package version	Reel dimensions $\Phi \times H$ (mm)	Per Reel (pcs)	Reels per box	Inner box dimensions $L \times W \times H$ (mm)	Outer box (pcs)	Outer box dimensions $L \times W \times H$ (mm)
TO-252	$\Phi 330 \times 20$	2500	2	360*340*50	25000	375*375*280

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.