




RoHS




REV.	ECN.#	DESCRIPTION	NAME	DATE
A0	_____	NEW RELEASE	liuhongping	2023.01.0

NOTES:

1. . FINISH:
 - 1.1 TERMINAL: Au 15 μ " MIN. PLATED ON CONTACT AREA;
Tin 50 μ " MIN PLATED ON SOLDER AREA;;
Ni 20 μ " MIN. UNDERPLATED OVERALL.
 - 1.2 OTHER: CLEANING.
 2. ELECTRICAL SPECIFICATION:
 - 2.1 CONTACT RESISTANCE: 100m Ω MAX.
 - 2.2 INSULATION RESISTANCE: 500M Ω MIN.
 - 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.
 3. ENVIRONMENTAL SPECIFICATION:
 - 3.1 OPERATING CONDITION: TEMPERATURE-40°C~+85°C;
HUMIDITY 80% R.H MAX
 - 3.2 SALT SPRAY: 24H
 4. SOLDER ABILITY: 245±5°C, 5±0.5s
 5. IR REFLOW: THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.

7	端子	磷铜	8	
6	Z形片	不锈钢	1	
5	小轴	黄铜	1	
4	推杆	不锈钢	1	
3	弹簧	不锈钢	1	
2	按钮	LCP黄色	1	
1	塑胶主体	LCP黑色	1	
序号	名称	材料	数量	备注




MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X. ±2°	X. ±2°				
X. ±0.30	.X. ±0.012				
X.X. ±0.20	.XX. ±0.008				
XXX. ±0.10	.XXX. ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilai Metal Plastic Technology Co.,Ltd					
TITLE	3.0H PIN-PUSH SIM CARD			DR	
PART NO.	102154002-YT			CHKD	
PRO J.	PAGE	1/4	UNITS	mm	APPD
	SIZE	A4	SCALE	1:1	DIS NO.

RoHS


1 2 3 4 5 6 7

USER DIRECTION OF UNREELING





NOTES

1. NUMBER OF CONNECTORS: 500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 2000PCS/CARTON



MILLIMETERS	INCH
X. ±2'	X. ±2'
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBilai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBilai Metal Plastic Technology Co.,Ltd	
TITLE	3.0H PIN-PUSH SIM CARD
PART NO.	102154002-YT
PRO J.	PAGE 2/4 UNITS mm APPD
	SIZE A4 SCALE 1:1 DIS NO.




东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

1 2 3 4 5 6 7

1 2 3 4 5 6 7

RoHS





REV.	ECN.#	DESCRIPTION	NAME	DATE
A0	_____	NEW RELEASE	liuhongping	2023.01.02

技术要求:

1. 产品外观无脏污, 刮伤, 变形现象
2. 塑体无毛边, 未射饱; 接触片无氧化, 生锈现象

备注: 接触片镀金层的厚度可根据客户的需求做变更



字母是正向的

2	接触片	磷铜	1	底层Ni≥40 μ", 表层Au,
1	抽屉	PBT黑	1	
序号	名称	材料	数量	备注

MILLIMETERS	INCH
X. ±2'	X. ±2'
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004


THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF Dongguan JinBilai
Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF Dongguan
JinBilai Metal Plastic Technology Co.,Ltd

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	3.0H PIN-PUSH SIM CARD	DR		
PART NO.	102154002-YT	CHKD		
PRO J.	PAGE 3/4 UNITS mm	APPD		
SIZE A4	SCALE 1:1	DIS NO.		

1 2 3 4 5 6 7

RoHS



PE BAG

技术要求:

1. 材质说明: PE
2. 规格尺寸: 100*150*0.08mm
3. 100PCS/袋

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X. ±2'	X. ±2'				
.X ±0.30	.X ±0.012				
.XX ±0.20	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBilai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBilai Metal Plastic Technology Co.,Ltd					
PART NO.	102154002-YT			CHKD	
PRO J.	PAGE	4/4	UNITS	mm	APPD
	SIZE	A4	SCALE	1:1	DIS NO.