



Features

- Epitaxial planar die construction
- Built-in biasing resistors (R_1 : 4.7k Ω , R_2 : 47k Ω)
- Also available in lead free version
- RoHS compliant with Halogen-free

Mechanical Data

- Case: SOT-23
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



Ordering Information

Part Number	Package	Shipping Quantity
MMUN2233LT1G	SOT-23	3000 pcs / Tape & Reel

Maximum Ratings (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
		SOT-23	
Supply Voltage	V_{CC}	50	V
Input Voltage	V_I	-5 to +30	V
Output Current	I_O	100	mA
Collector Current	$I_{C(\text{Max})}$	100	mA
Power Dissipation	P_D	200	mW
Junction Temperature Range	T_J	-55 ~ +150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150	$^\circ\text{C}$

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input Voltage	$V_{I(OFF)}$	$V_{CC} = 5V, I_O = 100\mu A$	0.5	-	-	V
Input Voltage	$V_{I(ON)}$	$V_O = 0.3V, I_O = 5mA$	-	-	1.3	V
Output Voltage	$V_{O(on)}$	$I_O = 5mA, I_I = 0.25mA$	-	-	0.3	V
Input Current	I_I	$V_I = 5V$	-	-	1.8	mA
Output Current	$I_{O(off)}$	$V_{CC} = 50V, V_I = 0V$	-	-	0.5	μA
DC Current Gain	G_I	$V_O = 5V, I_O = 10mA$	80	-	-	-
Input Resistor	R_I		3.29	4.7	6.11	k Ω
Resistance ratio	R_2/R_1		8	10	12	-
Gain-Bandwidth Product	f_T	$V_{CE} = 10V, I_E = 5mA$ $f = 100MHz$	-	250	-	MHz

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Input Voltage vs Output Current




Fig 2 Output Current vs Input Voltage




Fig 3 DC Current Gain vs Output Current




Fig 4 Output Voltage vs Output Current





Fig 5 Output Current vs. Output Voltage

Package informantion (Unit: mm)

SOT-23



Mounting Pad Layout (Unit: mm)

