






G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
Voltage rating: 24V AC
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles
- 9.Waterproof grade: IP-X6

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First



RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05mm

1	SHELL	ZN-ALLOY	Ni PLATED
2	MID PLATE	STAINLESS STEEL	--
3	EMI	STAINLESS STEEL	--
4	HOUSING	HIGH TEMPERATURE PLASTIC	LCP BLACK UL 94 V-0
5	TERMINALS	COPPER ALLOY	Au PLATING ON CONTACT AREA
	WATERPROOF RING	SILICA GEL	RED
NO.	PARTS	MATERIAL	REMARKS



RoHS
Compliant
2002/95/EC



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:

X. ±0.40
X.x ±0.30
X.xx ±0.20
Angles ±3°

Title: Horizontal Type-c 16P Female
SMT Sink 0.8 CH=0.78 L=6.7mm

Molde Code: GT-USB-7103A

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2024.12.11

品赞科技®
b-Switch
www.dg-switch.com

REV: A1 SHEET: 1/1