







REV.	ECN.#	DESCRIPTION	NAME	DATE
A0	_____	NEW RELEASE	HuHaoteng	2023.01.02
A1	_____	取消前空透明Cover tape 最小300mm	lhp.liu	2024.04.03



NOTES

1. MATERIAL:
 - 1.1 HOUSING: LCP UL94V-0; COLOR: WHITE
 - 1.2 TERMINAL: C5210
 - 1.3 SHELL: SUS201
 2. FINISH:
 - 2.1 TERMINAL: G/F PLATED ON CONTACT AREA;
G/F PLATED ON SOLDER AREA;
Ni 20 μ m MIN. UNDER PLATED OVERALL.
 - 2.2 SHELL: Ni 20 μ m MIN. UNDER PLATED OVERALL.
 3. ELECTRICAL SPECIFICATION:
 - 3.1 RATED CURRENT: 0.5A.
 - 3.2 CONTACT RESISTANCE: 100m Ω MAX.
 - 3.3 INSULATION RESISTANCE: 100M Ω MIN.
 - 3.4 DIELECTRIC WITHSTANDING VOLTAGE: 100V AC .
 4. MACHINERY SPECIFICATION:
 - 4.1 MATING FORCE: 10N MAX.
UNMATING FORCE: 10N MAX.
 - 4.2 DURABILITY: 1000 CYCLES MIN.
 5. ENVIRONMENTAL SPECIFICATION:
 - 5.1 OPERATING CONDITION: TEMPERATURE -40°C ~ +85°C
HUMIDITY 80% R.H MAX
 - 5.2 SOLDER ABILITY: 245±5°C, 5±0.5s
 - 5.3 IR REFLOW: THE PEAK TEMPERATURE ON THE BOARD
BE MAINTAINED FOR 10 SECONDS AT 260°C.



SIM pin assignment	
	Name
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved


TF CARD PIN ASSIGNMENT	
PIN NO.	PIN ASSIGNMENT
T1	DAT2
T2	CD/DAT3 ²
T3	CMD
T4	VDD
T5	CLK
T6	VSS
T7	DAT0
T8	DAT1

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD						
X.* ±2'	X.* ±2'							
X .±0.30	.X ±0.012							
XX ±0.20	.XX ±0.008							
XXX ±0.10	.XXX ±0.004							
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuAn JinBilai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuAn JinBilai Metal Plastic Technology Co.,Ltd		TITLE	2.3H 二合一卡座插脚		DR			
		PART NO.	102312992			CHKD		
		PRO J.	PAGE	1/2	UNITS	mm	APPD	
			SIZE	A4	SCALE	1:1	DIS NO.	

1 2 3 4 5 6 7


RoHS

USER DIRECTION OF UNREELING



NOTES

1. NUMBER OF CONNECTORS: 1000PCS/REEL
2. LEAD TAPE LENGTH



A1


3. QUANTITY: 10000PCS/CARTON

COVER TAPE PEELING ANGLE: 165°~180°


PEELING FORCE: 20~130g

CARRIER TAPE

USER DIRECTION OF UNREELING





DETAIL B



DETAIL B

10-RELL

4-TRIANGLE PARTITION

CARTON
350*350*345

MILLIMETERS	INCH			
X. ±2'	X. ±2'			
.X ±0.30	.X ±0.012			
.XX ±0.20	.XX ±0.008			
.XXX ±0.10	.XXX ±0.004			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBilai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBilai Metal Plastic Technology Co.,Ltd				
TITLE	2.3H 二合一卡座插脚	DR		
PART NO.	102312992	CHKD		
PRO J.	PAGE 2/2	UNITS mm	APPD	
	SIZE A4	SCALE 1:1	DIS NO.	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

1 2 3 4 5 6 7