



P. C. B LAYOUT TOP VIEW



技术性能

- 插入力: 5~20N (0.3~3.0kgf)
- 拔出力: 5~20N (0.3~3.0kgf)
- 接触电阻: $\leq 30\text{m}\Omega$
- 绝缘电阻: $>100\text{M}\Omega$ DC 500V
- 耐电压: AC 500V 1min 无飞弧及击穿
- 寿命: 10000 10~20次/min
- 额定负载: DC 12V 1A
- 适用温度范围: -25~85° C
- 推荐使用插头:

Schematic	JQ-DC-0002F-1	JQ-DC-0002F-2
	1 3 2	1 2

序号	零件料号	名称	材料	数量	镀层/颜色	备注
1	JQ-DC-0002F-平片	1号脚	黄铜=0.35	1PCS	Ag	
2	JQ-DC-0002F-弹片	2号脚	锰钢=0.25	1PCS	Ag	
3	JQ-DC-0002F-弯钩	3号脚	黄铜=0.35	1PCS	Ag	
4	JQ-DC-0002F-圆针	PIN	黄铜	1PCS	TX	
5	JQ-DC-0002F-基座	塑料座	PBT	1PCS	黑色	
6	JQ-DC-0002F-盖子	塑料盖	PBT	1PCS	黑色	

SH 首韩 深圳市首韩科技有限公司

1. 尺寸
X ±0.15
XX ±0.10
XXX ±0.05

2. 带环
XX ±2°
X.X ±1°

绘制	李春风	日期	2020.8.24	品名	DC POWER JACK		
审核	钟华华	日期	2020.8.24	型号	DC002F-1.3		
批准	罗孝金	日期	2020.8.24	页码	1F1	A4	⊕



深圳市首韩科技有限公司
SHENZHEN SHOUHAN TECHNOLOGY CO., LTD
Tel: 0755-27597601 Fax: 0755-27597491

承 认 书

SPECIFICATION FOR APPROVAL

产品编码
Material code:

产品名称 Project: DC座

规格型号 Part No: DC002F-1.3

贵公司承认印 Approval signatures

料号/Part No.	签章/Signatures

日期 Date:

拟制/Drawn	李春风	
审核/Check	钟华华	
批准/Approved	罗孝金	



深圳市首韩科技有限公司

品名 (NAME) : DC座		規格 (SPECIFICATION)	
ITEM 專案		TEST CONDITION 測試條件	SPECIFICATION 規格
3 . ELECTRONICAL RESISTANCE 電氣性能			
3.1	CONTACT RESISTANCE 接觸阻抗	Being measured at 1KHZ small current connect resistance meter. 在1KHZ小電流下測量。	30毫歐以下
3.2	INSULATION RESISTANCE 絕緣阻抗	Measurements shall be made following application of DC500V potential across terminals and across terminals and frame for 1 minute. 在端子之間和端子與殼之間加DC500V條件下，持續1分鐘測量。	100M min 100兆歐以上。
3.3	WITHSTAND VOLTAGE 耐電壓	AC500V(50HZ or 60HZ) shall be applied across terminals and across terminals and frame for one minute. 在端子之間和端子與殼之間加AC500V條件下，持續1分鐘測量。	There shall be no breakdown 無擊穿現象。
4 . MECHANICAL CHARACTERISTICS 機械性能			
4.1	INSERTION AND WITHDRAW 插拔力	Being measure at across spring piece and across matching plug for ergo meter. 用測力計在插頭與彈片之間進行測試	Insertion and extraction force 5-20N, 插拔力5-20N
4.2	TERMINAL STRENGTH 端子強度	A static force of 500gf being applied in one direction on the top of terminal for 1 minute. 一個500克之靜負荷施加於端子頂部的一個方向持續1分鐘。	There shall be no sign of damage mechanically and electrically. 無任何迹象顯示機械及電器性能之損壞。



5. DURABILITY 耐久性

5. 1	SOLDERING TEST 可焊性試驗	The top of terminals shall be dipped 2mm in the loder bath at a temperature of 230: 5°C for 3sec. 端子頂部被浸入焊池2mm深，溫度230±5°C時間3秒	A new uniform coating of shall cover above 75 % of the surface being Immersed. 浸入的部分75%以上表面將被錫覆蓋.
5. 2	LIFE TEST 壽命試驗	10000 cycles of operation at rate of 20-30cycles per minute with unloading. 無負載條件下，每分鐘10—20次的速度操作10000次。	(1) Contact resistance 40mΩ max 接觸阻抗40毫歐以下 (2) Drive force 30 initial value 動作力變化範圍初始值30 (3) ITEM 專案—3.2 (4) ITEM 專案—3.3 (5) INEM—4.2
5. 3	HEAT TEST 耐熱試驗	80: 2°C for 48 hours after test keep in normal condition for 30minutes. 在80±2°C環境中放48小時，再放在正常環境中30分鐘後進行測試。	(1) Contact resistance 50mΩ max 接觸阻抗50毫歐以下
5. 4	HUMIDITY TEST 耐濕試驗	The condition of temperature 40±2°C and humidity 90-95 % for 48 hours after test keep in normal condition for 30 min. 在40±2°C 90—95% Rh環境中放48小時，再放在正常環境中30分鐘後進行測試。	(2) Insulation resistance 100MΩ min 絶緣电阻100M歐以上 (3) There shall be no sign of damage mechanically and electrically. 無任何迹象顯示機械及電器性能之損壞。
5. 5	COLD TEST 耐冷試驗	At—30±2°C for 48 hours, after test keep in normal condition for 30 min. 在—30±2°C環境中放48小時，再置於正常環境中30分鐘後進行測試。	