









RECOMMENDED METAL MASK LAYOUT
(TOLERANCE:±0.02,T=0.08 mm)



RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE


NOTES:




- 1.0 VOLTAGE: 30V AC/DC
- 2.0 IMPEDANCE: 50Ω
- 3.0 POWER RATING: 2W
- 4.0 OPERATION TEMPERATURE: -40° C TO +85° C
- 5.0 CONTACT RESISTANCE: SIGNAL PIN 100mΩ MAX;SHELL 50mΩ MAX
- 6.0 INSULATION RESISTANCE: 300MΩ MIN INITIAL,100MΩ MIN AFTER TEST
- 7.0 DIELECTRIC WITHSTANDING VOLTAGE: 100V AC FOR ONE MINUTE
- 8.0 DURABILITY:30 CYCLES
- 9.0 IR REFLOW CYCLE: 2 CYCLES MAX.
- 10.0 VSWR:
1.2MAX.at DC~3 GHz ; 1.3MAX.at 3~6 GHz; 1.5MAX.at 6~11 GHz
- 11.0 INSERTION LOSS:
-0.1dB MAX.at DC~3 GHz ; -0.2dB MAX.at 3~6 GHz; -0.5dB MAX.at 6~11 GHz
- 12.0 ISOLATION:
-20dB MIN.at DC~3 GHz ; -15dB MIN.at 3~6 GHz; -10dB MIN.at 6~11 GHz

3	SIGNAL IN CONTACT	STAINLESS STEEL, GOLD PLATING OVER NICKEL			
2	SIGNAL CONTACT MOLDING	LCP, BLACK, UL 94 V-0	5	GROUND CONTACT	COPPER ALLOY, GOLD PLATING ON SOLDER AREA OVER NICKEL
1	GROUND CONTACT MOLDING	LCP, BLACK, UL 94 V-0	4	SIGNAL OUT CONTACT	STAINLESS STEEL, GOLD PLATING OVER NICKEL
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS





深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RF六代测试座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW24-RF1412-065B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2511191701
			SHEET NO.	1 OF 1



DIRECTION OF UNREELING



TRAILER

TAPING (FREE)

LEADER

STYLE AND DIMENSION OF REEL

PER REEL 15000 CONNECTORS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	
			SHEET NO.	1 OF 1