







REV.	ECN NO.	REVISED	DATE



PCB Layout Diagram
Top View

NOTE:

1.MATERIAL:

a.HOUSING:PBT

b.CONTACT:BRASS

(SURFACE PLATING: Sn100u"-120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 30 MILLIOHMS MAX

b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL

d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

电池座系列

DIP 90° TYPE

PLATING:

A-Au1U*

J-Ni100U*~120U*

K-Sn100U*~120U*

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±1°
X.X :±0.25 X.X :±0.5°
X.XX :±0.20
X.XXX :±0.10

WEIGHT: 1.8g

SHEET 1 OF 1



东莞市溪榜电子有限公司

DONG GUAN XI BANG ELECTRONICS CO., LTD.

DSND		DATE	2017-12-14
CHKD		DATE	2017-12-14
APVD		DATE	2017-12-14
SCALE: 2:1	SIZE: A4	VIEW: ④ ⑤	
UNIT: mm	REV.: A/0	OBJECT: MY	DRAW NO.

TITLE:	
PART NO.:	

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL(-)	1	BRASS, T=0.30mm	Sn Plating
2	TERMINAL(+)	1	BRASS, T=0.30mm	Sn Plating
1	HOUSING	1	PBT	BLACK